

MPS - MSL Level for Lead Free Products (260°C max)

Package Type	Lead Finish	MSL Level
FCQFN-3x4	100% Matte Sn	1
FCQFN-4x5	100% Matte Sn	1
FCQFN-5x5	100% Matte Sn	1
FCQFN-6x6	100% Matte Sn	1
MSOP-8	100% Matte Sn	1
MSOP-8-EP	100% Matte Sn	2
MSOP-10	100% Matte Sn	1
MSOP-10-EP	100% Matte Sn	2
PDIP-8	100% Matte Sn	N/A
PDIP-16	100% Matte Sn	N/A
QFN/TQFN-2x2	100% Matte Sn	1
QFN/TQFN-2x3	100% Matte Sn	1
QFN/TQFN-3x3	100% Matte Sn	1
QFN/TQFN-3x4	100% Matte Sn	1
QFN/TQFN-4x4	100% Matte Sn	1
QFN/TQFN-4x5	100% Matte Sn	2
QFN/TQFN-5x5	100% Matte Sn	2
QFN/TQFN-5x6	100% Matte Sn	2

Package Type	Lead Finish	MSL Level
QFN/TQFN-6x6	100% Matte Sn	2
QFN/TQFN-7x7	100% Matte Sn	2
QFN/TQFN-8x8	100% Matte Sn	2
SC70	100% Matte Sn	1
SOICN-8	100% Matte Sn	2
SOICN-8-EDP	100% Matte Sn	2A
SOICN-16	100% Matte Sn	2
SOICW-20	100% Matte Sn	3
SOICW-24	100% Matte Sn	3
SOICW-28	100% Matte Sn	3
SOT23-3/5/6	100% Matte Sn	1
TSOT23-5/6	100% Matte Sn	1
TSSOP-8	100% Matte Sn	2
TSSOP-14	100% Matte Sn	2
TSSOP-16	100% Matte Sn	2
TSSOP-16-EP	100% Matte Sn	2A
TSSOP-20	100% Matte Sn	2
TSSOP-20-EP	100% Matte Sn	2A
TSSOP-28	100% Matte Sn	2