EVM3690-30A-BF-00A

16V, Dual 18A, High-Efficiency, Synchronous Step-Down Module Evaluation Board

DESCRIPTION

The EVM3690-30A-BF-00A evaluation board is designed to demonstrate the capabilities of the MPM3690-30A, a fully integrated, high-efficiency, synchronous, dual 18A output current, step-down power module.

The MPM3690-30A adopts internally compensated constant-on-time (COT) control to provide fast transient response and ease loop stabilization. The operating frequency can be set between 400kHz to 1MHz by connecting a resistor between f_{SET} and AGND. Refer to the MPM3690-30A datasheet for more detailed information.

It is recommended to read the datasheet for the MPM3690-30A prior to making any changes to the EVM3690-30A-BF-00A.

PERFORMANCE SUMMARY (1)

Specifications are at T_A = 25°C, unless otherwise noted.

Parameters	Conditions	Value
Input voltage range (V_{IN})		3.2V to 16V (2)
Output voltage (V_{OUT})	V_{IN} = 3.2V to 16V, I_{OUT} = 0A to 18A	1.2V
Maximum output current (I_{OUT})	V_{IN} = 3.2V to 16V, V_{OUT} = 1.2V	18A
Full load efficiency (3)	V_{IN} = 12V, V_{OUT} = 1.2V, I_{OUT} = 18A, f_{SW} = 500kHz	91.28%
Peak efficiency (3)	V_{IN} = 12V, V_{OUT} = 1.2V, I_{OUT} = 10A, f_{SW} = 500kHz	92.96%
Default switching frequency		500kHz

Notes:

1) For different V_{IN} and V_{OUT} specifications with different output capacitors, the application circuit parameters may require changes.
2) If V_{IN} < 4V, an external 3.3V V_{CC} is required.
3) Only one channel is working; the other channel is off.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVALUATION BOARD



(LxWxH) 10cmx10cmx1.5cm

Board Number	MPS IC Number
EVM3690-30A-BF-00A	MPM3690GBF-30A

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

QUICK START GUIDE

The EVM3690-30A-BF-00A evaluation board is easy to set up and use to evaluate the performance of the MPM3690-30A. See Figure 1 on page 4 for the proper measurement equipment set-up, and follow the procedure below:

1. Preset the power supply (V_{IN}) between 4V and 16V, then turn off the power supply. (4)
2. Connect the power supply terminals to:
   a. Positive (+): VIN
   b. Negative (-): GND
3. Connect the load terminals (no initial load) to:
   a. Positive (+): VOUT
   b. Negative (-): GND
4. After making the connections, turn on the power supply on. The board should automatically start up.
5. Check for the proper output voltage (V_{OUT}) between the VOSENSE and VOGNDSEN terminals.
6. Once the proper V_{OUT} is established, adjust the load within the operating range and measure the efficiency, output ripple voltage, and other parameters. (5)
7. After completing all tests, adjust the load to 0A, then turn off the input power supply.

Notes:

4) Ensure that V_{IN} does not exceed 16V.
5) When measuring the output or input voltage ripple, do not use the long ground lead on the oscilloscope probe.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.



Figure 1: Proper Measurement Equipment Set-Up

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVALUATION BOARD SCHEMATIC



Figure 2: Evaluation Board Schematic

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVM3690-30A-BF-00A BILL OF MATERIALS

Qty	Ref	Value	Description	Package	Manufacturer	Manufacturer PN
2	C19, C20	100µF	Surface-mount polymer aluminum capacitor, 25V	SMD	Panasonic	25SVPF100M
8	C11, C14, C15, C17, C24, C27, C28, C30	47µF	Ceramic capacitor, 6.3V	0805	Murata	GRM21BR60J476 ME15L
8	C2, C3, C4, C5, C6, C8, C9, C10	22µF	Ceramic capacitor, 25V	0805	Murata	GRM21BR61E226 ME44L
2	C1, C7	1µF	Ceramic capacitor, 25V	0805	Murata	GRM219R71E105 KA88D
2	C36, C37	100nF	Ceramic capacitor, 50V	0603	Murata	GRM188R71E104 KA01D
2	C35, C23	33nF	Ceramic capacitor, 50V	0603	Wurth	885012206092
4	R4, R5, R10, R14	0Ω	Resistor, 1%	0603	Yageo	RC0603FR-070RL
2	R16, R17	48kΩ	Resistor, 1%	0603	Yageo	RC0603FR-0748KL
4	R2, R7, R12, R13	10kΩ	Resistor, 1%	0603	Yageo	RC0603FR-0710KL
2	R3, R9	60.4kΩ	Resistor, 1%	0603	Yageo	RC0603FR-0760K4L
2	SWITCH1, SWITCH2	500mA	Switch slide SPDT, 5V	10mmx 2.5mm	Wurth	450301014042
2	C22, C33	220µF	Tantalum capacitor, 6.3V, 15mΩ	SMD	Panasonic	EEFCX0J221R
1	U1	MPM3690 -30A	16V, dual 18A, step-down power module	BGA (16mmx 16mmx 5.18mm)	MPS	MPM3690GBF-30A

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS

Performance curves and waveforms are tested on the evaluation board. V_{IN} = 12V, V_{OUT1} = V_{OUT2} = 1.2V, f_{SW1} = f_{SW2} = 500kHz, T_A = 25°C, unless otherwise noted.

Efficiency vs. Load Current (6)

V_{IN} = 12V, with external 3.3V VCC



Thermal Performance

I_{OUT1} = I_{OUT2} = 18A, no forced airflow, T_A = 28°C, T_{CASE} = 73.9°C



Note:

6) Only one channel is working; the other channel is off.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board. V_{IN} = 12V, V_{OUT1} = V_{OUT2} = 1.2V, f_{SW1} = f_{SW2} = 500kHz, T_A = 25°C, unless otherwise noted.

Steady State

I_{OUT1} = I_{OUT2} = 18A



Load Transient Ripple

I_{OUT1} = 0A to 9A, slew rate = 10A/μs



Start-Up through VIN

I_{OUT1} = I_{OUT2} = 18A



Shutdown through VIN

I_{OUT1} = I_{OUT2} = 18A



Start-Up through EN

I_{OUT1} = 18A



Shutdown through EN

I_{OUT1} = 18A



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PCB LAYOUT



Figure 3: Top Silk



Figure 4: Top Layer



Figure 5: Mid-Layer 1



Figure 6: Mid-Layer 2

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PCB LAYOUT *(continued)*



Figure 7: Bottom Layer



Figure 8: Bottom Silk

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	08/23/2021	Initial Release	-

Notice: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.