



PRODUCT RELIABILITY REPORT

Product: MP4558/59/60/61

**Reliability Department
Monolithic Power Systems
79 Great Oaks Boulevard
San Jose, CA 95119
Tel: 408-826-0600
Fax: 408-826-0601**

1. Device Information

Product:	MP4558/59/60/61
Package:	QFN3×3-10 and SOIC8-EP
Process Technology:	BCD
Report Date:	08/08/2016

2. Summary of Test Results

Test	Test Condition	Lot# or Date Code	Test Results (S.S./Rej)	Comment
Temperature, Bias, and Operating Life	JESD22-A108, @+125°C for 1000 hours or equivalent	FA0Z2608	80/0	
		FA0Z2608B	80/0	
		FA0Z2608C	80/0	
ESD: Human Body Model (HBM)	ANSI/ESDA/JEDEC JS-001	FA0Z2608A	3/0	>2000V
		FA0Z2608B	3/0	
ESD: Device Charged Model (CDM)	ANSI/ESDA/JEDEC JS-002	FA0Z2608A	3/0	>750V
		FA0Z2608B	3/0	
Latch-up	EIA/JESD78	FA0Z2608A	6/0	>+/-100mA & >1.5Vccmax
		FA0Z2608B	6/0	
Moisture/Reflow Sensitivity	J-STD-020	1111	300/0	QFN3×3-10,MSL=1
		1114	300/0	QFN3×3-10,MSL=1
		1117	300/0	QFN3×3-10,MSL=1
		1224	300/0	SOIC8-EP,MSL=2A
		1245	300/0	SOIC8-EP,MSL=2A
		1301	300/0	SOIC8-EP,MSL=2A
High Temperature Storage Life	JESD22-A103, @150°C for 1000 hours	1111	50/0	QFN3×3-10
		1114	50/0	QFN3×3-10
		1117	50/0	QFN3×3-10
		1224	50/0	SOIC8-EP
		1245	50/0	SOIC8-EP
		1301	50/0	SOIC8-EP
Temperature Cycling	JESD22-A104, from -65°C to 150°C for 1000 cycles or equivalent	1111	80/0	QFN3×3-10
		1114	80/0	QFN3×3-10
		1117	80/0	QFN3×3-10
		1224	80/0	SOIC8-EP
		1245	80/0	SOIC8-EP
		1301	80/0	SOIC8-EP

Accelerated Moisture Resistance- Unbiased Autoclave	JESD22-A102, @ 121°C/100%RH for 168 hours or equivalent	1111	80/0	QFN3×3-10
		1114	80/0	QFN3×3-10
		1117	80/0	QFN3×3-10
		1224	80/0	SOIC8-EP
		1245	80/0	SOIC8-EP
		1301	80/0	SOIC8-EP
Steady State Temperature Humidity Bias Life Test	JESD22-A101, @85°C/85%RH static bias at Vinmax for 1000 hours or equivalent	1111	80/0	QFN3×3-10
		1114	80/0	QFN3×3-10
		1117	80/0	QFN3×3-10
		1224	80/0	SOIC8-EP
		1245	80/0	SOIC8-EP
		1301	80/0	SOIC8-EP

3. Failure Rate Calculation

Sample Size: 7210
 Rejects: 0
 Activation Energy (eV): 0.7
 Equivalent Device Hours: 5.62×10^8 Hours
 Failure Rate (FIT@60%CL): 1.6 FIT
 MTBF (years): 70,162 Years

Revision / Update History

Revision	Reason for Change	Date	Rel Engineer
1.0	Initial release	August 2016	Ramon Lei

Appendix: Description of Reliability Test and Failure Rate Calculation

High Temperature Operating Life Test

Purpose: This test is a worst-case life test that checks the integrity of the product. The high temperature testing is use for acceleration of any potential failures over time. The calculation for failure rate (FIT) using the operating ambient temperature is done using the Arrhenius equation.

Condition: 125°C @ Vinmax

Pass Criteria: All units must pass the min/max limits of the datasheet.

ESD Test

Purpose: The purpose of the ESD test is to guarantee that the device can withstand electrostatic voltages during handling.

Condition: Human Body Model and Charged Device Model

Pass Criteria: ESD Testing on every pin. The device must be fully functional after testing and pass the min/max limits in the datasheet.

IC Latch-Up Test

Purpose: The purpose of this specification is to establish a method for determining IC latch-up characteristics and to define latch-up failure criteria. Latch-up characteristics are extremely important in determining product reliability and minimizing No Trouble Found (NTF) and Electrical Overstress (EOS) failures due to latch-up.

Condition: Voltage and current injection

Pass criteria: All pins with the exception of “no connect” pins and timing related pins, shall be latch-up tested. The device must be fully functional after testing and pass the min/max limits in the datasheet.

Moisture/Reflow Sensitivity Classification for Nonhermetic Solid State Surface Mount Devices

Purpose: The purpose of this standard is to identify the classification level of nonhermetic solid state surface mount devices (SMDs) that are sensitive to moisture-induced stress so that they can be properly packaged, stored, and handled to avoid damage during assembly solder reflow attachment and/or repair operations.

Condition: Bake + moisture sock + 3X reflow at 260°C

Pass criteria: All units must pass the min/max limits of the datasheet

High Temperature Storage Life

Purpose: The test is typically used to determine the effects of time and temperature, under storage conditions, for thermally activated failure mechanisms and time-to-failure distributions of solid state electronic devices, including nonvolatile memory devices (data retention failure mechanisms).

Condition: Bake at 150°C

Pass Criteria: All units must pass min/max limits of the datasheet

Accelerated Moisture Resistance- Unbiased Autoclave

Purpose: To check the performance of the device in humid environments. This test checks the integrity of the passivation, poor metal to plastic seal and contamination level during assembly and material compatibility.

Condition: 121°C/15psig/100% RH (no bias)

Pass Criteria: All units must pass min/max limits of the datasheet

Temperature Cycle Test

Purpose: This test is used to evaluate the die attach integrity and bond integrity. This is similar to the Thermal Shock test, but can generate different failure modes due to the longer dwell time and gradual temperature change.

Condition: -65°C to 150°C

Pass Criteria: All units must pass min/max limits of the datasheet

Steady State Temperature Humidity Bias Life Test

- Purpose:** This is to check the performance of the device in humid environments. This test checks the integrity of the passivation, poor metal to plastic seal and contamination level during assembly and material compatibility.
- Condition:** 85%RH at 85°C with Vin=Vinmax
- Pass Criteria:** All units must pass min/max limits of the datasheet

Highly Accelerated Temperature and Humidity Stress Test

- Purpose:** This is an equivalent test to Steady State Temperature Humidity Bias Life test with different (higher) temperature stress condition.
- Condition:** 85%RH at 130°C with Vin=Vinmax
- Pass Criteria:** All units must pass min/max limits of the datasheet

Failure Rate Calculation

The failure rate is gauged by a Failures-In-Time (FIT) based upon accelerated stress data. The unit for FIT is failure per billion device hour.

$$FIT\ Rate = \frac{(\chi^2 / 2) \times 10^9}{EDH}$$

Where

χ^2 (Chi-Squared) is the goodness-of-fit test statistic at a specified level of confidence;

EDH= Equivalent Device Hours = AF × (Life test sample size) × (test duration);

AF= Acceleration Factor.

High Temperature Operating Life (HTOL) test is usually done under acceleration of temperature and voltage. The total number of failures from the stress test determines the chi-squared factor.

$$AF = AF_T \times AF_V$$

The Temperature Acceleration Factor AF_T :

$$AF_T = \exp\left(\frac{E_a}{K} \left(\frac{1}{T_{J(Use)}} - \frac{1}{T_{J(stress)}} \right)\right)$$

$T_{J(Use)}$ = Junction temp under typical operating conditions;

$T_{J(stress)}$ = Junction temp under accelerated test conditions;

E_a is Activation energy=0.7eV;

K =Boltzmann's constant=8.62×10⁻⁵ eV/K.

The voltage Acceleration Factor AF_V :

$$AF_V = e^{\beta \times [V_{stress} - V_{use}]}$$

V_{use} = Gate voltage under typical operating conditions;

V_{stress} = Gate voltage under accelerated test conditions;

β = Voltage acceleration factor (in 1/Volts) and specified by technology.

Note: For calculation in the report, $AF_V = 1$ for simplicity.

MTBF (Mean Time Between Failure) equals to 10⁹/FIT (in hours).