

## 1. Introduction


All plastic integrated-circuit packages have a tendency to absorb moisture. During surface-mount assembly, this moisture can vaporize when subjected to the heat associated with solder reflow operations. Vaporization creates internal stresses that can cause the plastic molding compound to crack. This cracking process is commonly referred to as the “popcorn effect.”

Cracks in the plastic molding may cause internal damage or may allow contamination to penetrate to the die, which can reduce the reliability of the semiconductor device.

Since plastic packages absorb moisture, care must be taken to prevent exposure to humid conditions greater than 10% RH for extended periods of time prior to surface mount reflow processing. If exposed to excessive moisture, the devices should be baked to remove moisture prior to solder reflow operations.

All MPS surface mount ICs have a moisture sensitivity level and peak reflow classification. This information is displayed on the reel, MBB and box packing.

The figure below show an example of the labels.



## 2. Definitions

### Dry Pack

Dry pack consists of desiccant material and a humidity indicator card (HIC) sealed with the surface mount device (SMD) packages inside a moisture barrier bag (MBB).



## Moisture Sensitivity Technical Note

### Floor Life

The allowable time period between removals of moisture-sensitive devices from a moisture-barrier bag, dry storage, or dry bake and the soldering (surface mount) process.

### Shelf Life

The minimum time that a dry-packed, moisture-sensitive device can be stored in an unopened moisture barrier bag (MBB) such that a specified interior bag ambient humidity is not exceeded.

### 3. Dry Packing Requirements

- a) Dry-packing requirements for the various moisture sensitivity levels are shown in Table 1 below.

**Table 1 Dry Packing Requirements**

MSL Level	Dry Before Bag	MBB With HIC	Desiccant	MSID Label	Caution Label
1	Optional	Optional	Optional	Not Required	Not Required if classified at 220 - 225 °C [428 - 437 °F] Required* if classified at other than 220 - 225 °C [428 - 437 °F]
2	Optional	Required	Required	Required	Required
2a-5a	Required	Required	Required	Required	Required
6	Optional	Optional	Optional	Required	Required

\*A "Caution" label is not required if level and reflow temperature are given, in human readable form, on the barcode label attached to the lowest level shipping container.

- b) The floor life of SMDs will be modified by environmental conditions other than 30 °C/60% RH. Please refer to below table.

**Table 2 Moisture Classification Level and Floor Life**

Moisture Sensitivity Level	Floor Life (out of bag) at factory ambient ≤30 °C/60% RH or as stated
1	Unlimited at ≤30 °C/85% RH
2	1 year
2a	4 weeks
3	168 hours
4	72 hours
5	48 hours
5a	24 hours
6	Mandatory bake before use. After bake, must be reflowed within the time limit specified on the label.



## Moisture Sensitivity Technical Note

### c) Drying of SMD Devices

Drying Requirements - Levels 2 - 5a

SMD devices classified at Levels 2 through 5a that exceed floor life may be adequately dried by baking according to Table 3 (for rebake prior to reflow) or Table 4 (for drying prior to dry packing).

**Table 3 Reference Conditions for Drying Mounted or Unmounted SMD Packages**  
(User Bake: Floor life begins counting at time = 0 after bake)

Package Body	Level	Bake @ 125 °C +10/-0 °C		Bake @ 90 °C +8/-0 °C ≤5% RH		Bake @ 40 °C +5/-0 °C ≤5% RH	
		Exceeding Floor Life by >72 h	Exceeding Floor Life by ≤72 h	Exceeding Floor Life by >72 h	Exceeding Floor Life by ≤72 h	Exceeding Floor Life by >72 h	Exceeding Floor Life by ≤72 h
Thickness ≤1.4 mm	2	5 hours	3 hours	17 hours	11 hours	8 days	5 days
	2a	7 hours	5 hours	23 hours	13 hours	9 days	7 days
	3	9 hours	7 hours	33 hours	23 hours	13 days	9 days
	4	11 hours	7 hours	37 hours	23 hours	15 days	9 days
	5	12 hours	7 hours	41 hours	24 hours	17 days	10 days
	5a	16 hours	10 hours	54 hours	24 hours	22 days	10 days
Thickness >1.4 mm ≤2.0 mm	2	18 hours	15 hours	63 hours	2 days	25days	20 days
	2a	21 hours	16 hours	3 days	2 days	29 days	22 days
	3	27 hours	17 hours	4 days	2 days	37 days	23 days
	4	34 hours	20 hours	5 days	3 days	47 days	28 days
	5	40 hours	25 hours	6 days	4 days	57 days	35 days
	5a	48 hours	40 hours	8 days	6 days	79 days	56 days
Thickness >2.0 mm ≤4.5 mm	2	48 hours	48 hours	10 days	7 days	79 days	67 days
	2a	48 hours	48 hours	10 days	7 days	79 days	67 days
	3	48 hours	48 hours	10 days	8 days	79 days	67 days
	4	48 hours	48 hours	10 days	10 days	79 days	67 days
	5	48 hours	48 hours	10 days	10 days	79 days	67 days
	5a	48 hours	48 hours	10 days	10 days	79 days	67 days
BGA package >17 mm x 17 mm or any stacked die package	2-5a	96 hours	As above per package thickness and moisture level	Not applicable	As above per package thickness and moisture level	Not applicable	As above per package thickness and moisture level
		(See Note 2)					



## Moisture Sensitivity Technical Note

**Table 4 Default Baking Times Used Prior to Dry-Pack that were Exposed to Conditions  $\leq 60\%$  RH (MET = 24 h)**

Package Body Thickness	Level	Bake @ 125 °C +10/-0 °C	Bake @ 150 °C +10/-0 °C
$\leq 1.4$ mm	2	7 hours	3 hours
	2a	8 hours	4 hours
	3	16 hours	8 hours
	4	21 hours	10 hours
	5	24 hours	12 hours
	5a	28 hours	14 hours
$> 1.4$ mm $\leq 2.0$ mm	2	18 hours	9 hours
	2a	23 hours	11 hours
	3	43 hours	21 hours
	4	48 hours	24 hours
	5	48 hours	24 hours
	5a	48 hours	24 hours
$> 2.0$ mm $\leq 4.5$ mm	2	48 hours	24 hours
	2a	48 hours	24 hours
	3	48 hours	24 hours
	4	48 hours	24 hours
	5	48 hours	24 hours
	5a	48 hours	24 hours

Note 1: If baking of packages  $> 4.5$  mm thick is required, see appendix B in IPC/JEDEC J-SDT-033.

#### 4. Shelf life

MPS warrants the shelf life of its analog IC devices for two (2) years based on production date code, assuming the integrity of the seal has not been compromised during that time period and consider to store in environment of  $< 40$  °C/90% RH.

Please see MPS International Ltd. Standard Terms and Conditions for other warranties applied to its products.

### 5. MPS Recommended IR Reflow Temperature Profile

The profile meets IPC/JEDEC J-STD-020 spec




Table:  $T_p$  for Pb-Free Process

Package Thickness	Volume $\text{mm}^3$ <350	Volume $\text{mm}^3$ 350 - 2000	Volume $\text{mm}^3$ >2000
<1.6 mm	$\leq 260^\circ\text{C}$	$\leq 260^\circ\text{C}$	$\leq 260^\circ\text{C}$
1.6 mm - 2.5 mm	$\leq 260^\circ\text{C}$	$\leq 250^\circ\text{C}$	$\leq 245^\circ\text{C}$
>2.5 mm	$\leq 250^\circ\text{C}$	$\leq 245^\circ\text{C}$	$\leq 245^\circ\text{C}$

### 6. Reference Docs

**IPC/JEDEC J-STD-033** Handling, Packing, Shipping and Use of Moisture/Reflow Sensitive Surface Mount Devices

**IPC/JEDEC J-STD-020E** Moisture/Reflow Sensitivity Classification for Nonhermetic Surface Mount Devices