EV3422-G-00A

6.5A, 600kHz Synchronous Step-up Converter with Output Disconnect Evaluation Board

DESCRIPTION

EV3422-G-00A Evaluation Board is designed to demonstrate the capability of MP3422. MP3422 is a high-efficiency, synchronous, current-mode, step-up converter with output disconnect.

The MP3422 can provide inrush current limiting and output short-circuit protection. It can work with an input voltage as low as 2.5V. The integrated P-channel synchronous rectifier improves efficiency and eliminates the need for an external Schottky diode. The PMOS disconnects the output from the input when the part shuts down.

The 600kHz switching frequency allows for small external components, while the internal compensation and soft-start minimize the external component count. The MP3422 is available in 14-pin QFN 2mmx2mm package.

ELECTRICAL SPECIFICATION

Parameter	Symbol	Value	Units
Input Voltage	V_{IN}	2.8 – 4.2	V
Output Voltage	V_{OUT}	5	V
Output Current	I_{OUT}	0 – 2.5	A

FEATURES

- 2.5V to 5.5V Input Work Range
- 2.5V to 5.5V Output Range
- Internal Synchronous Rectifier
- 600kHz Fixed Frequency Switching
- >6.5A Switch Current Limit Capability
- 43uA Quiescent Current
- High Efficiency over Full Load Range
- Internal Soft-start and Compensation
- True Output Load Disconnect from Input
- OCP, SCP, OVP and OTP Protection
- Small QFN2x2-14 Package

APPLICATIONS

- Battery-Powered Products
- Personal Medical Devices
- Portable Media Players
- Wireless Peripherals
- Handheld Computers and Smart Phones

All MPS parts are lead-free and adhere to the RoHS directive. For MPS green status, please visit MPS website under Products, Quality Assurance page.

"MPS" and "The Future of Analog IC Technology", are Registered Trademarks of Monolithic Power Systems, Inc.

EV3422-G-00A EVALUATION BOARD

(L x W x H) 6.35cm x 6.35cm x 0.6cm

Board Number	MPS IC Number
EV3422-G-00A	MP3422GG



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2014 MPS. All Rights Reserved.

EVALUATION BOARD SCHEMATIC



Notes:

1) NC (PIN10) need short to VIN.

2) NC (PIN7) need float or connect to GND

3) It is strongly recommended control IC on/off through EN pin.

EV3422-G-00A BILL OF MATERIALS

Qty	Ref	Value	Description	Package	Manufacturer	Part Number
4	C1A, C1B, C2B, C2C	22μF	Ceramic Cap, 10V,X7R	1210	Murata	GRM32ER71A226KE20L
1	C2A	1μF	Ceramic Cap,10V,X5R	0603	Murata	GRM188R61A105KA61D
1	L1	1.5μH	RDC=6.6mΩ, IR=11A,Isat=14A,	SMD	Wurth	744311150
1	R1	787kΩ	Film Res,1%	0603	YAGEO	RC0603FR-07787KL
1	R2	150kΩ	Film Res,1%	0603	ROYAL	RL0603FR-07150KL
1	R3	100kΩ	Film Res,1%	0603	ROYAL	RL0603FR-07100KL
1	U1	MP3422	6.5A Synchronous Step-up Converter with Output Disconnect	QFN-14 2mmx2mm	MPS	MP3422GG

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2014 MPS. All Rights Reserved.

EVB TEST RESULTS

Performance waveforms are tested on the evaluation board.
V_{IN} = 3.3V, V_{OUT} = 5V, L = 1.5µH, T_A = 25ºC, unless otherwise noted.

Efficiency vs. Load Current



Case Temperature Rising vs. Load Current



Line Regulation



Load Regulation



Bode Plot
V_{IN} =2.8V, I_{OUT}=2.5A



Bode Plot
V_{IN} =4.2V, I_{OUT}=2.5A



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2014 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance waveforms are tested on the evaluation board.
V_{IN} = 3.3V, V_{OUT} = 5V, L = 1.5µH, T_A = 25ºC, unless otherwise noted.

Output Voltage Ripple
I_{OUT} = 0A



Output Voltage Ripple
I_{OUT} = 0.1A



Output Voltage Ripple
I_{OUT} = 2.5A



V_{IN} Startup
I_{OUT} = 0A



V_{IN} Startup
R_{LOAD} = 3.5Ω



V_{IN} Shutdown
I_{OUT} = 0.01A



V_{IN} Shutdown
R_{LOAD} = 3.5Ω



EN Startup
I_{OUT} = 0A



EN Startup
R_{LOAD} = 3.5Ω



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2014 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance waveforms are tested on the evaluation board.
V_{IN} = 3.3V, V_{OUT} = 5V, L = 1.5µH, T_A = 25ºC, unless otherwise noted.

EN Shutdown
I_{OUT} = 0.01A



EN Shutdown
R_{LOAD} = 3.5Ω



Load Transient Response
Load = 0.01A --> 1A @ 100mA/µs



Load Transient Response
Load = 1A --> 2A @ 100mA/µs



Short Circuit Entry
V_{IN}=4.2V, I_{OUT}=0.5A



Short Circuit Recovery
Recovers to 0.1A Load



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2014 MPS. All Rights Reserved.

PRINTED CIRCUIT BOARD LAYOUT



Figure 1—Top Silk Layer



Figure 2—Top Layer



Figure 3—Bottom Layer

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2014 MPS. All Rights Reserved.

QUICK START GUIDE

The output voltage of this board is set to 5V. The board layout accommodates most commonly used components.

1. Preset Power Supply to 2.8V ≤ V_{IN} ≤ 4.2V.
2. Turn Power Supply off.
3. Connect Power Supply terminals to:
    a. Positive (+): VIN
    b. Negative (–): GND
4. Connect Load to:
    a. Positive (+): VOUT
    b. Negative (–): GND
5. Turn Power Supply on after making connections.
6. The MP3422 is enabled on the evaluation board once VIN is applied.
7. The output voltage VOUT can be changed by varying R2. Calculate the new value using the formula:

$$V_{out} = V_{FB} \times \frac{R1 + R2}{R2}$$

Where V_{FB} = 0.807V and R1=787kΩ.

8. To use the Enable function, apply a digital input to the EN pin. Drive EN higher than 1.2V to turn on MP3422 or less than 0.4V to turn it off.

NOTICE: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2014 MPS. All Rights Reserved.