EV8773EN-00A

Monolithic 3A, 23V, 500kHz Synchronous Step-down Converter Evaluation Board

The Future of Analog IC Technology

DESCRIPTION

The EV8773EN-00A is an evaluation board for the MP8773EN, a monolithic synchronous buck regulator.

This EV board can deliver 3A continuous load current over an operating input voltage 4.5V to 23V. High efficiency power conversion is achieved through the use of synchronous rectification techniques.

Current mode control is implemented, which provides fast transient response and cycle-by-cycle current limiting.

This EV board can be turned on or shut down via a remote ON/OFF input that is referenced to ground. This input is compatible with popular logic devices.

FEATURES

- Wide 4.5V to 23V Operating Input Range
- 3A Output Current
- Low RDS(ON) Internal Power MOSFETs
- Proprietary Switching Loss Reduction Technique
- Fixed 500kHz Switching Frequency
- Internal Compensation
- OCP Protection and Thermal Shutdown
- Output Adjustable from 0.8V
- Available in SOIC8E Package

APPLICATIONS

- Notebook Systems and I/O Power
- Networking Systems
- Digital Set Top Boxes
- Personal Video Recorders
- Flat Panel Television and Monitors
- Distributed Power Systems

ELECTRICAL SPECIFICATIONS

Parameter	Symbol	Value	Units
Input Voltage	V_{IN}	4.5 – 23	V
Output Voltage	V_{OUT}	3.3	V
Output Current	I_{OUT}	3	A

"MPS" and "The Future of Analog IC Technology" are Registered Trademarks of Monolithic Power Systems, Inc.

EV8773EN-00A EVALUATION BOARD

(L x W x H) 2.5" X 2.5" X 0.05"
(63mm x 63mm x 1.3mm)

Board Number	MPS IC Number
EV8773EN-00A	MP8773EN

Efficiency



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2013 MPS. All Rights Reserved.

EVALUATION BOARD SCHEMATIC



EV8773EN-00A BILL OF MATERIALS

Qty	Ref	Value	Description	Package	Manufacturer	Manufacturer P/N
1	C1A	22µF	Ceramic Cap, 25V, X7R	1210	Murata	GRM32ER71E226KE15L
5	C1B,C1C, C2D,C3,C4	0.1µF	Ceramic Cap, 25V, X7R	0603	Murata	GRM188R71E104KA01D
2	C2A,C2B	22µF	Ceramic Cap, 6.3V, X5R	1210	Murata	GRM32DR60J226KA01L
2	C2C,C5	NS				
1	C6	82pF	Ceramic Cap, 50V, X7R	0603	TDK	C1608COG1H820J
1	R1	6.34k	Film Res, 1%	0603	Yageo	RC0603FR-076K34L
1	R2	2k	Film Res, 1%	0603	Yageo	RC0603FR-072KL
1	R3	100k	Film Res, 1%	0603	Yageo	RC0603FR-07100KL
1	R4	33.2k	Film Res, 1%	0603	Yageo	RC0603FR-0733K2L
1	R5	10k	Film Res, 1%	0603	Yageo	RC0603FR-0710kL
1	R6	0	Film Res, 5%	0603	Yageo	RC0603JR-070RL
1	R7	3k	Film Res, 1%	0603	Yageo	RC0603FR-073KL
2	R8,R9	10	Film Res, 1%	0603	Yageo	RC0603FR-0710RL
1	L1	1.8µH	DCR=7.6mΩ		TOKO	D104C-919AS-1R8N
1	D1	NS				
1	U1		Step-Down Converter	SO-8	MPS	MP8773EN

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2013 MPS. All Rights Reserved.

PRINTED CIRCUIT BOARD LAYOUT



Figure 1—Top Silk Layer



Figure 2—Top Layer



Figure 3—Inner Layer 1



Figure 4— Inner Layer 2



Figure 5—Bottom Layer

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2013 MPS. All Rights Reserved.

QUICK START GUIDE

1. Connect the positive and negative terminals of the load to the VOUT and GND pins, respectively.
2. Preset the power supply output between 4.5V and 23V, and then turn off the power supply.
3. Connect the positive and negative terminals of the power supply output to the VIN and GND pins, respectively.
4. Turn the power supply on. The MP8773 will automatically startup.
5. To use the Enable function, apply a digital input to the EN pin. Drive EN higher than 2V to turn on the regulator or less than 0.4V to turn it off.
6. Use R1 and R2 to set the output voltage with VFB = 0.8V. Follow the Application Information section in the device datasheet to select the proper value of R1, R2, inductor and output capacitor values when output voltage is changed.

NOTICE: The information in this document is subject to change without notice. Users should warrant and guarantee that third party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2013 MPS. All Rights Reserved.