EVM3650C-QW-00A

17V, 6A, 1.2MHz, Ultra-Thin, Synchronous, Step-Down Power Module Evaluation Board

DESCRIPTION

The EVM3650C-QW-00A is an evaluation board designed to demonstrate the capabilities of the MPM3650C, a fully integrated, high-frequency, synchronous, rectified, step-down power module with an internal inductor. It offers a highly compact solution to achieve 6A of continuous output current (I_{OUT}) across a wide 2.75V to 17V input voltage (V_{IN}) range, with excellent load and line regulation. The MPM3650C offers synchronous operation for high efficiency across the I_{OUT} load range.

Constant-on-time (COT) control enables ultra-fast transient response and easy loop design, as well as very tight output regulation.

Full protection features include short-circuit protection (SCP), over-current protection (OCP), under-voltage protection (UVP), and thermal shutdown.

The MPM3650C is available in a QFN-24 (4mmx6mmx1.6mm) package.

ELECTRICAL SPECIFICATIONS

Parameter	Symbol	Value	Units
Input voltage	V_{IN}	2.75 to 17	V
Output voltage	V_{OUT}	1	V
Output current	I_{OUT}	6	A

FEATURES

- Wide 2.75V to 17V Operating Input Voltage (V_{IN}) Range
- Output Current (I_{OUT}) for Different Output Voltage (V_{OUT}) Ranges:
  - 6A I_{OUT} for 0.6V to 1.8V V_{OUT}
  - 5A I_{OUT} for 1.8V to 3.3V V_{OUT}
- 3.3V Maximum V_{OUT}
- Forced Continuous Conduction Mode (CCM) for Low Output Voltage Ripple
- High-Efficiency Synchronous Operation
- Supports Pre-Biased Start-Up
- Fixed 1200kHz Switching Frequency (f_{SW})
- Externally Configurable Soft-Start Time (t_{SS})
- Enable (EN) and Power Good (PG) for Power Sequencing
- Over-Current Protection (OVP) with Hiccup Mode
- Thermal Shutdown
- Available in a QFN-24 (4mmx6mmx1.6mm) Package

APPLICATIONS

- Field-Programmable Gate Array (FPGA) Power Systems
- Optical Modules
- Telecommunications
- Networking
- Industrial Equipment

All MPS parts are lead-free, halogen-free, and adhere to the RoHS directive. For MPS green status, please visit the MPS website under Quality Assurance. “MPS”, the MPS logo, and “Simple, Easy Solutions” are trademarks of Monolithic Power Systems, Inc. or its subsidiaries.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVM3650C-QW-00A EVALUATION BOARD



LxWxH (63.5mmx63.5mmx1.6mm)

Board Number	MPS IC Number
EVM3650C-QW-00A	MPM3650CGQY



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

QUICK START GUIDE

1. Preset the power supply between 2.75V and 17V.
2. Turn off the power supply.
3. Connect the power supply terminals to:
   a. Positive (+): VIN
   b. Negative (-): GND
4. Connect load terminals (≤6A) to:
   a. Positive (+): VOUT
   b. Negative (-): GND
5. After making the connections, turn on the power supply. The board should start up automatically.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVALUATION BOARD SCHEMATIC



Figure 1: Evaluation Board Schematic

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVM3650C-QW-00A BILL OF MATERIALS

Qty	Ref	Value	Description	Package	Manufacturer	Manufacturer PN
6	C1, C2, C4, C5, C20, C7	22µF	Ceramic capacitor, 25V, X5R	0805	Murata	GRM21BR61E226ME44L
4	C3, C8, C11, C19	0.1µF	Ceramic capacitor, 25V, X5R	0402	Wurth	885012105018
1	C10	1µF	Ceramic capacitor, 25V, X5R	0402	Murata	GRM155R61E105KA12D
1	C9	39pF	Ceramic capacitor, 50V, C0G	0402	Murata	GRM1555C1H390JA01D
1	R1	499kΩ	Film resistor, 1%	0402	Yageo	RC0402FR-07499KL
1	R4	100kΩ	Film resistor, 1%	0402	Yageo	RC0402FR-07100KL
2	R7, R6	0Ω	Film resistor, 1%	0402	Yageo	RC0402FR-070RL
1	R3	20kΩ	Film resistor, 1%	0402	Yageo	RC0402FR-0720KL
1	R5	30kΩ	Film resistor, 1%	0402	Yageo	RC0402FR-0730KL
1	EN	2.54mm	3-pin, single-row, straight socket header	DIP	Wurth	61300311821
0	V_{OUT} ripple	NS				
5	VIN, VEMI, GND, GND, VOUT	Φ2.0	2 copper pins	DIP	Custom	
4	EN, GND, VCC, PG	Φ1.0	1 copper pin	DIP	Custom	
1	U1	MPM3650C	Step-down power module, 17V, 6A, 1.2MHz	QFN-24 (4mmx 6mm)	MPS	MPM3650CGQW

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 1V, T_A = 25°C, unless otherwise noted.

Thermal Derating

V_{OUT} = 1V, no wind



Efficiency vs. Load Current

V_{OUT} = 1V



Line Regulation

V_{OUT} = 1V



Load Regulation

V_{OUT} = 1V



Case Temperature vs. Load Current

V_{OUT} = 1V, T_A = 15°C



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 1V, T_A = 25°C, unless otherwise noted.

V_{OUT} Ripple
I_{OUT} = 0A



V_{OUT} Ripple
I_{OUT} = 6A



Load Transient
I_{OUT} = 0A to 3A



Load Transient
I_{OUT} = 3A to 6A



Start-Up through VIN
I_{OUT} = 0A



Start-Up through VIN
I_{OUT} = 6A



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 1V, T_A = 25°C, unless otherwise noted.

Shutdown through VIN

I_{OUT} = 0A



Shutdown through VIN

I_{OUT} = 6A



Start-Up through EN

I_{OUT} = 0A



Start-Up through EN

I_{OUT} = 6A



Shutdown through EN

I_{OUT} = 0A



Shutdown through EN

I_{OUT} = 6A



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 1V, T_A = 25°C, unless otherwise noted.

SCP Steady State



SCP Entry and Recovery



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PCB LAYOUT



Figure 2: Top Silk



Figure 3: Top Layer



Figure 4: Mid-Layer 1



Figure 5: Mid-Layer 2



Figure 6: Bottom Layer



Figure 7: Bottom Silk

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	08/05/2021	Initial Release	-

Notice: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.