EVM3824C-PA-01A

6V, 2A, Ultra-Small, Low-Noise, Single-Ouput Step-Down Power Module Evaluation Board

DESCRIPTION

The EVM3824C-PA-01A is an evaluation board designed to demonstrate the capabilities of the MPM3824C, a high-efficiency, low-noise, single-output, step-down power module. The MPM3824C has a 1.25MHz fixed switching frequency (f_{SW}). The device's high f_{SW} and constant-on-time control (COT) control provide fast transient response, high efficiency, and easy loop stabilization. The MPM3824C is available in an ultra-small LGA-14 (2.5mmx2.5mmx1.2mm) package. For more information, refer to the MPM3824C datasheet.

PERFORMANCE SUMMARY

Specifications are at T_A = 25°C, unless otherwise noted.

Parameters	Conditions	Value
Input voltage (V_{IN}) range		2.75V to 6V
Output voltage (V_{OUT})	V_{IN} = 2.75V to 6V, I_{OUT} = 0A to 2A	V_{OUT} = 1.2V
Maximum output current (I_{OUT})	V_{IN} = 2.75V to 6V	2A
Typical efficiency	V_{IN} = 5V, V_{OUT} = 1.2V, I_{OUT} = 2A	85.3%
Peak efficiency	V_{IN} = 5V, V_{OUT} = 1.2V, I_{OUT} = 1A	86.7%
Switching frequency (f_{SW})		1.25MHz

EVALUATION BOARD



LxWxH (5.1cmx5.1cmx1.6cm)

Board Number	MPS IC Number
EVM3824C-PA-01A	MPM3824CGPA

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

QUICK START GUIDE

The EVM3824C-PA-01A is easy to set up to evaluate the MPM3824C's performance. For proper measurement, equipment, and set-up, refer to Figure 1 and follow the guidelines below:

1. Preset the power supply between 2.75V and 6V (1), then turn off the power supply.
2. Connect the power supply terminals to:
   a. Positive (+): VIN
   b. Negative (-): GND
3. Connect the load terminals to: (2)
   a. Positive (+): VOUT
   b. Negative (-): GND
4. After making the connections, turn on the power supply. The board should start up automatically.
5. Check that the set output voltage (V_{OUT}) is flowing between VO+S and VO-S.
6. Once V_{OUT} is established, adjust the load within its operating range, then measure the efficiency, output voltage ripple (ΔV_{OUT}), input voltage ripple (ΔV_{IN}), and other parameters. (3)

Notes:

1) The input voltage (V_{IN}) should not exceed 6V.
2) The load is initially no load by default.
3) Do not use the oscilloscope's ground lead to measure ΔV_{OUT} or ΔV_{IN}.



Figure 1: Measurement Equipment Set-Up

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVALUATION BOARD SCHEMATIC



Figure 2: Evaluation Board Schematic

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVM3824C-PA-01A BILL OF MATERIALS

Qty	Ref	Value	Description	Package	Manufacturer	Manufacturer PN
1	C1A	0.1µF	Ceramic capacitor, 10V, X7R	0402	TDK	C1005X7R1C104KT000E
2	C1B, C2A	22µF	Ceramic capacitor, 10V, X7R	0805	TDK	C2012X7R1C226MT000N
1	CFF	10pF	Ceramic capacitor, 10V, X7R	0402	TDK	C1005X7R1C100KT000E
2	R1, R2	200kΩ	Film resistor, 1%	0402	Yageo	RC0402FR-07200KL
2	R3, R4	100kΩ	Film resistor, 1%	0402	Yageo	RC0603FR-07100KL
1	R6	0Ω	Film resistor, 1%	2512	Yageo	RC2512FK-070RL
6	VIN_S, VO_S, GND_S, GND_S, EN, PG	φ1	φ1 copper pin	DIP	Custom	
4	VIN, VO, GND, GND	Φ2	Φ2 copper pin	DIP	Custom	
1	U1	MPM3824C	Step-down power module, 6V, 2A	LGA-14 (2.5mmx 2.5mm)	MPS	MPM3824CGPA

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS

Performance curves and waveforms are tested on the evaluation board. V_{IN} = 5V, V_{OUT} = 1.2V, T_A = 25°C, unless otherwise noted.

Efficiency vs. Load Current

V_{IN} = 5V



Thermal Performance

T_A = 28°C, I_{OUT} = 2A, t_{CASE} = 52.7°C, no forced airflow



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board. V_{IN} = 5V, V_{OUT} = 1.2V, T_A = 25°C, unless otherwise noted.

Steady State

V_{IN} = 5V, V_{OUT} = 1.2V, I_{OUT} = 0A



1µs/div.

Steady State

V_{IN} = 5V, V_{OUT} = 1.2V, I_{OUT} = 2A



1µs/div.

Load Transient

V_{IN} = 5V, V_{OUT} = 1.2V, I_{OUT} = 0A to 2A, 2.5A/µs, e-load



800µs/div.

Load Transient

V_{IN} = 5V, V_{OUT} = 1.2V, I_{OUT} = 1A to 2A, 2.5A/µs, e-load



800µs/div.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PCB LAYOUT



Figure 3: Top Silk



Figure 4: Top Layer



Figure 5: Mid-Layer 1



Figure 6: Mid-Layer 2

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PCB LAYOUT *(continued)*



Figure 7: Bottom Layer



Figure 8: Bottom Silk

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	09/09/2021	Initial Release	-

Notice: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.