EVQ4334-D-4000-00A

36V, 4A, Low Quiescent Current, Synchronous Step-Down Converter Evaluation Board in QFN-12 (2mmx3mm), AEC-Q100 Qualified

DESCRIPTION

The EVQ4334-D-4000-00A is an evaluation board designed to demonstrate the capabilities of the MPQ4334GDE-4000-AEC1, a configurable-frequency (200kHz to 2.5MHz), synchronous, step-down switching converter with an integrated, internal high-side MOSFET (HS-FET) and low-side MOSFET (LS-FET).

The MPQ4334GDE-4000-AEC1 provides up to 4A of highly efficient output current (I_{OUT}) with peak current mode control. The wide 3V to 36V input voltage (V_{IN}) range and 40V load dump tolerance accommodates a variety of step-down applications in automotive input environments. A 0.5µA shutdown mode quiescent current (I_Q) allows the device to be used in battery-powered applications.

High power conversion efficiency across a wide load range is achieved by scaling down the switching frequency (f_{SW}) under light-load conditions to reduce switching and gate driver losses.

An open-drain power good (PG) signal indicates whether the output voltage (V_{OUT}) is within 94.5% to 105.5% of its nominal voltage.

Frequency foldback helps prevent inductor current (I_L) runaway during start-up. Thermal shutdown provides reliable, fault-tolerant operation.

High duty cycle and low-dropout (LDO) mode are provided for automotive cold-crank conditions.

The EVQ4334-D-4000-00A is a fully assembled and tested evaluation board. The MPQ4334GDE-4000-AEC1 is available in a QFN-12 (2mmx3mm) package with wettable flanks, and is AEC-Q100 qualified.

PERFORMANCE SUMMARY

Specifications are at T_A = 25°C, unless otherwise noted.

Parameters	Conditions	Value
Input voltage (V_{IN}) range		3V to 36V
Output voltage (V_{OUT})	V_{IN} = 6V to 36V, I_{OUT} = 0A to 4A	5V
Maximum output current (I_{OUT})	V_{IN} = 3V to 36V	4A
Typical efficiency	V_{IN} = 12V, V_{OUT} = 5V, I_{OUT} = 4A	91.5%
Peak efficiency	V_{IN} = 8V, V_{OUT} = 5V, I_{OUT} = 1A	96%
Switching frequency (f_{SW})		2.2MHz

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVQ4334-D-4000-00A EVALUATION BOARD

LxWxH (8.3cmx8.3cmx1cm)

Board Number	MPS IC Number
EVQ4334-D-4000-00A	MPQ4334GDE-4000-AEC1

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

QUICK START GUIDE

The EVQ4334-D-4000-00A evaluation board is easy to set up and use to evaluate the performance of the MPQ4334. For proper measurement equipment set-up, refer to Figure 2 on page 4 and follow the steps below:

1. Preset the power supply (V_{IN}) to be between 6V and 36V, then turn off the power supply.
2. Set the load current between 0A and 4A. Electronic loads represent a negative impedance to the regulator, and setting the current too high can trigger hiccup mode.
3. If longer cables (>0.5m total) are used between the source and the evaluation board, place a damping capacitor at the input terminals (especially when V_{IN} ≥ 24V).
4. Connect the power supply terminals to:
   a. Positive (+): VEMI
   b. Negative (-): GND
5. Connect the load terminals to:
   a. Positive (+): VOUT
   b. Negative (-): GND
6. After making the connections, turn on the power supply. The board should start up automatically.
7. To use the enable (EN) function, apply a digital input to the EN pin. Pull EN above 1.02V to turn the regulator on; pull EN below 0.85V to turn it off. If the enable function is not used, EN can be connected directly to VIN.
8. Connect a resistor between the FREQ and GND pins to set the internal switching frequency (f_{SW}).
9. Set the output voltage (V_{OUT}) using the external resistor divider (see Figure 1).



Figure 1: Feedback Divider Network with Adjustable Output

R5 should be 100kΩ. Then R6 can be calculated with Equation (1):

$$R_6 = \frac{R_5}{\frac{V_{OUT}}{0.8V} - 1} \quad (1)$$

Refer to the Application Information section in the MPQ4334 datasheet to calculate the inductance (L) and output capacitance (C_{OUT}) for different output voltages.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.



Figure 2: Measurement Equipment Set-Up

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVALUATION BOARD SCHEMATIC



R3||R9 (kΩ)	f_{SW} (kHz)
48.7	415
41.2	470
19.1	1000
8.45	2200
7.87	2500

V_{OUT} (V)	R5 (kΩ)	R6||R8 (kΩ)
5	100 (1%)	19.1 (1%)
3.8	100 (1%)	26.7 (1%)
3.3	100 (1%)	31.6 (1%)
2.5	100 (1%)	47 (1%)
1.8	100 (1%)	80 (1%)
1	24.9 (1%)	100 (1%)

Figure 3: Evaluation Board Schematic

PACKAGE REFERENCE



QFN-12 (2mmx3mm)

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVQ4334-D-4000-00A BILL OF MATERIALS

Qty	Ref	Value	Description	Package	Manufacturer	Manufacturer PN
1	CIN1	1nF	Ceramic capacitor, 50V, X7R	0603	Murata	GRM216R71H102KA01
1	CIN2	10nF	Ceramic capacitor, 50V, X7R	0603	Murata	GRM188R71H103KA01D
2	CIN3, CIN4	2.2µF	Ceramic capacitor, 50V, X7R	0805	Murata	GRM21BD72A225KE01L
1	CIN5	22µF	Aluminum polymer capacitor, 50V	SMD	Panasonic	EEHZC1H220P
2	C1A, C1B	4.7µF	Ceramic capacitor, 50V, X7S	1206	Murata	GRM31CR71H475KA12L
3	C1C, C1D, C3	100nF	Ceramic capacitor, 50V, X7R	0603	Murata	GRM188R71H104KA93D
2	C2A, C2B	22µF	Ceramic capacitor, 16V, X7R	1210	Murata	GRM32ER71C226KE18L
1	C5	22pF	Ceramic capacitor, 100V, C0G	0603	Murata	GCM1885C2A220JA16D
1	C4	1µF	Ceramic capacitor, 25V, X7R	0603	Murata	GCM188R71E105KA64D
1	FB1	3A	Magnetic bead	0805	Wurth	742792063
1	L1	1µH	Inductor, 14.6mΩ, 9.6A	SMD	Coilcraft	XEL4020-102MEB
1	L2	2.2µH	Inductor, 22.1mΩ, 5.8A	SMD	Coilcraft	XEL4030-222MEB
4	R1, R5, R7, R2	100kΩ	Film resistor, 1%	0603	Yageo	RC0603FR-07100KL
1	R3	48.7kΩ	Film resistor, 1%	0603	Yageo	RC0603FR-0748K7L
1	R4	0Ω	Film resistor, 5%	0603	Yageo	RC0603JR-070RL
1	R6	31.6kΩ	Film resistor, 1%	0603	Yageo	RC0603FR-0731K6L
1	R8	47.5kΩ	Film resistor, 1%	0603	Yageo	RC0603FR-0747K5L
1	R9	10.2kΩ	Film resistor, 1%	0603	Yageo	RC0603FR-0710K2L
3	J1, J2, JP3	2.54mm	Test pin, 3-pin	DIP	Any	
4	VEMI, GND, VOUT, GND	2mm	Golden pin	DIP	Custom (1)	
5	SYNCIN, GND, PG, EN, GND	1mm	Golden pin	DIP	Custom (1)	
1	U1	MPQ4334-4000-AEC1	4A, low-I_Q, synchronous step-down converter, AEC-Q100 qualified	QFN-12 (2mmx 3mm)	MPS	MPQ4334GDE-4000-AEC1

Note:

1) MPS custom-produces these pins. Contact an MPS FAE for more information.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVB TEST RESULTS

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 5V, T_A = 25°C, unless otherwise noted.

Input Current vs. Load Current for 4000 Version

R_{FB1} = 100kΩ, R_{FB2} = 19.1kΩ, DCR = 22.1mΩ



Efficiency vs. Load Current for 4000 Version

R_{FB1} = 100kΩ, R_{FB2} = 19.1kΩ, DCR = 22.1mΩ



Efficiency vs. Load Current for 4000 Version

DCR = 22.1mΩ



Efficiency vs. Load Current for 4000 Version

DCR = 22.1mΩ



Load Regulation for 4000 Version

DCR = 22.1mΩ



Line Regulation for 4000 Version

DCR = 22.1mΩ



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 5V, T_A = 25°C, unless otherwise noted.

Case Temperature Rise

V_{OUT} = 5V, f_{SW} = 2.2MHz, QFN-12 (2mmx3mm)



Low-Dropout Mode

V_{OUT} = 5V, f_{SW} = 2.2MHz



Switching Frequency vs. Frequency Resistor

R_{FREQ} = 7kΩ to 19kΩ



Switching Frequency vs. Frequency Resistor

R_{FREQ} = 19kΩ to 40kΩ



Switching Frequency vs. Frequency Resistor

R_{FREQ} = 40kΩ to 100kΩ



Switching Frequency vs. Load Current for 4000 Version

V_{OUT} = 5V



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 5V, T_A = 25°C, unless otherwise noted.

Thermal Performance

I_{OUT} = 2A, no forced airflow, T_{CASE} = 41°C



Thermal Performance

I_{OUT} = 4A, no forced airflow, T_{CASE} = 80.8°C



Bode Plot

I_{OUT} = 1A, PM = 66.8°, GM = 14.4dB



Bode Plot

I_{OUT} = 4A, PM = 71.7°, GM = 16.8dB



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 5V, T_A = 25°C, unless otherwise noted.

CISPR 25 Class 5 Peak Conducted Emissions

150kHz to 108MHz



CISPR 25 Class 5 Average Conducted Emissions

150kHz to 108MHz



CISPR 25 Class 5 Peak Radiated Emissions

150kHz to 30MHz



CISPR 25 Class 5 Average Radiated Emissions

150kHz to 30MHz



CISPR 25 Class 5 Peak Radiated Emissions

Horizontal, 30MHz to 1GHz



CISPR 25 Class 5 Average Radiated Emissions

Horizontal, 30MHz to 1GHz



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 5V, T_A = 25°C, unless otherwise noted.

CISPR 25 Class 5 Peak Radiated Emissions

Vertical, 30MHz to 1GHz



CISPR 25 Class 5 Average Radiated Emissions

Vertical, 30MHz to 1GHz



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 5V, T_A = 25°C, unless otherwise noted.

Steady State
I_{OUT} = 0A



Steady State
I_{OUT} = 4A



Start-Up through VIN
I_{OUT} = 0A



Start-Up through VIN
I_{OUT} = 4A



Shutdown through VIN
I_{OUT} = 0A



Shutdown through VIN
I_{OUT} = 4A



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 5V, T_A = 25°C, unless otherwise noted.

Start-Up through EN

I_{OUT} = 0A



Start-Up through EN

I_{OUT} = 4A



Shutdown through EN

I_{OUT} = 0A



Shutdown through EN

I_{OUT} = 4A



PG Start-Up through VIN

I_{OUT} = 0A



PG Start-Up through VIN

I_{OUT} = 4A



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 5V, T_A = 25°C, unless otherwise noted.

PG Shutdown through VIN
I_{OUT} = 0A



PG Shutdown through VIN
I_{OUT} = 4A



PG Start-Up through EN
I_{OUT} = 0A



PG Start-Up through EN
I_{OUT} = 4A



PG Shutdown through EN
I_{OUT} = 0A



PG Shutdown through EN
I_{OUT} = 4A



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 5V, T_A = 25°C, unless otherwise noted.

Low-Dropout Mode

I_{OUT} = 0A, V_{IN} = 3.3V



Low-Dropout Mode

I_{OUT} = 4A, V_{IN} = 3.3V



SCP Entry

I_{OUT} = 0A



SCP Entry

I_{OUT} = 4A



SCP Recovery

I_{OUT} = 0A



SCP Recovery

I_{OUT} = 4A



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board, V_{IN} = 12V, V_{OUT} = 5V, T_A = 25°C, unless otherwise noted.

SCP Steady State

I_{OUT} = 0A



Load Transient

I_{OUT} = 2A to 4A, 1.6A/µs



Load Dump

V_{IN} = 12V to 40V, I_{OUT} = 0A



Load Dump

V_{IN} = 12V to 40V, I_{OUT} = 4A



Cold Crank

I_{OUT} = 0A



Cold Crank

I_{OUT} = 4A



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance curves and waveforms are tested on the evaluation board. V_{IN} = 12V, V_{OUT} = 5V, T_A = 25°C, unless otherwise noted.

V_{IN} Ramping Down and Up

V_{IN} = 6V to 0V, 0.5V/min, I_{OUT} = 0A



V_{IN} Ramping Down and Up

V_{IN} = 6V to 0V, 0.5V/min, I_{OUT} = 4A



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

PCB LAYOUT (2)



Figure 4: Top Silk and Top Layer



Figure 5: Mid-Layer 1



Figure 6: Mid-Layer 2



Figure 7: Bottom Layer and Bottom Silk

Note:

2) The copper thickness is 2oz.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	5/29/2025	Initial Release	-

Notice: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.