EVQ5073-G-00A

5.5V, 2A, Programmable Current, Low $R_{DS(ON)}$ Load Switch, AEC-Q100 Qualified Evaluation Board

DESCRIPTION

The EVQ5073-G-00A is an evaluation board for the MPQ5073, a low $R_{DS(ON)}$ load switch with current limit. The MPQ5073 is a load switch that provides 2A of load protection, covering a 0.5V to 5.5V voltage range. With a small $R_{DS(ON)}$ in a tiny package, the MPQ5073 provides a highly efficient, space-saving solution in notebook, tablet, and other portable device applications.

The max load at the output (source) is current-limited. This is accomplished by utilizing a sense FET topology. The magnitude of the current limit is controlled by an external resistor from the ILIM pin to ground.

The EVQ5073-G-00A board can deliver a continuous 2A load current across a 0.5V to 5.5V operating input range.

ELECTRICAL SPECIFICATIONS

Parameter	Symbol	Value	Units
Input voltage (1)	V_{IN}	3 to 5.5	V
Output voltage	V_{OUT}	3 to 5.5	V
Output current	I_{OUT}	2	A

Note:

1) For specifications of lower voltage, please contact factory.

FEATURES

- Integrated 50mΩ Low $R_{DS(ON)}$ FETs
- Adjustable Start-Up Slew Rate
- Wide V_{IN} Range: 0.5V to 5.5V
- <1μA Shutdown Current
- Programmable 2.5A Current Limit Range
- Power Good Indicator
- Output Discharge function
- Enable Pin
- <200ns Short-Circuit Protection Response Time
- Thermal Protection
- Available in a Small, Space-Saving QFN-12 (2mmx2mm) Package

APPLICATIONS

- Notebook and Tablet Computers
- Portable Devices
- Solid State Drives (SSDs)
- Handheld Devices

All MPS parts are lead-free, halogen free, and adhere to the RoHS directive. For MPS green status, please visit the MPS website under Quality Assurance. “MPS”, the MPS logo, and “Simple, Easy Solutions” are registered trademarks of Monolithic Power Systems, Inc. or its subsidiaries.

EVQ5073-G-00A EVALUATION BOARD

(LxWxH) 6.4cmx6.4cmx1.3cm

Board Number	MPS IC Number
EVQ5073-G-00A	MPQ5073GG

R_{ON} vs. V_{CC}



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

QUICK START GUIDE

1. Connect the load terminals to:
   a. Positive (+): VOUT
   b. Negative (-): GND
2. Preset the power supply output between 3V to 5.5V, then turn off the power supply.
3. Connect the power supply output terminals to:
   a. Positive (+): VIN
   b. Negative (-): GND
4. Turn the power supply on. The board should automatically start up.
5. To use the enable function, apply a digital input to the EN pin. Drive EN above 2.6V to turn the regulator on; drive it below 0.4V to turn it off.
6. Use R1 to set the output current limit. Use C4 to set the soft-start time. Refer to the Application Information section MPQ5073's datasheet to select appropriate values for R1 and C4.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVALUATION BOARD SCHEMATIC



Figure 1: Evaluation Board Schematic

EVQ5073-G-00A BILL OF MATERIALS

Qty	Ref	Value	Description	Package	Manufacturer	Manufacturer P/N
1	R1	13kΩ	Film resistor, 1%	0603	Royal Ohm	RL0603FR-0713KL
1	R2	100kΩ	Film resistor, 1%	0603	Royal Ohm	RL0603FR-07100KL
1	R3	0Ω	Film resistor, 1%	0603	Royal Ohm	RC0603FR-070RL
4	C1A, C1B, C2A, C2B	22 µ F	Ceramic capacitor, 10V, X5R	0805	Murata	GRM21BR61A226ME51L
2	C3,C4	0.1µF	Ceramic capacitor, 16V, X7R	0603	Murata	GRM188R71C104KA01D
1	U1	MPQ5073	2A load switch	QFN-12 (2mmx2mm)	MPS	MPQ5073GG

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS

Performance waveforms are tested on the evaluation board. V_{IN} = 3.6V, V_{CC} = 3.6V, EN = 2.5V, R_{LIM} = 13kΩ, T_A = 25°C, unless otherwise noted.

Quiescent Current



Disabled Supply Current vs. Input Voltage



V_{IN} UVLO vs. Temperature



EN Rising Threshold vs. Temperature



R_{ON} vs. V_{CC}



R_{ON} vs. Temperature



Maximum Current Limit vs.V_{IN}



R_{LIMIT} vs. Current Limit



Soft-Start Time vs. Soft-Start Capacitance

V_{IN} = 3.6V



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance waveforms are tested on the evaluation board. V_{IN} = 3.6V, V_{CC} = 3.6V, EN = 2.5V, R_{LIM} = 13kΩ, T_A = 25°C, unless otherwise noted.

Input-to-Output Voltage vs. Load Current



Case Temperature Rise vs. Output Current

V_{IN} = 5V, V_{CC} = 3.6V



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance waveforms are tested on the evaluation board. V_{IN} = 3.6V, V_{CC} = 3.6V, EN = 2.5V, R_{LIM} = 13kΩ, T_A = 25°C, unless otherwise noted.

Start-Up through EN
V_{IN} = 5V, V_{CC} = 3.6V, no load



Start-Up through EN
V_{IN} = 5V, V_{CC} = 3.6V, 2A load



Shutdown through EN
V_{IN} = 5V, V_{CC} = 3.6V, no load



Shutdown through EN
V_{IN} = 5V, V_{CC} = 3.6V, 2A load



Start-Up
V_{IN} = 5V, V_{CC} = 3.6V, I_{OUT} = 0A



Start-Up
V_{IN} = 5V, V_{CC} = 3.6V, I_{OUT} = 2A



Shutdown
V_{IN} = 5V, V_{CC} = 3.6V, I_{OUT} = 0A



Shutdown
V_{IN} = 5V, V_{CC} = 3.6V, I_{OUT} = 2A



Steady State
V_{IN} = 5V, V_{CC} = 3.6V, I_{OUT} = 2A



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

EVB TEST RESULTS *(continued)*

Performance waveforms are tested on the evaluation board. V_{IN} = 3.6V, V_{CC} = 3.6V, EN = 2.5V, R_{LIM} = 13kΩ, T_A = 25°C, unless otherwise noted.

Load Transient Response

V_{IN} = 3.6V, V_{CC} = 3.6V, I_{OUT} = 0A to 2.5A



SCP Entry

V_{IN} = 5V, V_{CC} = 3.6V



SCP Steady State

V_{IN} = 5V, V_{CC} = 3.6V



SCP Recovery

V_{IN} = 5V, V_{CC} = 3.6V



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PCB LAYOUT



Figure 2: Top Silk Layer



Figure 3: Top Layer



Figure 4: Bottom Layer

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	2/25/2021	Initial Release	-

Notice: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.