MP2002A

Low Input Voltage, 500mA Linear Regulator

DESCRIPTION

The MP2002A is a low-current, low-dropout linear regulator operating over a single input supply between 1.35V to 6.5V. The output voltage of the MP2002A is adjustable via an external resistor divider. The MP2002A can supply up to 500mA of load current. The enable pin (EN) allows the part to be put into a low current shutdown mode (EN = 0).

The MP2002A features thermal overload and current limit protection. It is available in an 8-pin QFN (2x 3mm) package

FEATURES

- Power Good Open-Drain Output
- Operates from 1.35V to 6.5V Input
- Low 300mV Dropout at 500mA Output
- Stable with Very Small Ceramic Capacitors
- 2% Feedback Reference
- Adjustable Output Voltage Option from 0.5V to 5V Using an External Resistor Divider
- Better Than 0.001%/mA Load Regulation
- Low 100µA Ground Current
- Internal Thermal Protection
- Current Limit Protection
- 7µA Typical Shutdown Current
- Available in a QFN-8 (2mmx3mm) Package

APPLICATIONS

- Low-Current Regulators
- Battery-Powered Systems
- Cellular Phones

All MPS parts are lead-free, halogen-free, and adhere to the RoHS directive. For MPS green status, please visit the MPS website under Quality Assurance. “MPS”, the MPS logo, and “Simple, Easy Solutions” are trademarks of Monolithic Power Systems, Inc. or its subsidiaries.

TYPICAL APPLICATION



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

ORDERING INFORMATION

Part Number*	Package	Top Marking	MSL Rating
MP2002AGD	QFN-8 (2mmx3mm)	*See Below*	1

* For Tape & Reel, add suffix –Z (e.g. MP2002AGD-Z).

TOP MARKING

BLRY

LLLL

BLR: Product code of MP2002AGD
Y: Year code
LLLL: Lot number

PACKAGE REFERENCE



QFN-8 (2mmx3mm)

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PIN FUNCTIONS

Pin #	Name	Description
1	OUT	**Regulator output.** OUT is the output of the linear regulator. Bypass OUT to GND with a 4.7µF or greater capacitor.
2	NC	**No connection.**
3	PG	**Power good open-drain output.** If PG is pulled up to an external voltage, PG will be de-asserted (pulled high by external power source) if input power is off. See the Application Information section on page 10 for additional details.
4	FB	**Feedback input.** Connect a resistive voltage divider from OUT to FB to set the output voltage. OUT feedback threshold is 0.5V.
5	EN	**Enable input.** Drive EN above 1.2V to turn on the MP2002A; drive EN below 0.4V to turn it off.
6	GND, Exposed pad	**Ground.** The exposed pad must be connected to the GND plane.
7	NC	**No connection.**
8	IN	**Power source input.** IN supplies the internal power to the MP2002A, and is the source of the pass transistor. Bypass IN to GND with a 2.2µF or greater capacitor.

ABSOLUTE MAXIMUM RATINGS (1)

IN, PG, FB to GND.....-0.3V to +7V
EN to GND.....-0.3V to V_{IN} + 0.3V
OUT .....-0.3V to V_{IN} + 0.3V
Continuous power dissipation (T_A = 25°C) (2)
.....2.27W
Junction temperature .....150°C
Lead temperature .....260°C
Storage temperature..... -65°C to +150°C

Recommended Operating Conditions (3)

Input Voltage (V_{IN}).....1.35V to 6.5V
Output voltage .....0.5V to 5V
Load current.....500mA maximum
Maximum junction temp (T_J) .....125°C

Thermal Resistance θ_{JA} θ_{JC}

QFN-8 (2mmx3mm)
JESD51-7 (4) ..... 55 ..... 12... °C/W

Notes:

1) Exceeding these ratings may damage the device.
2) The maximum allowable power dissipation is a function of the maximum junction temperature, T_J (MAX), the junction-to-ambient thermal resistance, θ_{JA}, and the ambient temperature, T_A. The maximum allowable continuous power dissipation at any ambient temperature is calculated by P_D (MAX) = (T_J (MAX) - T_A) / θ_{JA}. Exceeding the maximum allowable power dissipation can cause excessive die temperature, and the regulator may go into thermal shutdown. Internal thermal shutdown circuitry protects the device from permanent damage.
3) The device is not guaranteed to function outside of its operating conditions.
4) Measured on JESD51-7 4-layer board. The value of θ_{JA} is only valid for comparison with other packages, and cannot be used for design purposes. These values are calculated in accordance with JESD51-7, and simulated on a specified JEDEC board. They do not represent the performance obtained in an actual application.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

ELECTRICAL CHARACTERISTICS

V_{IN} = 1.8V, V_{OUT} = 1.2V, C_{OUT} = 4.7µF, C_{IN} = 2.2µF, T_A = 25°C, unless otherwise noted.

Parameter	Symbol	Condition	Min	Typ (5)	Max	Units
Operating voltage		I_{OUT} = 1mA	1.35		6.5	V
Ground pin current		I_{OUT} = 1mA (7)		100		µA
		I_{OUT} = 500mA		5		mA
Shutdown current		V_{EN} = 0V, V_{IN} = 5V		7		µA
FB regulation voltage			0.482	0.500	0.508	V
		-40°C ≤ T_A ≤ +85°C	0.477	0.495	0.513	
Dropout voltage (8)		I_{OUT} = 500mA		290		mV
Line regulation (6)		I_{OUT} = 1mA, V_{IN} = (V_{OUT} + 0.5V) to 6.5V (8)		0.005		%/V
Load regulation (6)		I_{OUT} = 1mA to 500mA, V_{IN} = V_{OUT} + 0.5V		0.001		%/mA
Power good low output voltage (9)	V_{OL}	I_{SINK} = 0.5mA		0.5		V
EN high input voltage			1.2			V
EN low input voltage					0.4	V
EN input bias current		V_{EN} = 1.5V, 5V		0.01	1	µA
Thermal protection				155		°C
Current limit			550	730		mA

Notes:

5) Parameter is guaranteed by design. Not tested in production.
6) Resistors for VOUT are measured as 10kΩ, 14kΩ, 1%.
7) The ground current does not include the current through the feedback current.
8) Dropout voltage is defined as the input to output differential when the output voltage drops 1% below its nominal value.
9) $V_{FEEDBACK}$ is 90% of the regulated value with a 10kΩ pull-up resistor to 5V

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS

C1 = 2.2µF, C2 = 4.7µF, C3 = 1nF, T_A = 25°C, unless otherwise noted.

Voltage Dropout vs. Current



Line Regulation



Load Regulation



Load Regulation at 85°C



Line Regulation



Load Regulation



Load Regulation at -40°C



Line Regulation



Load Regulation



TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

C1 = 2.2µF, C2 = 4.7µF, C3 = 1nF, T_A = 25°C, unless otherwise noted.

Supply Current



Shutdown Current vs. Input Voltage



PSRR vs. Frequency



Feedback Voltage vs. Temperature

V_{IN} = 1.8V, V_{EN} = V_{IN}, I_{LOAD} = 1mA



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

C1 = 2.2µF, C2 = 4.7µF, C3 = 1nF, T_A = 25°C, unless otherwise noted.

Line Transient

V_{IN} = 2V to 3V, V_O = 1.8V, V_{EN} = V_{IN}, I_{LOAD} = 50mA, with resisitor load



Load Transient

V_{IN} = 2.5V, V_O = 1.8V, V_{EN} = V_{IN}, I_{LOAD} = 50mA to 300mA, with resistor load



Power Good Off

V_{IN} = 3.6V, V_O = 1.8V, V_{EN} = V_{IN}, I_{LOAD} = 0.17A, with resisitor load



Enable Turn-On

V_{IN} = 1.35V, V_O = 0.6V, V_{EN} = 0V to 3.6V, I_{LOAD} = 200mA, with resistor load



Enable Turn-Off

V_{IN} = 1.35V, V_O = 0.6V, V_{EN} = 3.6V to 0V, I_{LOAD} = 200mA, with resistor load



Power Good On

V_{IN} = 2.5V, V_O = 1.8V, V_{EN} = V_{IN}, I_{LOAD} = 0.3A, with resistor load



Thermal Protection

V_{IN} = V_{EN} = 5V, V_O = 1.8V, I_{LOAD} = 0.5A



Short-Circuit Protection

V_{IN} = 4V, V_O = 1.8V, V_{EN} = V_{IN}



Short-Circuit Recovery

V_{IN} = 4V, V_O = 1.8V, V_{IN} = V_{EN}



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

FUNCTIONAL BLOCK DIAGRAM



Figure 1: Functional Block Diagram

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

OPERATION

The MP2002A is a low-current, low-voltage, high power supply rejection ratio (PSRR), low-dropout linear regulator. It is intended for devices that require very low voltage, low quiescent current power, and high PSRR (e.g. wireless modems, pagers, and cellular phones).

The MP2002A uses a PNP transistor. It features internal thermal shutdown and an internal current limit circuit.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

APPLICATION INFORMATION

Setting the Output Voltage

The MP2002A has an adjustable output voltage, set via an external resistor divider (R1 and R2). R1 can be calculated with Equation (1):

$$R1 = R2 \times \left(\frac{V_{OUT} - V_{FB}}{V_{FB}} \right) \quad (1)$$

Where V_{FB} is the feedback voltage threshold on the OUT pin (about 0.5V).

For example, if the output voltage is 2.5V and R2 is 10kΩ, R1 would be 40kΩ. A standard 40kΩ (±1%) resistor can be used for R1.

Table 1 lists R1 values for typical output voltages (assuming R2 = 10kΩ).

Table 1: Adjustable Output Voltage and R1 Values

V_{OUT} (V)	R1 (kΩ)
1.25	15
1.5	20
1.8	26
2	30
2.5	40
2.8	46
3	50
3.3	56
4	70
5	90

Power Good (PG)

The power good (PG) pin is an open-drain output with a pull-up resistor (10kΩ recommended). The pull-up resistor can be tied to a 0V to 5.5V supply within the voltage range of the pin. For example, the pull-up resistor can be tied to the input voltage when it is being monitored by an IC powered from this input voltage.

PG monitors the output voltage. If the output voltage is 10% below its regulation point, the PG pin is pulled low.

PG can be pulled up by external power source. PG is pulled high by the external VCC when V_{IN} is below 0.86V (typically), because the internal control circuits are disabled and the open-drain FET is off. When EN is off and V_{IN} drops below the under-voltage lockout (UVLO) threshold, PG is pulled low.

Selecting the Bypass Capacitor

To reduce noise, the reference voltage can be bypassed via an external capacitor. It is recommended to use a low-ESR ceramic capacitor for the best performance.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PCB Layout Guidelines

PCB layout is critical for good regulation, ripple rejection, transient response, and thermal performance. It is highly recommended to duplicate the EVB layout for optimal performance. For the best results, refer to Figure 2 and follow the guidelines below:

1. Place ceramic input ceramic capacitors close to the IN pin.
2. Place ceramic output capacitors close to the OUT pin.
3. Ensure all feedback connections are short and direct.
4. Place the feedback resistors and compensation components as close to the chip as possible.
5. Connect IN, OUT, and especially GND to a large copper area to cool the chip, and improve thermal performance and long-term reliability.



Top Layer **Bottom Layer**

Figure 2: Recommended PCB Layout

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL APPLICATION CIRCUIT



Figure 3: Typical Application Circuit with Fixed OUT Pin (10)

Note:

10) If PG is pulled up to an external power supply, see the Power Good (PG) section on page 10.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PACKAGE INFORMATION

QFN-8 (2mmx3mm)



TOP VIEW



BOTTOM VIEW



SIDE VIEW



DETAIL A



RECOMMENDED LAND PATTERN

NOTE:

1) ALL DIMENSIONS ARE IN MILLIMETERS.
2) EXPOSED PADDLE SIZE DOES NOT INCLUDE MOLD FLASH.
3) LEAD COPLANARITY SHALL BE 0.10 MILLIMETER MAX.
4) DRAWING CONFORMS TO JEDEC MO-229, VARIATION VCED-2.
5) DRAWING IS NOT TO SCALE.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

CARRIER INFORMATION



Part Number	Package Description	Quantity/ Reel	Quantity/ Tube	Reel Diameter	Carrier Tape Width	Carrier Tape Pitch
MP2002AGD-Z	QFN-8 (2mmx3mm)	5000	N/A	13in	12mm	8mm

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	4/23/2021	Initial Release	-

Notice: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.