User Guide

MP8867 Evaluation Kit (EVKT-8867)

Table of Contents

Overview 3
Section 1. Hardware Specifications 5
1.1 Personal Computer Requirements 5
1.2 EV8867-LE-00A Specifications 5
1.3 EVKT-USBI2C-02 Specifications 5
Section 2. Software Requirements 6
2.1 Software Installation Procedure 6
Section 3. Evaluation Kit Test Set-Up 7
3.1 Hardware Set-Up 7
3.2 Powering Up the EVB 7
3.3 Software Set-Up 7
3.4 Troubleshooting Tips 10
Section 4. Ordering Information 11

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2018 MPS. All Rights Reserved.

Overview

Introduction

The EVKT-8867 is an evaluation kit for the MP8867. The MP8867 is a high-frequency, synchronous, rectified, step-down, switch-mode converter with an I²C control interface. The MP8867 achieves 8A of output current with excellent load and line regulation over a wide input supply range. This kit allows for quick evaluation of the MP8867. By using the I²C, users can set the output voltage, slew rate, switching frequency, and work mode.

Kit Contents

EVKT-88647 kit contents (items below can be ordered separately):

#	Part Number	Item	Quantity
1	EV8867-LE-00A	MP8867GLE evaluation board	1
2	EVKT-USBI2C-02	Includes one USB to I²C communication interface, one USB cable, and one ribbon cable	1



Figure 1: EVKT-8867 Evaluation Kit Set-Up

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2018 MPS. All Rights Reserved.

Features and Benefits

The MP8867 is highly customizable. Users can program the MP8867 via the MPS I²C GUI.

⚠ *All changes made in I²C mode will NOT be retained once the EVB is powered down.*

Adjustable features:

I²C
• Adjustable output voltage • Selectable slew rate • Selectable switching frequency • Selectable PFM mode • System enable (EN bit) • Status indication: OC, OTEW, OT, PG

Kit Specifications

Features	Specification
Supply for Board	4.5V to 17V
Operating Input Voltage	4.5V to 17V
Output Voltage (V_{OUT})	1V
Output Current (I_{OUT})	8A
Operating Systems Supported	Windows XP, 7, or later
System Requirements	Minimum 22.2MB free
GUI Software	2 register controls: VSEL, System1
EVB Size (LxW)	8.5cmx8.5cm

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2018 MPS. All Rights Reserved.

Section 1. Hardware Specifications

1.1 Personal Computer Requirements

The following must be met to use the EVKT-8867:

- Operating system of Windows XP, 7, or later
- Net framework 4.0
- PC with a minimum of one available USB port
- At least 22.2MB of free space

1.2 EV8867-LE-00A Specifications

The EV8867-LE-00A is an evaluation board for the MP8867GLE. For more information, refer to the EV8867-LE-00A datasheet.

Figure 2: EV8867-LE-00A Evaluation Board

Feature	Specification
Supply for Board	4.5V to 17V
Operating Input Voltage	4.5V to 17V
Output Voltage (V_{OUT})	1V
Output Current (I_{OUT})	8A
EVB Size (LxW)	8.5cmx8.5cm

1.3 EVKT-USBI2C-02 Specifications

The EVKT-USBI2C-02 communication interface connects the EVB, the PC, and its supporting accessories. It provides I^2C and PMBus capabilities. Together with the MPS Virtual Bench Pro and GUI tools, it provides a quick and easy way to evaluate the performance of MPS digital products. For more details, refer to the EVKT-USBI2C-02 datasheet.

Figure 3: EVKT-USBI2C-02 Communication Interface

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2018 MPS. All Rights Reserved.

Section 2. Software Requirements

2.1 Software Installation Procedure

Programming occurs through the MPS I²C GUI. Follow the instructions below to download and install the software:

Note: This software can be downloaded directly from the MPS website.

1. Visit the MP88xx I²C GUI page at https://www.monolithicpower.com/en/i2c-tool.html.
2. Click the “Download” button in the upper right-hand corner.
3. Once the download has completed, double-click the .exe file to open the set-up guide (see Figure 4). If a protection window comes up, click “More info,” then click “Run anyway.”
4. Follow the prompts in the set-up guide.
5. Wait for the status screen to verify that installation is complete (see Figure 5).



Figure 4: MPS I²C GUI Set-Up Guide



Figure 5: MPS I²C GUI Set-Up Success

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2018 MPS. All Rights Reserved.

Section 3. Evaluation Kit Test Set-Up

3.1 Hardware Set-Up

The hardware must be configured properly prior to use. Use the USB cable to connect the EVKT-USBI2C-02 communication interface to the PC, and follow the instructions below to set up the EVB:

1. Locate the proper wires to connect the EVB to the EVKT-USBI2C-02 communication interface.
2. Connect SCL, SDA, and GND (see Figure 6). If needed, refer to the datasheet for further clarification.



Figure 6: EVB to MPS I²C Communication Interface Wire Connection

3.2 Powering Up the EVB

1. Connect the positive and negative terminals of the load to the VOUT and GND pins, respectively.
2. Preset the power supply output between 4.5V to 17V, then turn off the power supply.
3. Connect the positive and negative terminals of the power supply output to the VIN and GND pins, respectively.
4. Turn the power supply on. The MP8867 will enter the power-on sequence automatically.

3.3 Software Set-Up

After connecting the hardware according to the above steps, follow the steps below to use the GUI software:

1. Start the software. It will automatically check the EVB connection.
    - If the connection is successful, the address will be listed in the “Slave Address” (see Figure 7).

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2018 MPS. All Rights Reserved.



Figure 7: Appearance of Address Indicates Successful Connection

- If not, a warning will appear at the bottom. There are two warnings users can expect (see Figure 8). Each warning means there is an invalid connection.

  1) "EVB is Disconnected" means that the evaluation board is not connected.

  2) "Communication Board is Disconnected" means that the USB I^2C communication interface is not connected.



Figure 8: Warning Indicates Unsuccessful Connection

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2018 MPS. All Rights Reserved.

2. If the connection is successful, proceed to Step 3. Otherwise, check connections between the EVB, communication interface, and PC. Re-plug the USB into the computer and restart the GUI.
3. Click the “Part Select” button to select the MP8867 (see Figure 7). The default GUI window is for the MP8861. The Register Control menu will appear on the left side. I²C register values will be read and displayed on the right side after clicking the “Read” button (see Figure 9).



Figure 9: Values from I²C Shown in Table

4. Find the item you want to change, and select the desired value from the drop-down menu.
5. Click the “Read All” button to update values. The changed information of the item will appear on the right side (see Figure 10).



Figure 10: Refer to Datasheet to Translate 0s and 1s

⚠ *All changes made via the I²C will be restored to default values once the EVB is powered down.*

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2018 MPS. All Rights Reserved.

3.4 Troubleshooting Tips

Note: USBI2C-02 and USBI2C-01 drivers are not compatible. USBI2C-02 uses USBXpress and USBI2C-01 uses Cyusb3. USBI2C-02 is the recommended device for MPS PMBus and I²C.

EVKT-USBI2C-01

If the USBI2C-01 driver is not properly installed, manual installation is required. Follow the steps below:

1. Open the Device Manager and select “Update Driver Software” (see Figure 11).
2. Click “Browse My Computer for Driver Software,” find the downloaded driver, and install.



Figure 11: Updating the Driver Software

EVKT-USBI2C-02

If the USBI2C-02 driver is not properly installed, manual installation is required. Follow the steps below:

Note: Check the driver version. Find “USBXpress Device” in the Device Manager under USB controllers.



Right-click and view properties. Check to make sure the driver version matches the newest version (see Figure 12).

1. Install the correct USBXpress “.exe” file.

   Choose either the 32-bit or 64-bit operating system:

   32-bit: USBXpressInstaller_x86.exe

   64-bit: USBXpressInstaller_x64.exe
2. Connect the EVKT-USBI2C-02 communication interface to the PC with the USB cable.



Figure 12: Correct Driver Version

- **No Supply**

The MP8867’s input pin has an under-voltage lockout (UVLO) detection circuit. If the input voltage (AVIN) is lower than the UVLO rising threshold, the MP8867’s functions are disabled.

- **Shutdown Event**

If the MP8867 detects that the input voltage is lower than the UVLO falling threshold (enter no supply state) or over-temperature protection is triggered (enter power-off state), the MP8867 switches to no supply state or power-off state, regardless of the current state.

- **Thermal Recovery**

If the MP8867 is in a power-off state due to the die temperature exceeding the thermal protection threshold, the MP8867 enters the power-on sequence once the die’s temperature decreases.

- **Shutdown Sequence**

When the input voltage is lower than the UVLO falling threshold or the IC is over-temperature, the MP8867 immediately begins the shutdown sequence.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2018 MPS. All Rights Reserved.

Section 4. Ordering Information

The components of the evaluation kit can be purchased separately, depending on user needs.

Part Number	Description
EVKT-8867	Complete evaluation kit
Contents of EVKT-8867	
EV8867-LE-00A	MP8867GLE evaluation board
EVKT-USBI2C-02	Includes one USB to I^2C communication interface, one USB cable, and one ribbon cable

Order directly from MonolithicPower.com.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2018 MPS. All Rights Reserved.