MPQ7230

42V, 1.2A, Synchronous Buck-Boost or 3A Buck Automotive Infrared LED Driver, AEC-Q100 Qualified

DESCRIPTION

The MPQ7230 is a fixed-frequency, constant current buck-boost LED driver with integrated power MOSFETs. The device offers a very compact solution to achieve 1.2A of continuous output current, with excellent load and line regulation across a wide input supply range. The MPQ7230 can also be configured to buck mode to provide up to 3A of constant load current.

The MPQ7230 can support PWM dimming frequencies as low as 10Hz to adjust infrared radiation (IR) in LED driver applications. It is also compatible with 30FPS, 60FPS, and 120FPS dimming.

Constant frequency hysteretic control mode provides extremely fast transient response without loop compensation.

Full protection features include over-current protection (OCP), thermal derating (TD), and thermal shutdown (TSD).

The MPQ7230 requires a minimal number of readily available, standard external components. It is available in a space-saving QFN-19 (3mmx4mm) package.

FEATURES

- **Built for a Wide Range of IR LED Applications:**
  - Wide 6V to 42V Operating Input Range
  - 10Hz to 2kHz PWM Dimming Frequency
  - Compatible with 30FPS, 60FPS, and 120FPS Dimming
- **High Performance for Improved Thermals:**
  - Configurable LED Current without Sensing Resistor
  - 44mΩ/40mΩ Low $R_{DS(ON)}$ Internal Power MOSFETs
  - High-Efficiency Synchronous Mode Operation
- **Optimized for EMC/EMI:**
  - Default 410kHz f_{SW} with Spread Spectrum
  - EMI Reduction Technique
- **Full Protection Features:**
  - LED Short (to GND and Battery), LED Open, Output OVP with Fault Indication
  - OCP with Latch-Off Mode
  - Configurable Thermal Derating via NTC Remote Temperature Sense
  - Thermal Shutdown
- **Additional Features:**
  - Configurable 1.2A Current in Buck-Boost Mode or 3A in Buck Mode
  - 5% LED Current Accuracy (700mA–1.2A for Buck-Boost or 1A–2A for Buck)
  - Available in QFN-19 (3mmx4mm) Package
  - Available in Wettable Flank
  - Available in AEC-Q100 Grade 1

APPLICATIONS

- Infrared (IR) LED Drivers for Driver Monitoring Systems (DMS)
- Infrared (IR) Illumination for Automotive Cameras
- Surveillance Systems

All MPS parts are lead-free, halogen-free, and adhere to the RoHS directive. For MPS green status, please visit the MPS website under Quality Assurance. “MPS”, the MPS logo, and “Simple, Easy Solutions” are trademarks of Monolithic Power Systems, Inc. or its subsidiaries.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL APPLICATION



Figure 1: Buck Topology (≥14.7kΩ R_{IREF})





Figure 2: Buck-Boost Topology (≤9.09kΩ R_{IREF})



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

ORDERING INFORMATION

Part Number*	Package	Top Marking	MSL Rating**
MPQ7230GLE-AEC1***	QFN-19 (3mmx4mm)	*See Below*	1

* For Tape & Reel, add suffix -Z (e.g. MPQ7230GLE-AEC1-Z).

** Moisture Sensitivity Level Rating

*** Wettable Flank

TOP MARKING

MPYW
7230
LLL
E

MP: MPS prefix
Y: Year code
W: Week code
7230: Part number
LLL: Lot number
E: Wettable lead flank

PACKAGE REFERENCE



QFN-19 (3mmx4mm)

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PIN FUNCTIONS

Pin #	Name	Description
1	NTC	**Remote temperature sense.** Connect NTC to a resistor, or connect a resistor network from NTC to AGND, to configure the temperature derating starting point. The device provides protections for NTC to PGND, AGND, or INGND shorts.
2	NC	**Not connection.** Externally connect NC to PGND on the board.
3	EN	**Enable.** Pull EN above 1.2V to enable the chip; pull EN below 0.6V to shut down the chip. The part starts to sense the different pin configurations at the first positive edge of EN. The EN pin can be connected to VIN through a resistor below 100kΩ. EN is pulled low with an internal resistor. When EN is floating, the device is off by default.
4, 13	VIN	**Supply voltage.** The MPQ7230 operates from a 6V to 42V input rail. An input capacitor (C_{IN}) is required to decouple the input rail. Connect VIN to the input rail using a wide PCB trace.
5, 6, 11, 12	PGND	**Power ground.** PGND is the reference ground of the power device (including the configuration pins), so PGND requires careful consideration during PCB layout. Generally, PGND is used to dissipate thermal heat.
7	BST	**Bootstrap.** Connect a capacitor between the SW and BST pins to form a floating supply across the high-side MOSFET driver. A resistor can also be placed between SW and the capacitor to reduce the SW spike voltage and improve EMI performance.
8, 9	SW	**Switch output.** SW is the middle point of the high-side and low-side MOSFETs. It is recommended to keep the SW node small. Use a wide SW trace to reduce noise coupling and improve EMI.
10	FAULT	**Fault indicator.** FAULT is an open-drain output with an internal 300kΩ pull-up resistor connected to VIN, and a 4MΩ pull-down resistor connected to INGND. FAULT is pulled low if one of the following occurs: an LED short or open fault, over-temperature protection (OTP), false mode detection, and over-current protection (OCP). FAULT can be continuously connected to VIN through a pull-up resistor.
14	INGND	**VIN, EN, DIM, and FAULT ground for a buck-boost topology.** For a buck topology, connect INGND to PGND or AGND.
15	AGND	**Analog ground.** AGND is the reference ground of the logic circuit. Connect AGND to PGND with an external trace.
16	VCC	**Internal bias supply.** VCC supplies power to the internal control circuit and gate drivers. A ≥3µF decoupling capacitor should be connected from VCC to ground, and placed close to VCC. Considering the capacitance derating, a 10µF/10V or 16V capacitor with X7R dielectrics is strongly recommended.
17	IREF	**Mode selection and NTC reference current setting.** Connect a ≤9.09kΩ resistor to IREF to select buck-boost mode, or connect a ≥14.7kΩ resistor to select buck mode. The voltage on IREF is 0.57V after mode detection finishes. Connect a resistor (R_{IREF}) from IREF to GND to get a reference current (0.57V / R_{IREF}). If the IREF pin is shorted to ground or has an open fault, the device latches off and asserts FAULT. The current on the NTC pin is 50 (buck mode) or 5 (buck-boost mode) times the reference current.
18	ISET	**LED current set.** Connect an external resistor from ISET to ground to set the LED average current. If the ISET pin experiences a short or open fault, the part latches off and asserts FAULT.
19	DIM	**Dimming control.** Apply an external clock to the DIM pin for PWM dimming. Drive DIM above 1.6V to turn dimming on; drive DIM below 0.7V to turn dimming off. Ensure that the dimming on time is at least 100µs to avoid mistriggering FAULT. The dimming off time can be as long as 100ms. This means that the MPQ7230 can support a dimming frequency as low as 10Hz to handle 30Hz infrared LED driver applications.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

ABSOLUTE MAXIMUM RATINGS (1)

V_{IN} - $V_{PGND/AGND}$ ..... -0.3V to +50V
V_{IN} - V_{INGND} ..... -0.3V to +50V
V_{FAULT} - V_{INGND} ..... -0.3V to +50V
V_{EN}, V_{DIM} - V_{INGND} ..... -0.3V to +5.5V
V_{DIM} - $V_{PGND/AGND}$ ..... -0.3V to +50V
V_{SW} - $V_{PGND/AGND}$ .....-0.3V to V_{IN} - $V_{PGND/AGND}$ + 0.3V
V_{BST} .....V_{SW} + 5.5V
All other pins - $V_{PGND/AGND}$ ..... -0.3V to 5.5V
Continuous power dissipation (T_A = 25°C) (2) (6)
QFN-19 (3mmx4mm) 3.9W
Junction temperature ..... 150°C
Lead temperature ..... 260°C
Storage temperature ..... -65°C to +150°C

Electrostatic Discharge (ESD) Ratings

Human body model (HBM) ..... Class 2 (3)
Charged device model (CDM) .....Class C2b (4)

Recommended Operating Conditions

Supply voltage (V_{IN} - V_{PGND}) ..... 6V to 42V
LED current (I_{LED}) buck-boost mode.. Up to 1.2A
LED current (I_{LED}) buck mode..... Up to 3A
Operating junction temp (T_J) .... -40°C to +150°C

Thermal Resistance θ_{JA} ..... θ_{JC}

QFN-19 (3mmx4mm)			
JESD51-7 (5)	48	11	°C/W
EVQ7230-L-00A (6)	32	6	°C/W

Notes:

1) Exceeding these ratings may damage the device.
2) The maximum allowable power dissipation is a function of the maximum junction temperature, T_J (MAX), the junction-to-ambient thermal resistance, θ_{JA}, and the ambient temperature, T_A. The maximum allowable continuous power dissipation at any ambient temperature is calculated by P_D (MAX) = (T_J (MAX) - T_A) / θ_{JA}. Exceeding the maximum allowable power dissipation can cause excessive die temperature, and the device may go into thermal shutdown. Internal thermal shutdown circuitry protects the device from permanent damage.
3) Per AEC-Q100-002.
4) Per AEC-Q100-011.
5) Measured on JESD51-7, 4-layer PCB. The values given in this table are only valid for comparison with other packages and cannot be used for design purposes. These values were calculated in accordance with JESD51-7, and simulated on a specified JEDEC board. They do not represent the performance obtained in an actual application.
6) Measured on MPS standard EVB of MPQ7230, 4-layer PCB, 2oz.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

ELECTRICAL CHARACTERISTICS

Buck mode, V_{IN} = 13.5V, V_{EN} = 2V, T_J = -40°C to +150°C, typical values are at T_J = 25°C, unless otherwise noted.

Parameter	Symbol	Condition	Min	Typ	Max	Units
Supply current (shutdown)	I_{SD}	V_{EN} = 0V		30	80	μA
Supply current (quiescent)	I_Q	V_{EN} = 2V, no switching, I_{IREF} float (exclude I_{IREF} and NTC current)		1.2	2	mA
		FAULT latch			2	mA
HS switch on resistance	HS_{RDS-ON}	V_{BST-SW} = 5V, R_{ISET} = 13.3kΩ		44	85	mΩ
		V_{BST-SW} = 5V, R_{ISET} = 40.2kΩ		85	160	mΩ
LS switch on resistance	LS_{RDS-ON}	V_{CC} = 5.2V, R_{ISET} = 13.3kΩ		40	80	mΩ
		V_{CC} = 5.2V, R_{ISET} = 40.2kΩ		80	150	mΩ
Switch leakage	SW_{LKG}	V_{EN} = 0V, V_{SW} =13.5V, T_J = 25°C			1	μA
		V_{EN} = 0V, V_{SW} =13.5V			5	μA
Peak current limit (7)	I_{LIMIT_PEAK}	R_{ISET} = 40.2kΩ	2.65	3.15	3.65	A
		R_{ISET} = 13.3kΩ	5.3	6.3	7.3	A
ZCD (7)				50		mA
Oscillator frequency	f_{SW}	FSS activated	330	410	490	kHz
Minimum on time (7)	t_{ON_MIN}			55	80	ns
Minimum off time (7)	t_{OFF_MIN}			75	100	ns
Maximum duty cycle (7)	D_{MAX}	Low dropout	95	98		%
Spread spectrum frequency (7)				15		kHz
Spread spectrum frequency range (7)				±10%		f_{SW}
LED current	I_{LED}	R_{ISET} = 13.3kΩ, T_J = 25°C to 100°C	1.14	1.2	1.26	A
		R_{ISET} = 13.3kΩ	1.02	1.2	1.38	
LED current threshold for MOSFET (half off)	I_{LED_CUT}			600	700	mA
ISET voltage	V_{ISET}	I_{ISET} = 45μA	0.573	0.592	0.606	V
ISET current threshold for short fault		I_{LED} < I_{LED_CUT}	80	120	160	μA
		I_{LED} > I_{LED_CUT}	180	220	260	μA
ISET current threshold for open fault			0.5	1.4	5	μA
EN rising threshold	V_{EN_RISING}	V_{EN} - V_{INGND}		1	1.6	V
EN falling threshold	$V_{EN_FALLING}$	V_{EN} - V_{INGND}	0.6	0.9		V
EN threshold hysteresis	V_{EN_HYS}	V_{EN} - V_{INGND}		100		mV
EN input current	I_{EN}	V_{EN} - V_{INGND} = 2V		2	8	μA
		V_{EN} - V_{INGND} = 0V		0	0.2	μA

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

ELECTRICAL CHARACTERISTICS *(continued)*

Buck mode, V_{IN} = 13.5V, V_{EN} = 2V, T_J = -40°C to +150°C, typical values are at T_J = 25°C, unless otherwise noted.

Parameter	Symbol	Condition	Min	Typ	Max	Units
DIM rising threshold	V_{DIM_RISING}	V_{DIM} - V_{INGND}		1	1.6	V
DIM falling threshold	$V_{DIM_FALLING}$	V_{DIM} - V_{INGND}	0.7	0.9		V
DIM threshold hysteresis	V_{DIM_HYS}	V_{DIM} - V_{INGND}		100		mV
DIM input current	I_{DIM}	V_{DIM} - V_{INGND} = 2V		2		µA
		V_{DIM} - V_{INGND} = 0V		0	0.2	µA
Maximum DIM off time	t_{DIM_OFF}		100			ms
V_{IN} under-voltage lockout rising threshold	$INUV_{VTH_R}$	V_{IN} - V_{INGND}	5.75	6	6.25	V
V_{IN} under-voltage lockout falling threshold	$INUV_{VTH_F}$	V_{IN} - V_{INGND}	4.4	4.9	5.2	V
V_{IN} under-voltage lockout threshold hysteresis	$INUV_{HYS}$	V_{IN} - V_{INGND}		1.1		V
V_{CC} under-voltage lockout rising threshold	V_{CC_VTH}	V_{CC} - V_{AGND}	4.4	4.7	5	V
V_{CC} under-voltage lockout falling threshold		V_{CC} - V_{AGND}	3.4	4.05	4.7	V
V_{CC} under-voltage lockout threshold hysteresis	V_{CC_HYS}	V_{CC} - V_{AGND}		650		mV
VCC regulator	V_{CC}	I_{CC} = 0mA	4.9	5.1	5.3	V
VCC load regulation		I_{CC} = 20mA	4.7			V
VCC maximum current ability		V_{CC} = $V_{CC\ UVLO}$ + 100mV, no switching	50	80	120	mA
VCC source current ability (7)		V_{CC} = $V_{CC\ UVLO}$ + 100mV, switching		25		mA
Output under-voltage threshold	UV_{VTH}		0.6	1.1	1.7	V
LED low current threshold		$I_{LED_SETTING}$ < I_{LED_CUT}	45	60	75	mA
		$I_{LED_SETTING}$ > I_{LED_CUT}	100	120	150	mA
FAULT assertion delay time when startup	$t_{FT-D-START}$		20	35	45	ms
FAULT assertion deglitch time after start-up (7)	t_{FT-D}			20		µs
FAULT assertion low sink current ability	I_{FAULT_SINK}	V_{FAULT} = 12V	10	30	50	mA
		V_{FAULT} = 0.2V	5	12		mA
FAULT pull-up resistor			100	300	500	kΩ
FAULT pull-down resistor			2000	4000	6000	kΩ
IREF current for mode detection			200	240	280	µA
V_{IREF} threshold for mode detection			2.6	2.7	2.8	V

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

ELECTRICAL CHARACTERISTICS *(continued)*

Buck mode, V_{IN} = 13.5V, V_{EN} = 2V, T_J = -40°C to +150°C, typical values are at T_J = 25°C, unless otherwise noted.

Parameter	Symbol	Condition	Min	Typ	Max	Units
IREF voltage	V_{IREF}	I_{IREF} = 20µA	0.51	0.57	0.63	V
IREF current threshold for pin short detection			60	85	120	µA
IREF current threshold for pin open detection				3	6	µA
NTC source current	I_{NTC}	V_{NTC} = 1.25V, I_{REF} = 20µA	950	1020	1090	µA
NTC voltage for current derating		I_{LED} = 98% of nominal	-2.5%	1.25	+2.5%	V
		I_{LED} = 74% of nominal	-2.5%	0.89	+2.5%	V
		I_{LED} = 50% of nominal	-2.5%	0.53	+2.5%	V
VNTC threshold for OTP				0.37		V
VNTC deglitch time for OTP		V_{NTC} = 0.3V	180	256	320	µs
V_{NTC} recovery threshold for OTP				0.48		V
Thermal shutdown (7)			155	170	185	°C

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

ELECTRICAL CHARACTERISTICS *(continued)*

Buck-boost mode, V_{IN} = 13.5V, V_{EN} = 2V, T_J = -40°C to +150°C, typical values are at T_J = 25°C, unless otherwise noted.

Parameter	Symbol	Condition	Min	Typ	Max	Units
Supply current (shutdown)	I_{SD}	V_{EN} = 0V		30	80	μA
Supply current (quiescent)	I_Q	V_{EN} = 2V, no switching, I_{IREF} float (exclude I_{IREF} and NTC current)		1.2	2	mA
		FAULT latch			2	mA
HS switch on resistance	HS_{RDS-ON}	V_{BST-SW} = 5V, R_{ISET} = 13.3kΩ		44	85	mΩ
LS switch on resistance	LS_{RDS-ON}	V_{CC} = 5.2V, R_{ISET} = 13.3kΩ		40	80	mΩ
Switch leakage	SW_{LKG}	V_{EN} = 0V, V_{SW} = 13.5V, T_J= 25°C			1	μA
		V_{EN} = 0V, V_{SW} = 13.5V			5	μA
Peak current limit (7)	I_{LIMIT_PEAK}		5.3	6.3	7.3	A
ZCD (7)				50		mA
Oscillator frequency	f_{SW}	FSS activated	330	410	490	kHz
Minimum on time (7)	t_{ON_MIN}			55	80	ns
Minimum off time (7)	t_{OFF_MIN}			75	100	ns
Maximum duty cycle (7)	D_{MAX}	Low dropout	95	98		%
Spread spectrum frequency (7)				15		kHz
Spread spectrum frequency range (7)				±10%		f_{SW}
LED current	I_{LED}	R_{ISET} = 21.5kΩ, T_J = 25°C to 100°C	0.7125	0.75	0.7875	A
		R_{ISET} = 21.5kΩ	0.6375	0.75	0.8625	
		R_{ISET} = 13.3kΩ, T_J = 25°C to 100°C	1.14	1.2	1.26	A
		R_{ISET} = 13.3kΩ	1.02	1.2	1.38	
ISET voltage	V_{ISET}	I_{ISET} = 45μA	0.573	0.592	0.606	V
Power derating ratio		V_{IN} = 6.6V, V_{ISET} respect to nominal		95		%
		V_{IN} = 5.3V, V_{ISET} respect to nominal		75		%
ISET current threshold for pin short			80	120	160	μA
ISET current threshold for pin open			0.5	1.4	5	μA
EN rising threshold	V_{EN_RISING}	V_{EN} - V_{INGND}		1	1.6	V
EN falling threshold	$V_{EN_FALLING}$	V_{EN} - V_{INGND}	0.6	0.9		V
EN threshold hysteresis	V_{EN_HYS}	V_{EN} - V_{INGND}		100		mV
EN input current	I_{EN}	V_{EN} = 2V		2	8	μA
		V_{EN} = 0V		0	0.2	μA

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

ELECTRICAL CHARACTERISTICS *(continued)*

Buck-boost mode, V_{IN} = 13.5V, V_{EN} = 2V, T_J = -40°C to +150°C, typical values are at T_J = 25°C, unless otherwise noted.

Parameter	Symbol	Condition	Min	Typ	Max	Units
DIM rising threshold	V_{DIM_RISING}	V_{DIM} - V_{INGND}		1	1.6	V
DIM falling threshold	$V_{DIM_FALLING}$	V_{DIM} - V_{INGND}	0.7	0.9		V
DIM threshold hysteresis	V_{DIM_HYS}	V_{DIM} - V_{INGND}		100		mV
DIM input current	I_{DIM}	V_{DIM} - V_{INGND} = 2V		2		µA
		V_{DIM} - V_{INGND} = 0V		0	0.2	µA
Maximum DIM off time	t_{DIM_OFF}		100			ms
V_{IN} under-voltage lockout rising threshold	$INUV_{VTH_R}$	V_{IN} - V_{INGND}	5.75	6	6.25	V
V_{IN} under-voltage lockout falling threshold	$INUV_{VTH_F}$	V_{IN} - V_{INGND}	4.4	4.9	5.2	V
V_{IN} under-voltage lockout threshold hysteresis	$INUV_{HYS}$	V_{IN} - V_{INGND}		1.1		V
V_{CC} under-voltage lockout rising threshold	V_{CC_VTH}	V_{CC} - V_{AGND}	4.4	4.7	5	V
V_{CC} under-voltage lockout falling threshold		V_{CC} - V_{AGND}	3.4	4.05	4.7	V
V_{CC} under-voltage lockout threshold hysteresis	V_{CC_HYS}	V_{CC} - V_{AGND}		650		mV
VCC regulator	V_{CC}	I_{CC} = 0mA	4.9	5.1	5.3	V
VCC load regulation		I_{CC} = 20mA	4.7			V
VCC max current ability		V_{CC} = V_{CC_UVLO} + 100mV, no switching	50	80	120	mA
VCC source current ability (7)		V_{CC} = V_{CC_UVLO} + 100mV, switching		25		mA
Output over voltage threshold	OV_{VTH}	V_{INGND} - V_{AGND}	17	18	19	V
Output Under voltage threshold	UV_{VTH}	V_{INGND} - V_{AGND}	1	1.35	1.7	V
VIN load dump protection threshold			38	40	42	V
VIN load dump protection falling threshold			37	39	41	V
VIN load dump protection hysteresis				1		V
Output discharge current for load dump protection		V_{INGND} - V_{PGND} > 5V	40	100	180	mA
		V_{INGND} - V_{PGND} = 1V	20	45	90	mA

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

ELECTRICAL CHARACTERISTICS *(continued)*

Buck-boost mode, V_{IN} = 13.5V, V_{EN} = 2V, T_J = -40°C to +150°C, typical values are at T_J = 25°C, unless otherwise noted.

Parameter	Symbol	Condition	Min	Typ	Max	Units
FAULT assertion delay time when startup	$t_{FT-D-START}$		20	35	45	ms
FAULT assertion deglitch time after startup	t_{FT-D}			20		µs
FAULT assertion low sink current ability	I_{FAULT_SINK}	V_{FAULT} = 12V	10	30	50	mA
		V_{FAULT} = 0.2V	5	12		mA
FAULT pull-up resistor			100	300	500	kΩ
FAULT pull-down resistor			2000	4000	6000	kΩ
IREF current for mode detection			200	240	280	µA
VIREF threshold for mode detection			2.6	2.7	2.8	V
IREF voltage	V_{IREF}	I_{REF} = 20µA	0.51	0.57	0.63	V
IREF current threshold for pin short detection			650	800	950	µA
IREF current threshold for pin open detection				40	55	µA
NTC source current	I_{NTC}	V_{NTC} = 1.25V, I_{IREF} = 200µA	950	1020	1090	µA
NTC voltage for current derating		I_{LED} = 98% of nominal	-2.5%	1.25	+2.5%	V
		I_{LED} = 74% of nominal	-2.5%	0.89	+2.5%	V
		I_{LED} = 50% of nominal	-2.5%	0.53	+2.5%	V
VNTC threshold for OTP				0.37		V
VNTC deglitch time for OTP		V_{NTC} = 0.3V	180	256	320	µs
V_{NTC} recovery threshold for OTP				0.48		V
Thermal shutdown (7)			155	170	185	°C

Note:

7) Not tested in production and guaranteed by design and characterization.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL CHARACTERISTICS

V_{IN} = 12V, T_J = -40°C to +150°C, unless otherwise noted.

Shutdown Current vs. Temperature



Quiescent Current vs. Temperature



V_{IN} UVLO Threshold vs. Temperature



EN Threshold vs. Temperature



VCC Voltage vs. Temperature



VCC UVLO Threshold vs. Temperature



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL CHARACTERISTICS *(continued)*

V_{IN} = 12V, T_J = -40°C to +150°C, unless otherwise noted.

Current Limit with MOSFETs Fully On vs. Temperature



Current Limit with MOSFETs Half On vs. Temperature



V_{IREF} vs. Temperature



V_{ISET} vs. Temperature



Switching Frequency vs. Temperature



V_{OUT} UV Threshold vs. Temperature

Buck mode



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL CHARACTERISTICS *(continued)*

V_{IN} = 12V, T_J = -40°C to +150°C, unless otherwise noted.

V_{OUT} UV Threshold vs. Temperature

Buck-boost mode



V_{OUT} OVP Threshold vs. Temperature

Buck-boost mode



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, I_{LED} = 3A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

I_{LED} Part to Part Variation
T_J = 25°C to +100°C



I_{LED} Part to Part Variation
T_J = -40°C to +150°C



I_{LED} Precision vs. Input Voltage
L = 10µH, I_{LED} = 1.2A, V_{IN} ramping up



I_{LED} Precision vs. Input Voltage
L = 10µH, I_{LED} = 1.2A, V_{IN} ramping down



I_{LED} Precision vs. Input Voltage
L = 10µH, I_{LED} = 2A, V_{IN} ramping up



I_{LED} Precision vs. Input Voltage
L = 10µH, I_{LED} = 2A, V_{IN} ramping down



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, I_{LED} = 3A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

I_{LED} Precision vs. Input Voltage
L = 15µH, I_{LED} = 0.75A, V_{IN} ramping up



I_{LED} Precision vs. Input Voltage
L = 15µH, I_{LED} = 0.75A, V_{IN} ramping down



I_{LED} Precision vs. Input Voltage
L = 22µH, I_{LED} = 0.35A, V_{IN} ramping up



I_{LED} Precision vs. Input Voltage
L = 22µH, I_{LED} = 0.35A, V_{IN} ramping down



I_{LED} Precision vs. Input Voltage
L = 33µH, I_{LED} = 0.2A, V_{IN} ramping up



I_{LED} Precision vs. Input Voltage
L = 33µH, I_{LED} = 0.2A, V_{IN} ramping down



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

I_{LED} Precision vs. Inductor Value Variation

V_{IN} = 13.5V, 2 LEDs (V_{LED} = 6V)



I_{LED} Precision vs. Inductor Value Variation

V_{IN} = 13.5V, 1 LED (V_{LED} = 3V)



I_{LED} Precision vs. HS-FET Temperature Sense

2 LEDs (V_{LED} = 6V)



I_{LED} Precision vs. LS-FET Temperature Sense

2 LEDs (V_{LED} = 6V)



V_{IN} Slowly Ramps Up and Down

2 LEDs (V_{LED} = 6V), I_{LED} = 1.2A, V_{IN} = 0V to 20V, 0.001V/ms



V_{IN} Slowly Ramps Up and Down

1 LED (V_{LED} = 3V), I_{LED} = 1.2A, V_{IN} = 0V to 20V, 0.001V/ms



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, f_{SW} = 410kHz, L = 10µH, PWM dimming: 30Hz/5ms, with EMI filters, T_A = 25°C, unless otherwise noted. (8)

CISPR25 Class 5 Peak Conducted Emissions

150kHz to 108MHz



CISPR25 Class 5 Average Conducted Emissions

150kHz to 108MHz



CISPR25 Class 5 Peak Radiated Emissions

150kHz to 30MHz



CISPR25 Class 5 Average Radiated Emissions

150kHz to 30MHz



CISPR25 Class 5 Peak Radiated Emissions

Horizontal, 30MHz to 200MHz



CISPR25 Class 5 Average Radiated Emissions

Horizontal, 30MHz to 200MHz



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, f_{SW} = 410kHz, L = 10µH, PWM dimming: 30Hz/5ms, with EMI filters, T_A = 25°C, unless otherwise noted. (8)

CISPR25 Class 5 Peak Radiated Emissions

Vertical, 30MHz to 200MHz



CISPR25 Class 5 Average Radiated Emissions

Vertical, 30MHz to 200MHz



CISPR25 Class 5 Peak Radiated Emissions

Horizontal, 200MHz to 1GHz



CISPR25 Class 5 Average Radiated Emissions

Horizontal, 200MHz to 1GHz



CISPR25 Class 5 Peak Radiated Emissions

Vertical, 200MHz to 1GHz



CISPR25 Class 5 Average Radiated Emissions

Vertical, 200MHz to 1GHz



Note:

8) The MPQ7230 buck mode EMC test results are based on the application circuit with EMI filters in Figure 9 on page 50.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

Efficiency vs. Input Voltage

2 LEDs (V_{LED} = 6V), L = 10µH



Efficiency vs. Input Voltage

1 LED (V_{LED} = 3V), L = 10µH



Efficiency vs. Input Voltage

2 LEDs (V_{LED} = 6V), L = 15µH



Efficiency vs. Input Voltage

1 LED (V_{LED} = 3V), L = 15µH



Case Temperature Rise vs. Input Voltage

2 LEDs (V_{LED} = 6V)



Case Temperature Rise vs. Input Voltage

1 LED (V_{LED} = 3V)



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

Case Temperature Rise vs. Input Voltage

2 LEDs (V_{LED} = 6V),
PWM dimming: 30Hz/5ms



Case Temperature Rise vs. Input Voltage

1 LED (V_{LED} = 3V),
PWM dimming: 30Hz/50ms



Steady State

I_{LED} = 3A



Start-Up through VIN

I_{LED} = 3A



Shutdown through VIN

I_{LED} = 3A



Start-Up through EN

I_{LED} = 3A



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

Shutdown through EN

I_{LED} = 3A



PWM Dimming Steady State

Dimming frequency = 10Hz/5ms



PWM Dimming Steady State

Dimming frequency = 30Hz/5ms



PWM Dimming Steady State

Dimming frequency = 60Hz/5ms



PWM Dimming Steady State

Dimming frequency = 120Hz/3ms



PWM Dimming Steady State

Dimming frequency = 2kHz/50%



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

PWM Dimming
Start-up through VIN



PWM Dimming
Shutdown through VIN



No Dimming
LED open input start-up



No Dimming
LED open entry



PWM Dimming
LED open input start-up



PWM Dimming
LED open entry



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

No Dimming
LED+ short LED- start-up



No Dimming
LED+ short LED- entry



PWM Dimming
LED+ short LED- start-up



PWM Dimming
LED+ short LED- entry



IREF Short Fault before IC Starts Up



IREF Open Fault before IC Starts Up



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

IREF Short Fault after IC Starts Up



IREF Open Fault after IC Starts Up



IREF Short Fault after IC Starts Up

PWM dimming



IREF Open Fault after IC Starts Up

PWM dimming



ISET Short Fault before IC Starts Up



ISET Open Fault before IC Starts Up



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck mode, 2 LEDs in series (V_{LED} = 6V), V_{IN} = 13.5V, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

ISET Short Fault after IC Starts Up



ISET Open Fault after IC Starts Up



ISET Short Fault after IC Starts Up
PWM dimming



ISET Open Fault after IC Starts Up
PWM dimming



Incorrect Mode Detection during VIN Start-Up



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

I_{LED} Part to Part Variation
T_J = 25°C to +100°C



I_{LED} Part to Part Variation
T_J = -40°C to +150°C



I_{LED} Precision vs. Input Voltage
L = 10µH, I_{LED} = 1.2A, V_{IN} ramping up



I_{LED} Precision vs. Input Voltage
L = 10µH, I_{LED} = 1.2A, V_{IN} ramping down



I_{LED} Precision vs. Input Voltage
L = 10µH, I_{LED} = 1A, V_{IN} ramping up



I_{LED} Precision vs. Input Voltage
L = 10µH, I_{LED} = 1A, V_{IN} ramping down



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.













MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

I_{LED} Precision vs. Inductor Value Variation

V_{IN} = 13.5V, 4 LEDs (V_{LED} = 12V)



I_{LED} Precision vs. Inductor Value Variation

V_{IN} = 13.5V, 3 LEDs (V_{LED} = 9V)



I_{LED} Precision vs. Junction Temperature

4 LEDs (V_{LED} = 12V)



I_{LED} Precision vs. Junction Temperature

4 LEDs (V_{LED} = 12V)



V_{IN} Slowly Ramps Up and Down

4 LEDs (V_{LED} = 12V), I_{LED} = 1.2A, V_{IN} = 0V to 20V, 0.001V/ms



V_{IN} Slowly Ramps Up and Down

3 LEDs (V_{LED} = 9V), I_{LED} = 1.2A, V_{IN} = 0V to 20V, 0.001V/ms



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, PWM dimming: 30Hz/5ms, with EMI filters, T_A = 25°C, unless otherwise noted. (9)

CISPR25 Class 5 Peak Conducted Emissions

150kHz to 108MHz



CISPR25 Class 5 Average Conducted Emissions

150kHz to 108MHz



CISPR25 Class 5 Peak Radiated Emissions

150kHz to 30MHz



CISPR25 Class 5 Average Radiated Emissions

150kHz to 30MHz



CISPR25 Class 5 Peak Radiated Emissions

Horizontal, 30MHz to 200MHz



CISPR25 Class 5 Average Radiated Emissions

Horizontal, 30MHz to 200MHz



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, PWM dimming: 30Hz/5ms, with EMI filters, T_A = 25°C, unless otherwise noted. (9)

CISPR25 Class 5 Peak Radiated Emissions
Vertical, 30MHz to 200MHz



CISPR25 Class 5 Average Radiated Emissions
Vertical, 30MHz to 200MHz



CISPR25 Class 5 Peak Radiated Emissions
Horizontal, 200MHz to 1GHz



CISPR25 Class 5 Average Radiated Emissions
Horizontal, 200MHz to 1GHz



CISPR25 Class 5 Peak Radiated Emissions
Vertical, 200MHz to 1GHz



CISPR25 Class 5 Average Radiated Emissions
Vertical, 200MHz to 1GHz



Note:

9) The MPQ7230 buck-boost mode EMC test results are based on the application circuit with EMI filters in Figure 10 on page 50.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

Efficiency vs. Input Voltage

3 LEDs (V_{LED} = 9V), L = 10µH



Efficiency vs. Input Voltage

4 LEDs (V_{LED} = 12V), L = 10µH



Efficiency vs. Input Voltage

3 LEDs (V_{LED} = 9V), L = 15µH



Efficiency vs. Input Voltage

4 LEDs (V_{LED} = 12V), L = 15µH



Case Temperature Rise vs. Input Voltage

3 LEDs (V_{LED} = 9V), L = 10µH



Case Temperature Rise vs. Input Voltage

4 LEDs (V_{LED} = 12V), L = 10µH



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

Steady State

I_{LED} = 1.2A



Start-Up through VIN

I_{LED} = 1.2A



Shutdown through VIN

I_{LED} = 1.2A



Start-Up through EN

I_{LED} = 1.2A



Shutdown through EN

I_{LED} = 1.2A



PWM Dimming Steady State

Dimming frequency = 10Hz/5ms



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

PWM Dimming Steady State
Dimming frequency = 30Hz/5ms



PWM Dimming Steady State
Dimming frequency = 60Hz/5ms



PWM Dimming Steady State
Dimming frequency = 120Hz/5ms



PWM Dimming Steady State
Dimming frequency = 2kHz/50%



PWM Dimming
Start-up through VIN



PWM Dimming
Shutdown through VIN



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

No Dimming
LED open input start-up



No Dimming
LED open entry



PWM Dimming
LED open input start-up



PWM Dimming
LED open entry



No Dimming
LED+ short LED- start-up



No Dimming
LED+ short LED- entry



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

PWM Dimming
LED+ short LED- start-up



PWM Dimming
LED+ short LED- entry



IREF Short Fault before IC Starts Up



IREF Open Fault before IC Starts Up



IREF Short Fault after IC Starts Up



IREF Open Fault after IC Starts Up



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

IREF Short Fault after IC Starts Up

PWM dimming



IREF Open Fault after IC Starts Up

PWM dimming



ISET Short Fault before IC Starts Up



ISET Open Fault before IC Starts Up



ISET Short Fault after IC Starts Up



ISET Open Fault after IC Starts Up



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS *(continued)*

Buck-boost mode, 4 LEDs in series (V_{LED} = 12V), V_{IN} = 13.5V, I_{LED} = 1.2A, f_{SW} = 410kHz, L = 10µH, T_A = 25°C, unless otherwise noted.

ISET Short Fault after IC Starts Up

PWM dimming



ISET Open Fault after IC Starts Up

PWM dimming



Incorrect Mode Detection during VIN Start-Up



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

FUNCTIONAL BLOCK DIAGRAM



Figure 3: Functional Block Diagram

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

OPERATION

The MPQ7230 is a fixed-frequency, synchronous, rectified, buck or buck-boost, switch-mode LED driver with built-in power MOSFETs. The device offers a very compact solution to achieve 1.2A of continuous output current in a buck-boost topology and 3A in a buck topology. It also provides excellent load and line regulation across the 6V to 42V input supply range.

Fixed Frequency Band-Band Control

The MPQ7230 use fixed frequency band-band control with a spread spectrum technique to reduce EMC noise. When compared to fixed-frequency PWM control, band-band control offers the advantages of simpler control loop and faster transient response. Even without an output capacitor, the loop is stable. Band-band control compares the inductor current to two internal thresholds: $I_{BANDPEAK}$ and $I_{BANDVALLEY}$.

When the inductor current exceeds $I_{BANDPEAK}$, the high-side MOSFET (HS-FET) turns off. When the inductor current drops below $I_{BANDVALLEY}$, the HS-FET turns on. ($I_{BANDPEAK}$ + $I_{BANDVALLEY}$) / 2 is controlled by a PID loop to regulate the LED current (I_{LED}). $I_{BANDPEAK}$ - $I_{BANDVALLEY}$ is controlled by a PLL loop to regulate the switching frequency to be about 410kHz. If the minimum on time (t_{ON_MIN}) or minimum off time (t_{OFF_MIN}) is triggered, the switching frequency drops, and the switching frequency can be calculated with (D / t_{ON_MIN}) or [(1 - D) / t_{OFF_MIN}], where D is the required duty cycle. and t_{ON_MIN} and t_{OFF_MIN} are both 80ns maximum.

The additional spread spectrum uses a 15kHz modulation frequency with a triangular profile to spread the internal oscillator frequency across a ±10% nominal switching frequency window.

Middle Point Inductor Current Sense

The MPQ7230 senses I_{LED} by sensing the middle point of the inductor current (I_{LMID}). I_{LMID} is sensed through the HS-FET or low-side MOSFET (LS-FET) depending on the duty cycle. I_{LMID} is sensed through the HS-FET when the duty exceeds D_{TH_H} (55% in buck mode or 60% in buck-boost mode), or it is sensed through LS-FET when the duty cycle is below D_{TH_L} (45% in buck mode or 40% in buck-boost mode). A duty cycle hysteresis (D_{TH_HYS}, 10% in buck or 20% in buck-boost) prevents the current sense from switching between HS-FET and LS-FET at critical duty cycles (see Figure 4).



Figure 4: Current-Sense MOSFET vs. Duty Cycle

I_{LED} is equal to I_{LMID} in buck topologies. The LED current is equal to I_{LMID} x V_{IN} / (V_{IN} + V_{OUT}) in buck-boost topologies.

Selecting Buck Mode or Buck-Boost Mode

The MPQ7230 can be configured to a buck or buck-boost topology by connecting a different resistor (R_{IREF}) at the IREF pin. I_{LMID} is sensed through the sensing FET. I_{LED} is equal to I_{LMID} in buck topologies, while it is equal to I_{LMID} x V_{IN} / (V_{IN} + V_{OUT}) in buck-boost topologies.

Mode detection starts when V_{CC} reaches its under-voltage lockout (UVLO) threshold (about 4.7V). A 240μA current source (I_{IREF_DET}) flows from the IREF pin to detect the resistor's voltage value during start-up. If the voltage generated by I_{IREF_DET} x R_{IREF} < 2.6V, buck-boost mode is selected. Buck mode is selected when I_{IREF_DET} x R_{IREF} > 2.8V. This means that the corresponding R_{IREF} for buck-boost mode is ≤9.09kΩ, or ≥14.7kΩ for buck mode. To avoid an IREF short fault in buck-boost mode, set the resistor between 1.05kΩ and 9.09kΩ. To avoid an IREF open fault in buck mode, set the resistor between 14.7kΩ and 80.6kΩ.

Once detection finishes, the mode is latched, and I_{IREF} (0.57V / R_{IREF}) becomes the reference for the NTC pin current. The latched mode signal is reset by V_{CC} UVLO, but it cannot be reset by pulling EN low. An internal 1MHz filter works with the 250μs deglitch time to protect the part from false mode detection, which can be caused by noise coupling at the pin. To ensure that the detected mode is consistent with the real topology connection, the V_{INGND} - V_{PGND} voltage

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

is monitored. If the mode is detected as buck mode while V_{INGND} - V_{PGND} exceeds 1.35V, the part latches off and FAULT asserts low. If the mode is detected as buck-boost mode while V_{INGND} - V_{PGND} is below 1.35V (detected as an output under-voltage (UV) condition), the part latches off and FAULT asserts low.

Internal Regulator

The 5.1V internal regulator (VCC) powers most of the internal circuitries. VCC rises after V_{IN} reaches its rising UVLO threshold, regardless of whether EN is high or low. VCC is a reference to PGND/AGND, but not INGND. This means that INGND is not the reference ground for VCC in buck-boost mode.

A lower-value VCC capacitor can cause VCC voltage ringing and lead to unstable switching. It is recommended to place a ≥3µF decoupling ceramic capacitor at the VCC pin. When choosing the capacitor, consider the capacitance derating to ensure that the capacitance exceeds or is equal to 3µF. A 10µF capacitor with X7R dielectrics and a ≥10V DC voltage rating is recommended. V_{CC} has its own UVLO threshold, with a 4.7V rising threshold and a 4.05V falling threshold. Besides powering internal circuitries, VCC can also power external circuitries in the system with a current capability of 25mA.

Continuous Conduction Mode (CCM) and Discontinuous Conduction Mode (DCM)

The MPQ7230 uses continuous conduction mode (CCM) to ensure that the part works with a fixed frequency from the minimum load to full-load range. The advantages of CCM are its controllable frequency and lower output ripple under light loads. When $I_{BANDVALLEY}$ = 0A, the MPQ7230 enters discontinuous conduction mode (DCM). In DCM, the LS-FET acts as an ideal diode. Ensure that the part does not enter DCM mode, even during start-up or power derating, by selecting an appropriate inductor. Otherwise, LED current precision cannot be guaranteed.

Enable Control (EN)

EN is a control pin that turns the LED driver on and off. Drive V_{EN} - V_{INGND} above 1.6V to turn on the regulator; drive it below 0.6V to turn the part off and reset FAULT.

Connect EN to VIN through a resistor in both buck and buck-boost mode. If the enable function is not required in buck mode, connect EN to VCC. EN can be floated to shut down the chip due to the internal 1MΩ resistor connected from EN to INGND. An integrated Zener diode is placed in parallel with the EN pin to clamp its voltage to about 7V. This internal Zener diode can handle a 1mA current for load dump voltages up to 100V when a 100kΩ resistor is connected between the car battery (VBAT) and EN.

ISET

The LED average current can be configured by a resistor (R_{ISET}) connected at the ISET pin. The LED current (I_{LED}) can be calculated with Equation (1):

$$I_{LED}\ (A) = 16 / R_{ISET}\ (k\Omega) \quad (1)$$

The nominal voltage (V_{ISET}) of the ISET pin is about 0.592V. V_{ISET} can be adjusted below 0.592V to decrease the LED current in power derating or thermal derating.

During the mode detection period at start-up in buck mode, the ISET current is monitored to detect if I_{LED} is above or below 600mA. If I_{ISET} > 22.2µA during this period, I_{LED} is detected to be >600mA, and the MOSFETs fully turn on. If I_{LED} is detected to be <600mA, half of the LS-FETs and HS-FETs turn off to improve current-sense accuracy. When the MOSFETs cut off by half, the current limit drops from 6.3A to 3.15A. The signal that indicates if I_{LED} is above or below 600mA is latched once the detection finishes. This signal can only be reset by V_{CC} UVLO. After LED current detection, the MOSFET's $R_{DS(ON)}$ does not change, even if I_{LED} rises above or falls below 600mA. The MOSFET is fully on in buck-boost mode, and the current limit stays at 6.3A.

During normal operation, the ISET pin is continuously monitored to detect open or short to GND conditions. If the ISET rises above this threshold, the device detects a short to ground condition.

If I_{LED} is set below 600mA, the ISET current threshold for short detection is 120µA (corresponding to a 4.9kΩ resistor or 3.24A I_{LED}). If the LED current is set above 600mA, the threshold is 220µA (corresponding to a 2.7kΩ resistor or 5.9A I_{LED}).

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

When ISET current is lower than 1.4μA (corresponding to 428kΩ resistor or 37.3mA ILED), pin open will be detected.

The part latches off once the ISET pin detects a short or open fault, regardless of whether FAULT asserts or not. FAULT asserts low immediately if an ISET short or open condition is detected after start-up. There is a 20ms to 45ms delay for FAULT assertion if a short or open condition is detected during start-up.

IREF

The IREF pin configures the device for buck mode or buck-boost mode, then it sets the current in the external NTC. After mode detection finishes, the voltage on the IREF pin (V_{IREF}) is set to 0.57V with a 10.5% tolerance. Connect a resistor between IREF and GND to obtain a current (I_{IREF}) equal to 0.57V / R_{IREF}. This current is used as a reference current for the NTC's current source. Note that the NTC current is 50 x I_{IREF} in buck mode and 5 x I_{IREF} in buck-boost mode.

The IREF pin is continuously monitored to detect open and short to GND conditions. If the IREF current exceeds 85μA in buck mode (corresponding to a 6.7kΩ resistor) or 800μA in buck-boost mode (corresponding to a 0.71kΩ resistor), the pin detects a short to GND condition. If the IREF current is below 3μA in buck mode (corresponding to a 190kΩ resistor) or 40μA in buck-boost mode (corresponding to a 14.7kΩ resistor), the pin detects an open fault.

The part latches off once the IREF pin detects a short or open condition, regardless of whether FAULT asserts. FAULT asserts low immediately if a short or open fault occurs after start-up. There is a 20ms to 45ms delay for FAULT assertion if a short or open condition is detected during start-up.

PWM Dimming

An external 10Hz to 2kHz PWM waveform can be applied to the DIM pin to implement PWM dimming. The part stops switching when DIM drops below 0.7V and I_{LED} is zero. The device resumes normal operation with the nominal LED current when DIM exceeds 1.6V. The average LED current is proportional to the PWM duty.

Note that DIM should be high for longer than 100μs. Otherwise, the part may stop switching and latch due to an LED open condition. To avoid this, the DIM voltage should not be low for longer than 100ms.

Under-Voltage Lockout (UVLO)

Under-voltage lockout (UVLO) protects the chip from operating at an insufficient supply voltage. Both (V_{IN} - V_{INGND}) and V_{CC} have UVLO thresholds. V_{IN} - V_{INGND} UVLO has a 6V rising threshold with a 1.1V hysteresis. V_{CC} UVLO has a 4.7V rising threshold with a 0.65V hysteresis. V_{IN} and V_{CC} UVLO do not trigger FAULT.

Fault Detection and Indicator

The MPQ7230 has fault indication. The FAULT pin is the open drain of a MOSFET. FAULT is pulled to VIN through a 300kΩ resistor, and it is pulled to INGND with a 4MΩ pull-down resistor. FAULT is pulled high during normal operation. FAULT pulls low if one of the following occurs: LED short, LED open, thermal shutdown, false mode detection, and over-current protection (OCP). FAULT also asserts if the ISET or IREF pins experience a short or open fault during start-up.

The MPQ7230 senses the output voltage (V_{OUT}) by monitoring SW's average voltage in buck mode, or INGND's voltage in buck-boost mode. If an LED+ short to LED- or LED+ short to GND occurs, V_{OUT} drops below the under voltage (UV) threshold. Then a short circuit is detected, and FAULT indicates the fault.

FAULT asserts in buck-boost mode if one of the following occurs: LED+ short to battery, LED open, and output over-voltage (OV) condition. FAULT also asserts if HS-FET's current is low. This low current threshold is 60mA when I_{LED} is below 600mA; otherwise, the threshold is 120mA.

In buck mode, low current detection is disabled when V_{IN} drops below 7.5V to keep the part from latching under cold-crank conditions. In buck-boost mode, FAULT does not assert under the following conditions: if LED+ (or INGND) short to battery occurs, or V_{IN} - V_{INGND} drops below its UV. If LED- (or PGND) is shorted to INGND, or V_{INGND} falls below its UV threshold, FAULT asserts. If there is an LED open condition, V_{INGND} exceeds its OV threshold, and FAULT asserts.

In case of higher temperatures, the part operates with a reduced current. The device only stops operating when the internal temperature reaches

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

the over-temperature protection (OTP) threshold (about 170°C), then FAULT asserts.

If a fault occurs, the part stops switching, and the FAULT output asserts after 20µs. Then the part latches. During the latch, VCC is still present, and the part consumes <2mA of current.

The FAULT pin can only can be reset by V_{CC} UVLO. At start-up, the FAULT pin is not activated, and it remains inactive to 20ms. FAULT activates within 45ms to avoid any false functions when multiple FAULT pins are connected to one another and share the same EN signal. Individual parts are self-protected and latch off immediately if a fault condition is detected, regardless of whether FAULT asserts.

The FAULT pin can withstand 30mA of current, and it protects itself even if it experiences a short or a high voltage. At lower voltages (typically <1.6V), the FAULT sink current increases to enhance the pull-down capability. Figure 5 shows the detailed FAULT sink current when the pin is pulled low at different voltages.



Figure 5: FAULT Sink Current vs. FAULT Voltage

In PWM dimming, fault conditions will not be detected correctly when the dimming ON time is below 100µs. So make sure that the dimming ON time is always higher than 100µs to ensure that the fault detection operates correctly.

Table 1: Fault Detection (10)

Fault Conditions	Detection	
	Buck	Buck-Boost
LED+ short to LED-	V_{OUT} UV (V_{OUT} < 1.1V)	INGND UV (V_{INGND} - V_{PGND} < 1.35V) (12)
LED+ short to PGND	V_{OUT} UV (V_{OUT} < 1.1V)	INGND UV (V_{INGND} - V_{PGND} < 1.35V) (12)
LED+ short to INGND	V_{OUT} UV (V_{OUT} < 1.1V)	Normal Condition
LED+ short to battery	Low LED current (I_{HS} < 60mA when $I_{LED_SETTING}$ < 600mA; I_{HS} < 120mA when $I_{LED_SETTING}$ > 600mA)	FAULT does not assert (V_{IN} - V_{INGND} UVLO)
LED- short to INGND	Normal conditions	INGND UV (V_{INGND} - V_{PGND} < 1.35V) (12)
LED- short to battery	FAULT does not assert (V_{IN} - V_{INGND} UVLO)	FAULT does not assert (V_{IN} - V_{INGND} UVLO)
LED open	Low LED current (I_{HS} < 60mA when $I_{LED_SETTING}$ < 600mA, I_{HS} < 120mA when $I_{LED_SETTING}$ > 600mA)	INGND OV (V_{INGND} - V_{PGND} > 18V)
Incorrect mode detection	V_{INGND} - V_{PGND} > 1.35V	INGND UV (V_{INGND} - V_{PGND} < 1.35V)
OTP	T_J > 170°C or V_{NTC} < 0.37V for >256µs	
ISET short (12)	I_{ISET} > 120µA when $I_{LED_SETTING}$ < 600mA; I_{ISET} > 220µA when $I_{LED_SETTING}$ > 600mA	I_{ISET} > 120µA
ISET open (12)	I_{ISET} < 1.4µA	
IREF short (12)	I_{IREF} > 85µA	I_{IREF} > 800µA
IREF open (12)	I_{IREF} < 3µA	I_{IREF} < 40µA
OCP	Current limit triggered 3 times continuously	

Notes:

10) Once a fault in the table is detected, the part latches and FAULT is asserted, unless otherwise noted.
11) FAULT may glitch if INGND - PGND is pulled below -0.3V when an LED+ short to LED- fault occurs with a long cable.
12) The part latches when the ISET or IREF pins experience a short or open fault before or after start-up when FAULT is pulled low.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

Over-Current Protection (OCP)

The MPQ7230 has cycle-by-cycle peak current-limit protection. The inductor current is monitored while the HS-FET is on. If the inductor current exceeds the current limit value (about 6.3A when I_{LED} is set above 600mA, or 3.15A when I_{LED} is below 600mA), the HS-FET turns off immediately. Then the LS-FET turns on to discharge the energy, and the inductor current decreases. The HS-FET remains off unless the inductor current reaches the zero current detection (ZCD) threshold. Then another HS-FET on cycle begins. If the over-current condition remains after three cycles, the part latches off and reports a failure with FAULT.

Load Dump Protection

The MPQ7230's internal MOSFETs have a 50V absolute maximum rating, and the operating voltage can be up to 42V. In buck mode, the maximum voltage can handle load dump conditions up to 42V. In buck-boost mode, the voltage difference between VIN and PGND is equal to the car battery's voltage plus the LED voltage.

Under load dumps, the voltage can rise above the maximum value. To protect the device from load dumps in buck-boost mode, the MPQ7230 stops switching when V_{IN} - V_{PGND} rises above 40V. Then a 100mA sink current at INGND is activated to discharge the output voltage, so that the MOSFET only supports V_{IN} voltage stress. The device automatically restarts when V_{IN} - V_{PGND} drops back to 39V. Load dump protection does not trigger faults, and this protection is not active in buck mode. Load dump protection can reset FAULT after another fault occurs, but it cannot the reset a latch-off state.

Power Derating

When V_{IN} falls below a threshold (about 7V) in buck-boost mode, the power derating starts, and I_{LED} linearly drops with V_{IN}, similar to analog dimming. The derating continues until V_{IN} UVLO occurs, with a -29% derating ratio at UVLO. During start-up, power derating is activated in buck-boost mode, but it is disabled in buck mode.

Thermal Derating through NTC

Connecting a NTC resistor network (R_{NTC}) to the NTC pin drops the output current via analog dimming when the sensed temperature rises above a configured value. The current source (I_{NTC}) is 50 x I_{IREF} in buck mode, or 5 x I_{IREF} in buck-boost mode. I_{IREF} flows out the NTC pin and generates a voltage (V_{NTC}) that is equal to I_{NTC} x R_{NTC}). V_{NTC} is sensed to indicate the real temperature and determine the dimming ratio.

When V_{NTC} exceeds 1.25V, there is no dimming. To avoid activating the NTC function, pull the NTC pin above 1.25V, or pull it to VCC. When V_{NTC} is lower than 1.2V, dimming is activated and the dimming ratio decreases as V_{NTC} decreases. The dimming ratio drops by a step of 2% when V_{NTC} drops by 30mV. When V_{NTC} drops from 1.25V to 0.5V, the dimming ratio drops to 50%, and the LED average current drops to 50% of the set value accordingly. The LED current does not drop below 50%, even if V_{NTC} is below 0.5V. The device triggers OTP if V_{NTC} drops below 0.4V for longer than 256µs. The device stops switching and does not recover until V_{NTC} rises back to 0.5V. FAULT does not assert for this event.

Thermal Shutdown (TSD)

Thermal shutdown prevents the chip from operating at exceedingly high temperatures. If the die temperature exceeds 170°C, the entire chip shuts down and FAULT is asserted. Restart the device with a power-on restart, or by resetting EN.

Floating Driver and Bootstrap Charging

An external bootstrap capacitor powers the floating power MOSFET driver. The bootstrap capacitor voltage is charged to about 5V from VCC through the pass transistor when the LS-FET is on. This floating driver has its own UVLO protection, with a rising threshold of 2.5V and a hysteresis of 700mV. When the BST-to-SW voltage drops to 2.2V, the LS-FET is forced on to refresh the BST voltage.

A 22nF to 220nF ceramic capacitor is recommended for the bootstrap capacitor. The capacitance should have a derating for the DC voltage and temperature. Consider this derating when choosing the capacitor to ensure that the real capacitance is between 22nF and 200nF. A maximum 22Ω resistor can be placed in series with the bootstrap capacitor to reduce the SW spike voltage.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

APPLICATION INFORMATION

Buck and Buck-Boost Mode Selection

The operation mode can be configured by connecting a different resistor (R_{IREF}) at the IREF pin. Select a 1.05kΩ ≤ R_{IREF} ≤ 9.09kΩ for buck-boost mode, or a 80.6kΩ ≥ R_{IREF} ≥ 14.7kΩ for buck mode.

Setting the LED Current

The external resistor (R_3) connected to the ISET pin sets the LED current (I_{LED}). R_3 can be calculated with Equation (2):

$$R_3 = \frac{16}{I_{LED}(A)}(k\Omega) \quad (2)$$

Table 2 shows the recommended values for R_3.

Table 2: Resistor Selection for Common LED Currents

I_{LED} (A)	R_3 (kΩ)
3	5.36
2	8
1.2	13.3
0.75	21.1

If I_{LED} is below 0.7A in buck-boost mode, certain resistors are recommended (see Table 3).

Table 3: Resistor Selection when I_{LED} ≤ 700mA in Buck-Boost Mode

I_{LED} (A)	R_3 (kΩ)
0.7	22.6
0.65	24.4
0.6	26.3
0.55	28.6
0.5	31.5
0.45	34.9
0.4	39.1

Figure 6 shows the relationship between I_{LED} and R_{ISET} in buck-boost mode.



Figure 6: I_{LED} vs. R_{ISET} when I_{LED} ≤ 700mA in Buck-Boost Mode

Selecting the Inductor

For most applications, use an inductor ranging between 4.7µH and 33µH with a DC current rating higher than the maximum inductor current. Consider the inductor's DC resistance when estimating the output current and the inductor's power consumption.

For buck converter designs, estimate the required inductance value with Equation (3):

$$L = \frac{V_{OUT} \times (V_{IN} - V_{OUT})}{V_{IN} \times \Delta I_L \times f_{SW}} \quad (3)$$

Choose the inductor ripple current to be higher than 20% of the LED current. The inductor peak current can be calculated with Equation (4):

$$I_{L_PEAK} = I_{L_AVG} + \frac{\Delta I_L}{2} \quad (4)$$

Where I_{L_AVG} is the average current through the inductor, which is equal to the output load current (LED current) in buck applications. Under light-load conditions, use a larger-value inductor to improve efficiency and current precision. Table 4 shows the recommended inductor values in buck mode with common LED currents.

Table 4: Buck Mode Inductor Value for Common LED Currents

I_{LED} (A)	Recommended Inductor Value (µH)
(1A, 3A]	10
(0.5A, 1A]	15
(0.3A,0.5A]	22
[0.2A, 0.3A]	33

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

For buck-boost converter designs, estimate the required inductance value with Equation (5):

$$L = \frac{V_{OUT} \times V_{IN}}{(V_{OUT} + V_{IN}) \times \Delta I_L \times f_{SW}} \quad (5)$$

Where ΔI_L is the inductor peak-to-peak current ripple. Set ΔI_L to be over 25% of the inductor average current when I_{LED} > 0.7A, and set it to be over 20% of the inductor average current when I_{LED} < 0.7A. I_{L_AVG} can be calculated with Equation (6):

$$I_{L_AVG} = I_{LED} \times (1 + \frac{V_{OUT}}{V_{IN}}) \quad (6)$$

The inductor's peak current can be calculated with Equation (7):

$$I_{L_PEAK} = I_{L_AVG} + \frac{1}{2} \times \Delta I_L \quad (7)$$

Under light-load conditions, use a larger-value inductor to improve efficiency and current precision. Table 5 shows the recommended inductor values in buck-boost mode with common LED currents.

Table 5: Buck-Boost Mode Inductor Value for Common LED Currents

I_{LED} (A)	Recommended Inductor Value (µH)
(0.75A, 1.2A]	10
(0.5A, 0.75A]	15
(0.3A, 0.5A]	22
[0.2A, 0.3A]	33

Selecting the Input Capacitor

The input current in buck and buck-boost mode is discontinuous, and requires a capacitor to supply AC current to the converter while maintaining the DC input voltage. For the best performance, use low-ESR capacitors. Ceramic capacitors with X7R dielectrics are highly recommended because of their low ESR and small temperature coefficients.

For most applications, use a 4.7µF to 22µF capacitor. The input capacitor can be electrolytic, tantalum, or ceramic. When using electrolytic or tantalum capacitors, it is recommended to use another lower-value capacitor (e.g. 0.1µF) with a small package size (0603) to absorb high-frequency switching noise. Place the smaller capacitor as close to VIN and GND (INGND is connected to PGND in buck mode, but the capacitor should be close to both INGND and PGND in buck-boost mode) as possible.

Since C_{IN} absorbs the input switching current in buck mode, it requires an adequate ripple current rating. The RMS current in the input capacitor can be estimated with Equation (8):

$$I_{CIN} = I_{LOAD} \times \sqrt{\frac{V_{OUT}}{V_{IN}} \times (1 - \frac{V_{OUT}}{V_{IN}})} \quad (8)$$

The worst-case condition occurs at V_{IN} = 2 x V_{OUT}, calculated with Equation (9):

$$I_{CIN} = \frac{I_{LOAD}}{2} \quad (9)$$

For simplification, choose an input capacitor with an RMS current rating greater than half of the maximum load current. The input voltage ripple caused by the capacitance can be estimated with Equation (10):

$$\Delta V_{IN} = \frac{I_{LOAD}}{f_{SW} \times C_{IN}} \times \frac{V_{OUT}}{V_{IN}} \times (1 - \frac{V_{OUT}}{V_{IN}}) \quad (10)$$

At buck-boost mode, if the $I_{BANDVALLEY} \geq I_{LED}$, the capacitance can be calculated with Equation (11):

$$\Delta V_{IN} = \frac{I_{LED} \times V_{OUT}}{(V_{IN} + V_{OUT}) \times f_{SW} \times C_{IN}} \quad (11)$$

In buck-boost mode, the capacitor between VIN and PGND must consider VCC regulator stability. When (V_{INGND} - V_{PGND}) > 5.1V, the input of the VCC regulator switches to V_{INGND} to reduce power loss. A 2.2µF to 10µF/50V X7R ceramic capacitor should be placed between VIN to PGND to keep VCC stable when the VCC charging source changes from VIN to INGND. Place a symmetric 4.7µF/50V, X7R ceramic capacitor between VIN and PGND.

Selecting the Output Capacitor

The output capacitor maintains the DC output voltage. Ceramic, tantalum, or low-ESR electrolytic capacitors are recommended. For the best results, use low-ESR capacitors to keep the output voltage ripple low.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

In buck mode, the output voltage ripple can be estimated with Equation (12):

$$\Delta V_{OUT} = \frac{V_{OUT}}{f_{SW} \times L} \times (1 - \frac{V_{OUT}}{V_{IN}}) \times (R_{ESR} + \frac{1}{8 \times f_{sw} \times C_{OUT}}) \quad (12)$$

Where L is the inductor value, and R_{ESR} is the equivalent series resistance (ESR) value of the output capacitor. For ceramic capacitors, the capacitance dominates the impedance at the switching frequency, and the capacitance causes the majority of the output voltage ripple. For simplification, the output voltage ripple can be estimated with Equation (13):

$$\Delta V_{OUT} = \frac{V_{OUT}}{8 \times f_{SW}^{2} \times L \times C_{OUT}} \times (1 - \frac{V_{OUT}}{V_{IN}}) \quad (13)$$

For tantalum or electrolytic capacitors, the ESR dominates the impedance at the switching frequency. For simplification, the output ripple can be approximated with Equation (14):

$$\Delta V_{OUT} = \frac{V_{OUT}}{f_{SW} \times L} \times (1 - \frac{V_{OUT}}{V_{IN}}) \times R_{ESR} \quad (14)$$

For buck-boost applications, if the $I_{BandValley}$ ≥the I_{LED}, the output capacitor can be selected using Equation (15):

$$\Delta V_{OUT} = I_{LED} \times (R_{ESR} + \frac{V_{OUT}}{f_{sw} \times C_{OUT} \times (V_{IN} + V_{OUT})}) \quad (15)$$

For tantalum or electrolytic capacitors, the ESR dominates the impedance at the switching frequency. For simplification, the output ripple can be approximated with Equation (16):

$$\Delta V_{OUT} = I_{LED} \times R_{ESR} \quad (16)$$

A 2.2µF to 10µF ceramic capacitor is sufficient for most applications.

Selecting the Diode from PGND to INGND in Buck-Boost Mode

In buck-boost mode, place a Schottky diode between INGND and PGND to handle the charge current for the VIN to PGND capacitor, especially when V_{IN} has a high slew rate. When (V_{INGND} - V_{PGND}) < 5.1V, VCC is powered from VIN. In this scenario, the VCC charge current flows from the VCC capacitor to PGND, then back to INGND and the car battery. A Schottky diode with a low forward voltage (V_F) (about 0.32V), a minimum 1A current rating, and a VRRM voltage exceeding 20V is sufficient. It is recommended to use the PMEG2010EPAS Schottky diode.

Selecting VCC Capacitor

A smaller-value VCC capacitor causes VCC voltage ringing and leads to unstable switching. It is recommended to place a ≥3µF decoupling ceramic capacitor at the VCC pin. When choosing the capacitor, consider the capacitance derating to ensure that the real capacitance is ≥3µF. A 10µF capacitor with X7R dielectrics and a ≥10V DC rated voltage is recommended. VCC is referenced to PGND/AGND.

BST Resistor and Capacitor

It is recommended to place a resistor in series with the BST capacitor to reduce the SW spike voltage. A higher resistance improves SW spike reduction but compromises efficiency. The recommended external BST capacitor value is a 22nF to 220nF ceramic capacitor with a 10V/16V DC derating. A maximum 22Ω resistor with a 0603/0402 package is recommended. It is not necessary to use a large resistor package.

In normal operation, the average current flowing through the bootstrap resistor is about 20mA in buck mode and 10mA in buck-boost mode. If the capacitor is short-circuited, the current inside the resistor is limited by the internal LDO. Then the device quickly detects that the LED current is below the low limit, and a failure is detected. Then the part latches off and no more current is sourced to the resistor. A 0402 package can handle the power dissipation on the bootstrap resistor.

Low Dimming Frequency Application

For applications with low PWM dimming frequencies at small dimming duty cycles, the error amplifier's output voltage (V_{COMP}) may be discharged by the leakage if the dimming off time is too long. The minimum dimming frequency should not be below 10Hz.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PCB Layout Guidelines

Efficient PCB layout is critical for stable operation, especially for input capacitor placement. A 4-layer layout is strongly recommended to improve thermal performance. For the best results, refer to Figure 7 and Figure 8 (on page 49) and follow the guidelines below:

1. Use a large ground plane to connect directly to PGND. If the bottom layer is a ground plane, add vias near PGND.
2. Ensure that the high-current paths at PGND and IN have short, direct, and wide traces.
3. Place the ceramic input capacitor, especially the small package (0603) input bypass capacitor, as close to the VIN and PGND pins as possible to minimize high-frequency noise. Keep the connection between the input capacitor and VIN as short and wide as possible.
4. Place the VCC capacitor as close as possible to the VCC and GND pins.
5. Route SW and BST away from sensitive analog areas, such as FB.
6. Place the feedback resistors close to chip to ensure that the trace connected to the FB pin is as short as possible.
7. Use multiple vias to connect the power planes to the internal layers.



Top Layer



Mid-Layer 1



Mid-Layer 2



Bottom Layer

Figure 7: Recommended PCB Layout for Buck Mode (13)

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.



Top Layer



Mid-Layer 1



Mid-Layer 2



Bottom Layer

Figure 8: Recommended PCB Layout for Buck-Boost Mode (14)

Notes:

13) The recommended layout is based on Figure 9 on page 50.
14) The recommended layout is based on Figure 10 on page 50.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

TYPICAL APPLICATION CIRCUITS



Figure 9: Buck Application Circuit (I_{LED} = 3A)



Figure 10: Buck-Boost Application Circuit (I_{LED} = 1.2A)

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

PACKAGE INFORMATION

QFN-19 (3mmx4mm)
Wettable Flank



TOP VIEW



BOTTOM VIEW



SIDE VIEW



SECTION A-A



RECOMMENDED LAND PATTERN

NOTE:

1) ALL DIMENSIONS ARE IN MILLIMETERS.
2) EXPOSED PADDLE SIZE DOES NOT INCLUDE MOLD FLASH.
3) LEAD COPLANARITY SHALL BE 0.08 MILLIMETERS MAX.
4) JEDEC REFERENCE IS MO-220.
5) DRAWING IS NOT TO SCALE.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

CARRIER INFORMATION



Part Number	Package Description	Quantity/ Reel	Quantity/ Tube	Quantity/ Tray	Reel Diameter	Carrier Tape Width	Carrier Tape Pitch
MPQ7230GLE-AEC1-Z	QFN-19 (3mmx4mm)	5000	N/A	N/A	13in	12mm	8mm

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	10/18/2021	Initial Release	-

Notice: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.