



EVBL4423H-Q-00A

36V, 3A, Synchronous, Step-Down Converter Evaluation Board

DESCRIPTION

The EVBL4423H-Q-00A is an evaluation board designed to demonstrate the MP4423H and the MPQ4423H. The MP4423H is a high-frequency, synchronous, rectified, step-down switch-mode converter with built-in power MOSFETs and an integrated MPS power inductor. It offers a compact solution that can achieve up to 3A of continuous output current (I_{OUT}) across a wide 4V to 36V input voltage (V_{IN}) range, with excellent load and line regulation.

Synchronous mode provides high efficiency across the entire I_{OUT} range. Current-mode control provides fast transient response and eases loop stabilization.

Full protection features include over-current protection (OCP) with hiccup mode and thermal shutdown.

The EVBL4423H-Q-00A is a fully assembled and tested evaluation board. The MP4423H is available in a QFN-8 (3mmx3mm) package.

ELECTRICAL SPECIFICATIONS

Parameter	Symbol	Value	Units
Input voltage	V_{IN}	4 to 36	V
Output voltage	V_{OUT}	3.3	V
Output current	I_{OUT}	3	A

FEATURES

- Wide 4V to 36V Operating Input Voltage (V_{IN}) Range
- 85mΩ/55mΩ, Low $R_{DS(ON)}$ Internal Power MOSFETs
- High-Efficiency Synchronous Mode
- 410kHz Default Switching Frequency (f_{SW})
- 200kHz to 2.2MHz Synchronized External Clock
- High Duty Cycle for Automotive Cold-Crank Conditions
- Power-Save Mode (PSM)
- Internal Soft Start (SS)
- Power Good (PG)
- Over-Current Protection (OCP) with Hiccup Mode
- Thermal Shutdown
- Fully Assembled and Tested
- Available in a QFN-8 (3mmx3mm) Package
- Available in AEC-Q100 Grade 1



Optimized Performance with MPS Inductor MPL-AL6060 Series

APPLICATIONS

- Automotive Applications
- Industrial Control Systems
- Distributed Power Systems

All MPS parts are lead-free, halogen-free, and adhere to the RoHS directive. For MPS green status, please visit the MPS website under Quality Assurance. "MPS", the MPS logo, and "Simple, Easy Solutions" are trademarks of Monolithic Power Systems, Inc. or its subsidiaries.

EVBL4423H-Q-00A EVALUATION BOARD




LxWxH (6.35cmx6.35cmx0.5cm)

Board Number	MPS IC Number	MPS Inductor
EVBL4423H-Q-00A	MP4423HGQ, MPQ4423HGQ	MPL-AL6060-100

Efficiency vs. Load Current vs. Power Loss

$V_{OUT} = 3.3V$



QUICK START GUIDE

1. Connect the load terminals to:
 - a. Positive (+): VOUT
 - b. Negative (-): GND
2. Preset the power supply between 4V and 36V, then turn the power supply off.
3. Connect the power supply terminals to:
 - a. Positive (+): VIN
 - b. Negative (-): GND
4. Turn the power supply on. The evaluation board should start up automatically.
5. To use the enable (EN) function, apply a digital input to the EN/SYNC pin. Pull EN/SYNC above 1.65V to turn the converter on; pull EN/SYNC below 1.05V or float EN/SYNC to turn it off. Connect an internal 500kΩ resistor between the EN/SYNC and GND pins to allow EN/SYNC to be floated.
6. Connect the EN/SYNC input pin to any voltage connected to the VIN pin via a pull-up resistor (R1). Ensure that R1 is large enough to limit the EN input current below 150μA. For example, if EN/SYNC is connected to a 12V VIN, then R1 should be ≥36.7kΩ.
7. To connect EN/SYNC directly to a voltage source without using a pull-up resistor, the voltage amplitude should be limited to ≤6V to prevent damage to the internal Zener diode at EN/SYNC.
8. After the output voltage (VOUT) is set, connect the EN/SYNC input pin to a 200kHz to 2.2MHz external clock to synchronize the internal clock's rising edge to the external clock's rising edge. The external clock's pulse-width signal should be below 1.7μs.
9. Use R7 and R8 to set VOUT. R8 can be calculated by Equation (1):

$$R8 = \frac{R7}{\frac{V_{OUT}}{0.792} - 1} \quad (1)$$

Where R7 is 41.2kΩ, and VFB is 0.792V.

If VOUT is changed, refer to the Application Information section in the MP4423H/MPQ4423H datasheet to calculate the compensation, inductance, and output capacitance.

10. CLK_OUT is a signal inverted to SW that can be used as another buck's SYNC signal to operate 180° out-of-phase. The CLK_OUT high voltage is equal to VOUT. Ensure that it is safe to operate the synchronized part while VOUT is high.

EVALUATION BOARD SCHEMATIC




Figure 1: Evaluation Board Schematic

EVBL4423H-Q-00A BILL OF MATERIALS



Qty	Ref	Value	Description	Package	Manufacturer	Manufacturer PN
2	C1A, C1B	10 μ F	Ceramic capacitor, 50V, X7R	1210	Murata	GRM32ER71H106KA12L
1	C1C	0.1 μ F	Ceramic capacitor, 50V, X7R	0603	Murata	GRM188R71H104KA93D
2	C2A, C2B	22 μ F	Ceramic capacitor, 16V, X7R	1210	Murata	GRM32ER71C226KE79
4	C2, C2C, C3, COUT1	0.1 μ F	Ceramic capacitor, 16V, X7R	0603	Murata	GRM188R71C104KA01D
1	C4	33pF	Ceramic capacitor, 50V, C0G	0603	Murata	GRM1885C1H330JA01D
4	CIN1, CIN2, CIN3, CIN4	NS				
1	CIN5	22 μ F	Electrolytic capacitor	SMD	Jianghai	VTD-63V22
1	D1	NS				
1	FB1	NS				
1	L1	NS				
1	R1	1M Ω	Film resistor, 5%	0603	Yageo	RC0603JR-071ML
2	R3, R9	100k Ω	Film resistor, 1%	0603	Yageo	RC0603FR-07100KL
1	R4	20 Ω	Film resistor, 1%	0603	Yageo	RC0603FR-0720RL
1	R5	51k Ω	Film resistor, 1%	0603	Yageo	RC0603FR-0751KL
1	R6	10 Ω	Film resistor, 1%	0603	Yageo	RC0603FR-0710RL
1	R7	41.2k Ω	Film resistor, 1%	0603	Yageo	RC0603FR-0741K2L
1	R8	13k Ω	Film resistor, 1%	0603	Yageo	RC0603FR-0713KL
1	R10	20k Ω	Film resistor, 1%	0603	Yageo	RC0603FR-0720KL
1	R12	1k Ω	Film resistor, 1%	0603	Yageo	RC0603FR-071KL
2	R2, R11	NS				
5	VIN, VEMI, GND, VOUT, GND	2mm	2mm golden test pin	DIP	Custom ⁽¹⁾	
5	EN/SYNC, GND, PG, GND, CLK_OUT	1mm	1mm golden pin	DIP	Custom ⁽¹⁾	
1	Q1	40V	Transistor, 0.2A	SOT-23	ON Semiconductor	MMBT3904LT1
1	L2	MPL-AL6060-100	Inductor, 10 μ H, 7A, DCR = 27m Ω	SMD	MPS	MPL-AL6060-100
1	U1	MPQ4423H	Step-down converter, 36V, 3A	QFN-8 (3mmx3mm)	MPS	MPQ4423HGQ

Note:

1) These pins are custom-made by MPS. Contact an MPS FAE for more information.

EVB TEST RESULTS

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $C_{OUT} = 2 \times 22\mu F$, $L = 10\mu H$, $T_A = 25^\circ C$, unless otherwise noted.




EVB TEST RESULTS *(continued)*

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $C_{OUT} = 2 \times 22\mu F$, $L = 10\mu H$, $T_A = 25^\circ C$, unless otherwise noted.


Steady State

$I_{OUT} = 0A$




Steady State

$I_{OUT} = 3A$




Start-Up

$I_{OUT} = 0A$




Start-Up

$I_{OUT} = 3A$




Shutdown

$I_{OUT} = 0A$



Shutdown

$I_{OUT} = 3A$




EVB TEST RESULTS (continued)

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $C_{OUT} = 2 \times 22\mu F$, $L = 10\mu H$, $T_A = 25^\circ C$, unless otherwise noted.


Start-Up through EN

$I_{OUT} = 0A$




Start-Up through EN

$I_{OUT} = 3A$




Shutdown through EN

$I_{OUT} = 0A$




Shutdown through EN

$I_{OUT} = 3A$




SCP Entry

$I_{OUT} = 0A$



SCP Entry


$I_{OUT} = 3A$



EVB TEST RESULTS *(continued)*


$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $C_{OUT} = 2 \times 22\mu F$, $L = 10\mu H$, $T_A = 25^\circ C$, unless otherwise noted.

SCP Steady State




SCP Recovery

$I_{OUT} = 0A$




SCP Recovery

$I_{OUT} = 3A$




Load Transient

$I_{OUT} = 1.5A$ to $3A$




Cold Crank

$V_{IN} = 12V$ to $4V$ to $5V$, $I_{OUT} = 0A$



Cold Crank

$V_{IN} = 12V$ to $4V$ to $5V$, $I_{OUT} = 3A$




EVB TEST RESULTS *(continued)*

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $C_{OUT} = 2 \times 22\mu F$, $L = 10\mu H$, $T_A = 25^\circ C$, unless otherwise noted.


V_{IN} Ramps Down and Up

$V_{IN} = 18V$ to $4V$ to $0V$ to $4V$ to $18V$, $I_{OUT} = 0A$




V_{IN} Ramps Down and Up

$V_{IN} = 18V$ to $4V$ to $0V$ to $4V$ to $18V$, $I_{OUT} = 3A$



Load Dump

$V_{IN} = 12V$ to $36V$ to $12V$, $I_{OUT} = 3A$



PCB LAYOUT




Figure 2: Top Silk and Top Layer




Figure 3: Mid-Layer 1




Figure 4: Mid-Layer 2




Figure 5: Bottom Silk Layer and Bottom Layer



REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	9/29/2019	Initial Release	-
1.1	10/21/2021	Updated the footnote below the Applications section	1
		Updated the Quick Start Guide section	2
		Updated the graph and waveform titles in the EVB Test Results section	6–10
		Grammar and formatting updates; updated pagination; updated figure titles; updated headers	All

Notice: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.