



EVM3612-LQ-00A

3V to 22V Input, 1A , Ultra-Low 5 μ A I_Q,
Power Module Evaluation Board

DESCRIPTION

The EVM3612-LQ-00A evaluation board is designed to demonstrate the capabilities of MPM3612, a synchronous, rectified, step-down, switch-mode converter with built-in internal power MOSFETs and high light-load efficiency. The MPM3612 has an ultra-low 5 μ A I_Q. The device offers a very compact solution that achieves 1A of continuous output current with excellent load and line regulation across a wide input supply range.

The MPM3612 switching edge is optimized for EMI reduction. Constant-on-time (COT) control provides seamless mode transition and a fast load transient response. Full protection features include over-current protection (OCP), over-voltage protection (OVP), and thermal shutdown.

The MPM3612 requires a minimal number of readily available, standard external components. It is available in a space-saving LGA (3mmx3mmx2mm) package.

ELECTRICAL SPECIFICATIONS

Parameter	Symbol	Value	Units
Input voltage	V _{IN}	12	V
Output voltage	V _{OUT}	3.3	V
Output current	I _{OUT}	1	A

EVALUATION BOARD



(LxWxH) 64mmx64mmx1.6mm

Board Number	MPS IC Number
EVM3612-LQ-00A	MPM3612GLQ

FEATURES


- Wide 3V to 22V Operating Input Range
- 5 μ A Low I_Q
- 1A Load Current
- High Efficiency from a 100 μ A to 1A Load within a 4V to 22V V_{IN} Range
- Power-Save Mode (PSM)
- 1.25MHz Fixed Switching Frequency during CCM
- t_{ON} Extension to Support Large Duty Cycles
- Power Good (PG) Indication
- EN Shutdown Output Discharge
- Over-Current Protection (OCP), Over-Voltage Protection (OVP), and Hiccup Mode
- Adjustable V_{OUT}
- Available in an LGA (3mmx3mmx2mm) Package

APPLICATIONS

- Internet of Things (IoT)
- Home Automation, Home Security
- Single-Cell or Multi-Cell Li-Ion Battery Systems
- Multi-Cell Dry Battery Systems
- Sever Power

All MPS parts are lead-free, halogen-free, and adhere to the RoHS directive. For MPS green status, please visit the MPS website under Quality Assurance. "MPS", the MPS logo, and "Simple, Easy Solutions" are trademarks of Monolithic Power Systems, Inc. or its subsidiaries.


Efficiency vs. Load Current
V_{OUT} = 3.3V



QUICK START GUIDE

1. Preset the power supply (V_{IN}) between 3V and 22V.
2. Turn the power supply off.
3. Connect the power supply terminals to:
 - a. Positive (+): VIN
 - b. Negative (-): GND
4. Connect the load to:
 - a. Positive (+): VOUT
 - b. Negative (-): GND
5. Turn the power supply on after making the connections. The board should automatically start up.

EVALUATION BOARD SCHEMATIC






BILL OF MATERIALS

Qty	Ref	Value	Description	Package	Manufacturer	Manufacturer P/N
2	C2, C3	100nF	Ceramic capacitor, 25V, X7R	0603	Murata	GRM188R71E104KA01D
2	C1,C4	22μF	Ceramic capacitor, 25V, X5R	0805	SAMSUNG	CL21A226MAQNNNE
1	C6	1μF	Ceramic capacitor, 25V, X5R	0402	Murata	GRM155R61E105KA12D
1	R1	976kΩ	Film resistor, 1%, 976kΩ	0402	YAGEO	RC0402FR-07976KL
1	R2	220kΩ	Film resistor, 1%, 220kΩ	0402	YAGEO	RC0402FR-07220KL
1	Cf	22pF	Ceramic capacitor, 50V, COG	0402	Murata	GRM1555C1H220JA01D
2	R3,R4	100kΩ	Film resistor, 1%, 100kΩ	0402	YAGEO	RC0402FR-07100KL
1	R5	0Ω	Film resistor, 1%, 0Ω	0402	YAGEO	RC0402FR-070RL

EVB TEST RESULTS

Performance waveforms are tested on the evaluation board. $V_{IN} = 12V$, $V_{OUT} = 3.3V$, $T_A = 25^\circ C$, unless otherwise noted.




EVB TEST RESULTS *(continued)*

Performance waveforms are tested on the evaluation board. $V_{IN} = 12V$, $V_{OUT} = 3.3V$, $T_A = 25^{\circ}C$, unless otherwise noted.


Steady State

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 0A$




Steady State

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 1A$




VIN On

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 0A$




VIN On

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 1A$




VIN Off

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 0A$



VIN Off

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 1A$




EVB TEST RESULTS *(continued)*

Performance waveforms are tested on the evaluation board. $V_{IN} = 12V$, $V_{OUT} = 3.3V$, $T_A = 25^\circ C$, unless otherwise noted.


EN On

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 0A$




EN On

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 1A$




EN Off

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 0A$




EN Off

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 1A$




SCP Steady State

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 0A$



SCP Entry

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 0A$




EVB TEST RESULTS *(continued)*

Performance waveforms are tested on the evaluation board. $V_{IN} = 12V$, $V_{OUT} = 3.3V$, $T_A = 25^{\circ}C$, unless otherwise noted


SCP Recovery

$V_{IN} = 12V$, $V_{OUT} = 3.3V$, $I_{OUT} = 0A$




Load Transient

$0.8A/\mu s$, $0A$ to $0.5A$, $V_{IN} = 12V$, $V_{OUT} = 3.3V$



Load Transient

$0.8A/\mu s$, $0A$ to $1A$, $V_{IN} = 12V$, $V_{OUT} = 3.3V$



PCB LAYOUT




Figure 1: Top Layer




Figure 2: Bottom Layer

Notice: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.