MP8130

Ultra Low Power 36V, 200KHz, High Voltage Op Amp

The Future of Analog IC Technology

DESCRIPTION

The MP8130 is a rail-to-rail output, high voltage operational amplifier in a TSOT-23 package. This amplifier provides 200KHz bandwidth while consuming an incredibly low 10µA of supply current. The MP8130 can operate over a single supply range of 2.7V to 36V. It is available in tiny TSOT23-5 packages.

FEATURES

- Single Supply Operation: 2.7V to 36V
- TSOT23-5 Package
- 200KHz –3dB Bandwidth
- 10µA Supply Current
- Rail-to-Rail Output
- Unity-Gain Stable
- Input Common Mode to Ground
- Drives Up to 1000pF of Capacitive Loads
- Available in a TSOT23-5 Package

APPLICATIONS

- Precision Micropower Amplifiers
- Micropower Signal Processing
- Test Equipment

"MPS" and "The Future of Analog IC Technology" are Registered Trademarks of Monolithic Power Systems, Inc.

TYPICAL APPLICATION



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2007 MPS. All Rights Reserved.

PACKAGE REFERENCE



Part Number*	Package	Temperature
MP8130DJ	TSOT23-5	–40°C to +85°C

* For Tape & Reel, add suffix –Z (eg. MP8130DJ–Z)
For RoHS compliant packaging, add suffix –LF (eg. MP8130DJ–LF–Z)

ABSOLUTE MAXIMUM RATINGS (1)

Supply Voltage (V+ to V-) ..... +40.0V
Differential Input Voltage (V_{IN+} – $V_{IN–}$) ..... +6.0V
Input Voltage
V_{IN+} = $V_{IN–}$ ..... (V-) – 0.3V, (V+) + 0.3V

Recommended Operating Conditions (2)

Supply Voltage ..... +2.7V to +36V
Operating Temperature ..... –40°C to +85°C

Thermal Resistance (3)

	θ_{JA}	θ_{JC}	
TSOT23-5	220	110 ..	°C/W

Notes:
1) Exceeding these ratings may damage the device.
2) The device is not guaranteed to function outside of its operating conditions.
3) Measured on approximately 1" square of 1 oz copper.

ELECTRICAL CHARACTERISTICS

V_+ = +20V, V_- = 0V, V_{CM} = V+/2, R_L = 50kΩ, T_A = +25°C, unless otherwise noted.

Parameter	Symbol	Condition	Min	Typ	Max	Units
Input Offset Voltage	V_{OS}		–5	1	+5	mV
Input Offset Voltage Temp Coefficient				15		µV/°C
Input Bias Current (4)	I_B			2		pA
Input Offset Current (4)	I_{OS}			0.2		pA
Input Voltage Range	V_{CM}	CMRR > 60dB (V+ = 36V)	0		36	V
Common-Mode Rejection Ratio	CMRR	0 < V_{CM} < 36.0V (V+ = 36V)	80	82		dB
Power Supply Rejection Ratio	PSRR	Supply Voltage change of 2.7V/ 36V		80		dB
Large Signal Voltage Gain	A_{VOL}	R_L = 100kΩ, V_{OUT} = 5.0 Peak to Peak	60	88		dB
Maximum Output Voltage Swing	V_{OUT}	R_L = 100k		(V+) – 50mV		V
Minimum Output Voltage Swing	V_{OUT}	R_L = 100k		(V–) + 50mV		V
Gain-Bandwidth Product (4)	GBW	R_L = 1MΩ,C_L = 2pF, V_{OUT} = 0V		100		KHz
–3dB Bandwidth (4)	BW	A_V = 1, C_L = 2pF, R_L = 1MΩ		200		KHz
Slew Rate (4)	SR	A_V = 1, C_L = 2pF, R_L = 1MΩ		0.1		V/µs
Short Circuit Current	I_{SC}	Source	-20			mA
		Sink	20			mA
Supply Current	I_{sup}	No Load		10	15	µA

Note:
4) Guaranteed by design.

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2007 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS

C1= C3 =0.1µF, C2=C4=10µF, R_L = 1MΩ (Reference Figure 3)

Output Voltage vs. Output Current

Sourcing



Output Voltage vs. Output Current

Sinking



Gain Bandwidth and Phase Margin

R_L=1MΩ, Gain=1



Short Circuit Current vs. Supply Voltage

Sourcing



Short Circuit Current vs. Supply Voltage

Sinking



Gain Bandwidth and Phase Margin

R_L=1MΩ, Gain=10



Offset Voltage vs. Common Mode Voltage



Offset Voltage vs. Supply Voltage



PSRR



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2007 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS

C1= C3 =0.1µF, C2=C4=10µF, R_L = 1MΩ (Reference Figure 3)

Small Signal Pulse Response

A_V = 2, V_+ = V- = 10V, R_L = 1MΩ



Small Signal Pulse Response

A_V = 2, V_+ = V- = 15V, R_L = 1MΩ



Small Signal Pulse Response

A_V = -1, V_+ = V- = 5V, R_L = 1MΩ



Small Signal Pulse Response

A_V = -1, V_+ = V- = 12V, R_L = 1MΩ



Small Signal Pulse Response

A_V = 6, V_+ = V- = 5V, R_L = 1MΩ



Small Signal Pulse Response

A_V = 6, V_+ = V- = 15V, R_L = 1MΩ



Small Signal Pulse Response

A_V = -1, V_+ = V- = 2.5V, R_L = 1MΩ



Small Signal Pulse Response

A_V = 2, V_+ = V- = 2.5V, R_L = 1MΩ



Small Signal Pulse Response

A_V = -5, V_+ = V- = 12V, R_L = 1MΩ



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2007 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CHARACTERISTICS

C1= C3 =0.1µF, C2=C4=10µF, R_L = 1MΩ (Reference Figure 3)

Large Signal Pulse Response

A_V = -1, V_+ = V_- = 2.5V, R_L = 1MΩ



Large Signal Pulse Response

A_V = 6, V_+ = V_- = 12V, R_L = 1MΩ



Large Signal Pulse Response

A_V = 2, V_+ = V_- = 5V, R_L = 1MΩ



Rail to Rail Output Operation

A_V = 6, V_+ = V_- = 2.5V, R_L = 1MΩ



Rail to Rail Output Operation

A_V = 3, V_+ = V_- = 2.5V, R_L = 1MΩ



Rail to Rail Output Operation

A_V = 2, V_+ = V_- = 2.5V, R_L = 1MΩ



Rail to Rail Output Operation

A_V = -5, V_+ = V_- = 5V, R_L = 1MΩ



Rail to Rail Output Operation

A_V = -5, V_+ = V_- = 2.5V, R_L = 1MΩ



Rail to Rail Output Operation

A_V = -1, V_+ = V_- = 5V, R_L = 1MΩ



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2007 MPS. All Rights Reserved.

PIN FUNCTIONS

Pin #	Name	Description
1	OUT	Output.
2	V+	Supply Voltage.
3	IN+	Non-Inverting Input.
4	IN-	Inverting Input.
5	V-	Ground or Supply Return Pin.

TEST CIRCUITS



Notes: Close S3 for positive gain. Input signal to RF(+Av) connector.
The gain Av = 1 + R_{FB}/R_{IN}.
For unity gain, remove R_{IN} and short R_{FB}.
Open S3 for negative gain. Input signal to RF(-Av) connector.
The gain Av = -R_{FB}/R_{IN}.
S1 and S2 are switches for possible resistor and capacitor load connections.

Figure 1—AC Test Circuit

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2007 MPS. All Rights Reserved.

TEST CIRCUITS *(continued)*



Figure 2—Positive Power Supply Rejection Ratio Measurement

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2007 MPS. All Rights Reserved.

APPLICATION INFORMATION

Power Supply Bypassing

Regular supply bypassing techniques are recommended. A 10µF capacitor in parallel with a 0.1µF capacitor on both the positive and negative supplies is ideal. For the best performance, all bypassing capacitors should be located as close to the op amp as possible and all capacitors should be low ESL (Equivalent Series Inductance) and low ESR (Equivalent Series Resistance). Surface mount ceramic capacitors are ideal.

For large input signals, the op amp needs two clamp diodes to the input side. (See Figure 3 Large Input Signal Schematic).



Figure 3—Large Input Signal Schematic Sold

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2007 MPS. All Rights Reserved.

PACKAGE INFORMATION

TSOT23-5



TOP VIEW



RECOMMENDED LAND PATTERN



FRONT VIEW



SIDE VIEW



DETAIL "A"

NOTE:

1) ALL DIMENSIONS ARE IN MILLIMETERS.
2) PACKAGE LENGTH DOES NOT INCLUDE MOLD FLASH, PROTRUSION OR GATE BURR.
3) PACKAGE WIDTH DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION.
4) LEAD COPLANARITY (BOTTOM OF LEADS AFTER FORMING) SHALL BE 0.10 MILLIMETERS MAX.
5) DRAWING CONFORMS TO JEDEC MO-193, VARIATION AA.
6) DRAWING IS NOT TO SCALE.

NOTICE: The information in this document is subject to change without notice. Users should warrant and guarantee that third party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2007 MPS. All Rights Reserved.