



The Future of Analog IC Technology™

EV1528DQ-00A

9 Lamp, 20mA Precision WLED Driver Evaluation Board

GENERAL DESCRIPTION

The EV1528DQ-00A evaluation board is designed for driving up to nine (9) series WLEDs from a single cell Lithium Ion battery. The board is set up to obtain 20mA LED current. The current can be adjusted by varying the resistor R1.

The MP1528 uses current limited, variable frequency architecture to regulate the LED current while maintaining high efficiency. The BIAS pin measures the output voltage and turns off the converter if an over voltage condition is present to prevent damage due to an open circuit condition. The LED current is measured with an external current sense resistor. The low 0.4V full-scale regulation threshold and 0.4Ω power switch minimize power loss to improve efficiency. Either a DC voltage or a PWM signal at the BRT input can control the LED brightness.

FEATURES

- 2.7V to 5.5V Input Voltage Range
- Drives up to 9 Series White LEDs
- Analog and Digital PWM Brightness Control Through BRT
- Surface-Mount Components
- Fully Assembled and Tested

APPLICATIONS

- Handheld Computers
- PDAs
- PDA Phones
- Digital and Video Cameras
- Small LCD Displays

"MPS" and "The Future of Analog IC Technology" are Trademarks of Monolithic Power Systems, Inc.

ELECTRICAL SPECIFICATIONS

| Parameter | Symbol | Value | Units |
|---------------|-----------|-----------|-------|
| Input Voltage | V_{IN} | 2.7 – 5.5 | V |
| # of WLEDs | | 7 – 9 | |
| LED Current | I_{LED} | 20 | mA |


EV1528DQ-00A EVALUATION BOARD




(L x W x H) 2.0" x 1.5" x 0.5"
(5.0cm x 3.8cm x 1.4cm)

| Board Number | MPS IC Number |
|--------------|---------------|
| EV1528DQ-00A | MP1528DQ |

Efficiency vs Load Current



EVALUATION BOARD SCHEMATIC


EV1528_S01

EV1528DQ-00A BILL OF MATERIALS

| Qty | Ref | Value | Description | Package | Manufacturer P/N | Distributor P/N |
|-----|--------------------|-------|-----------------------------|---------|-----------------------------|----------------------------|
| 1 | C1 | 4.7µF | Ceramic Capacitor, 10V, X5R | 1206 | TDK: C3216X5R1A475K | Digikey: 445-1386-1-ND |
| 1 | C2 | 1µF | Ceramic Capacitor, 50V, X7R | 1206 | TDK: C3216X7R1H105K | Digikey: 445-1423-1-ND |
| 1 | C3 | 10nF | Ceramic Capacitor, 50V, X7R | 0805 | TDK: C2012X7R1H103K | Digikey: 445-1348-1-ND |
| 1 | D1 | | Diode Schottky, 60V, 1A | SMA | Diodes Inc.: B160B-13-F | Digikey: B160B-FDICT-ND |
| 1 | L1 | 6.2µH | Inductor, 1.45A, D62LCB | SMD | Toko: A918CY-6R2M | |
| 9 | LED1 to LED9 | | Not Stuffed | | | |
| 1 | R1 | 20Ω | Resistor, 1% | 0805 | Panasonic: ERJ-6GEYJ200V | Digikey: P20ACT-ND |
| 1 | R2 | 100kΩ | Resistor, 5% | 0805 | Panasonic: ERJ-6GEYJ104V | Digikey: P100KACT-ND |
| 1 | U1 | | White LED Driver | QFN6 | MPS: MP1528DQ | |

PRINTED CIRCUIT BOARD LAYOUT




Figure 1—Top Silk Layer




Figure 2—Top Layer




Figure 3—Bottom Layer

QUICK START GUIDE

1. Solder LED1 - LED9 to the board.
2. Attach the positive and negative terminals of the power supply (2.7V - 5.5V) to the VIN and GND pins, respectively.
3. Drive EN high to enable the MP1528.
4. Apply a DC voltage of 0.3V to 1.2V on BRT for analog dimming. Maximum brightness (20mA typical) occurs with 1.2V applied. For PWM dimming mode, apply a PWM rectangular wave with a minimum voltage less than 0.18V and a maximum greater than 1.2V. When a voltage less than 0.18V is applied to this pin, the output switch is turned off. The frequency of the PWM signal must be between 100Hz to 400Hz.

NOTICE: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.