



EV2348-TL-00A

High-Efficiency, 650kHz, 4A, 24V. Step-Down Converter Evaluation Board

DESCRIPTION

The EV2348-TL-00A Evaluation Board is designed to demonstrate the capabilities of MPS' MP2348, a fully-integrated high-frequency, synchronous rectified, step-down, switch-mode converter with internal power MOSFETs. It offers a very compact solution to achieve a 4A continuous output current over a wide input range, with excellent load and line regulation. The MP2348 has synchronous-mode operation for higher efficiency over the output current-load range.

Constant On-Time control operation provides very fast transient response and easy loop design as well as very tight output regulation.

Full protection features include SCP, OCP, UVP, and thermal shutdown.

The MP2348 requires a minimal number of readily-available, standard, external components and is available in a space-saving SOT583 (1.6mmx2.1mm) package.

ELECTRICAL SPECIFICATION (1)

Parameter	Symbol	Value	Units
Input Voltage	V _{IN}	19	V
Output Voltage	V _{OUT}	3.3	V
Output Current	I _{OUT}	4	A

Note:

- 1) For different Input/output voltage specs and different output capacitor/inductor may need change the application circuit parameters.

FEATURES

- Wide 4.2V-to-24V Operating Input Range
- 75mΩ/40mΩ Low-R_{DS(ON)} Internal Power MOSFETs
- 200μA Low I_q
- High-Efficiency Synchronous-Mode Operation
- Forced PWM, Auto PFM/PWM and Ultra-sonic Mode Selectable
- Fast Load Transient Response
- 650kHz Switching Frequency
- Programmable Soft-Start Time
- Over-Current Protection and Hiccup
- Pre-bias Startup
- Thermal Shutdown
- Available in a SOT583 package


APPLICATIONS

- Game Consoles
- Digital Set-Top Boxes
- Flat-Panel Television and Monitors
- General Purposes

All MPS parts are lead-free, halogen free, and adhere to the RoHS directive. For MPS green status, please visit MPS website under Quality Assurance.

"MPS" and "The Future of Analog IC Technology" are Registered Trademarks of Monolithic Power Systems, Inc.

EV2348-TL-00A EVALUATION BOARD





(L x W x H) 63.7mm x 48.4mm x 6.4mm

Board Number	MPS IC Number
EV2348-TL-00A	MP2348GTL

Efficiency

PFM without USM V_{OUT}=3.3V,
L=3.3μH, DCR=9mΩ



EVALUATION BOARD SCHEMATIC

EV2348-TL-00A BILL OF MATERIALS

Qty	Ref	Value	Description	Package	Manufacturer	Part Number
1	C1	22 μ F	Ceramic Cap., 25V, X5R	0805	muRata	GRM21BR61E226ME44L
1	C1A	0.1 μ F	Ceramic Cap., 25V, X7R	0603	muRata	GRM188R71E104KA01D
2	C2,C2A	22 μ F	Ceramic Cap., 16V, X5R	0805	muRata	GRM21BR61C226ME44L
1	C3	1 μ F	Ceramic Cap., 16V, X7R	0603	muRata	GRM188R71C105KA12D
1	C4	6.8nF	Ceramic Cap., 50V, X7R	0603	muRata	GRM188R71H682KA01D
1	C5	10pF	Ceramic Cap., 50V, COG	0603	muRata	GRM1885C1H100JA01D
0	C1B,C6	NS				
1	R1	40.2k	Thick Film Res., 1%	0603	Yageo	RC0603FR-0740K2L
1	R2	13k	Thick Film Res., 1%	0603	Yageo	RC0603FR-0713KL
1	R3	20k	Thick Film Res., 1%	0603	Yageo	RC0603FR-0720KL
1	R4	20 Ω	Thick Film Res., 1%	0603	Yageo	RC0603FR-0720RL
1	R5	604k	Thick Film Res., 1%	0603	Yageo	RC0603FR-07604KL
0	R6	NS				
1	R7	10 Ω	Thick Film Res., 1%	0603	Yageo	RC0603JR-0710RL
1	R8	NS				
1	R9	499k	Thick Film Res., 1%	0603	Yageo	RC0603FR-07499KL
1	L1	3.3 μ H	Inductor, DCR=9m Ω , Is=9A	SMD	Würth	744314330
1	U1	MP2348GTL	Synchronous Step-Down Converter	SOT583	MPS	MP2348GTL
1	JP1	Jumper	Jumper	SIP-3	Any	

EVB TEST RESULTS

$V_{IN} = 19V$, $V_{OUT} = 3.3V$, $L = 3.3\mu H$, $T_A = +25^\circ C$, unless otherwise noted.


Input/Output Ripple

$I_{OUT} = 0A$, PFM

CH1:
 V_{out}/AC
20mV/div.

CH2: V_{IN}
10V/div.
CH1: V_{sw}
10V/div.

CH4: I_L
2A/div.



1µs/div.


Input/Output Ripple

$I_{OUT} = 4A$

CH1:
 V_{out}/AC
20mV/div.

CH2: V_{IN}
10V/div.
CH1: V_{sw}
10V/div.

CH4: I_L
2A/div.



1µs/div.


Input/Output Ripple

$I_{OUT} = 0A$, PWM

CH1:
 V_{out}/AC
20mV/div.

CH2: V_{IN}
10V/div.
CH1: V_{sw}
10V/div.

CH4: I_L
2A/div.




1µs/div.

Start-Up through Input Voltage

$I_{OUT} = 0A$, PWM

CH1: V_{out}
2V/div.
CH2: V_{IN}
10V/div.
CH1: V_{sw}
10V/div.

CH4: I_L
2A/div.



1ms/div.


Start-Up through Input Voltage

$I_{OUT} = 0A$, PFM

CH1: V_{out}
2V/div.

CH2: V_{IN}
10V/div.
CH1: V_{sw}
10V/div.

CH4: I_L
2A/div.




1ms/div.

Start-Up through Input Voltage

$I_{OUT} = 4A$







CH1: V_{out}
2V/div.
CH2: V_{IN}
10V/div.
CH1: V_{sw}
10V/div.

CH4: I_L
2A/div.



1ms/div.

EVB TEST RESULTS (continued)
 $V_{IN} = 19V$, $V_{OUT} = 3.3V$, $L = 3.3\mu H$, $T_A = +25^\circ C$, unless otherwise noted.

Shutdown through Input Voltage
 $I_{OUT} = 0A$, PWM

Shutdown through Input Voltage
 $I_{OUT} = 0A$, PFM

Shutdown through Input Voltage
 $I_{OUT} = 4A$

Start-Up through Enable
 $I_{OUT} = 0A$, PWM

Start-Up through Enable
 $I_{OUT} = 0A$, PFM

Start-Up through Enable
 $I_{OUT} = 4A$



EVB TEST RESULTS *(continued)*

$V_{IN} = 19V$, $V_{OUT} = 3.3V$, $L = 3.3\mu H$, $T_A = +25^\circ C$, unless otherwise noted.

Shutdown through Enable

$I_{OUT} = 0A$, PWM

CH1: V_{out}
2V/div.
CH2: V_{EN}
5V/div.
CH3: V_{sw}
10V/div.
CH4: I_L
2A/div.




200ms/div.

Shutdown through Enable

$I_{OUT} = 0A$, PFM

CH1: V_{out}
2V/div.
CH2: V_{EN}
5V/div.
CH3: V_{sw}
10V/div.
CH4: I_L
2A/div.




200ms/div.

Shutdown through Enable

$I_{OUT} = 4A$


CH1: V_{out}
2V/div.
CH2: V_{EN}
5V/div.
CH3: V_{sw}
10V/div.
CH4: I_L
2A/div.



200µs/div.

Short-Circuit Entry


CH1: V_{out}
2V/div.
CH2: V_{in}
10V/div.
CH3: V_{sw}
10V/div.
CH4: I_L
2A/div.



5ms/div.

Short-Circuit Recovery

CH1: V_{out}
2V/div.
CH2: V_{EN}
10V/div.
CH3: V_{sw}
10V/div.
CH4: I_L
2A/div.




5ms/div.

Load Transient

$I_{OUT} = 2A-4A$

CH1: V_{out}/AC
100mV/div.
CH4: I_{out}
2A/div.



100µs/div.

PRINTED CIRCUIT BOARD LAYOUT




Figure1: Top Silk Layer




Figure2: Top Layer




Figure3: Bottom Layer

QUICK START GUIDE

1. Preset Power Supply to 19V.
2. Turn Power Supply off.
3. Connect Power Supply terminals to:
 - a. Positive (+): VIN
 - b. Negative (-): GND
4. Connect Load to:
 - a. Positive (+): VOUT
 - b. Negative (-): GND
5. Turn Power Supply on after making connections. The board will automatically start up.
6. To use the Enable function, apply a digital input to the EN pin. Drive EN higher than 1.3V to turn on the regulator, or less than 1V to turn it off.

NOTICE: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.