MPL-AT2512-6R8

Low-Profile Molded Inductor 6.8µH

APPLICATIONS

- Battery-powered devices
- High switching frequency SMPS
- IoT
- Wearable
- Portable devices
- Input filters

FEATURES

- Size 2.5mmx2.0mmx1.2mm
- Low Profile
- Low Audible Noise
- Molded Construction
- Soft Saturation
- Stable Over High Temperatures
- Low DCR
- Max Operating Temp +125°C
- RoHS/REACH-Compliant, Halogen-Free

ELECTRICAL CHARACTERISTICS

Parameter			Value	Unit
Inductance (1)	L	±20%	6.8	µH
Resistance	R_{DC}	Typ	260	mΩ
Resistance MAX	$R_{DC\ MAX}$	Max	300	mΩ
Rated Current (2)	I_R	Typ	1.4	A
Saturation Current 25°C (3)	$I_{SAT\ 25°C}$	Typ	2.2	A
Saturation Current 100°C (4)	$I_{SAT\ 100°C}$	Typ	2.2	A
Resonance Frequency	f_r	Typ	21	MHz

GENERAL SPECIFICATIONS

(1) Inductance	Measured at 100kHz, 100mA
(2) Rated Current	Rated current will cause the coil temperature rise ΔT of 40K *I_R measured with the inductor soldered in a single-layer PCB. Copper layer thickness 35µm Cu / PCB size 30x50mm. Temperature behavior dependent on circuit design, PCB layout, proximity to other components, and trace dimensions and thickness.*
(3) Saturation Current 25°C	Saturation current will cause L to drop from 30% at 25°C ambient temperature
(4) Saturation Current 100°C	Saturation current will cause L to drop from 30% at 100°C ambient temperature
Temperature Test Condition	Electrical specifications measured at 25°C, 35% RH if not given differently
Operating Condition	Operating temperature: -40°C to +125°C (including temp rise) Should not exceed +125°C under worst-case operation conditions
Storage Condition	Tape and Reel packaging: -10°C to +40°C Humidity: <50% RH

All MPS parts are lead-free, halogen-free, and adhere to the RoHS directive. For MPS green status, please visit the MPS website under Quality Assurance. “MPS”, the MPS logo, and “Simple, Easy Solutions” are registered trademarks of Monolithic Power Systems, Inc. or its subsidiaries.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

TYPICAL PERFORMANCE CURVES

Temperature Rise vs. Current



Inductance vs. Current



Impedance vs. Frequency



Inductance vs. Frequency



Quality Factor vs. Frequency



AC Resistance vs. Frequency



MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

DIMENSIONS

PRODUCT PACKAGE



(units in mm)

RECOMMENDED LAND PATTERN



(units in mm)

TOP MARKING

Marking	
Start of Winding	. (dot)

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

ORDERING INFORMATION

Part Number	L (1) ±20% (µH)	R_{DC} Typ (mΩ)	I_R (2) Typ (A)	$I_{SAT\ 25°C}$ (3) Typ (A)	$I_{SAT\ 100°C}$ (4) Typ (A)
MPL-AT2512-R33	0.33	13	6.4	7.8	7.8
MPL-AT2512-R47	0.47	14	5.8	6.4	6.4
MPL-AT2512-R68	0.68	23	4.8	6.0	6.0
MPL-AT2512-1R0	1.0	33	4.1	5.2	5.2
MPL-AT2512-1R5	1.5	43	3.4	4.2	4.2
MPL-AT2512-2R2	2.2	68	2.8	3.4	3.4
MPL-AT2512-3R3	3.3	116	2.2	3.0	3.0
MPL-AT2512-4R7	4.7	170	1.8	2.4	2.4
MPL-AT2512-6R8	6.8	260	1.4	2.2	2.2
MPL-AT2512-100	10	335	1.2	1.7	1.7

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.

REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	7/12/2019	Initial Release	-
1.1	7/30/2019	Updated Impedance vs. Frequency Curve	2
1.2	9/8/2025	Updated the Series picture	1
		Updated R_{DC} (Typ), $R_{DC\ MAX}$, and made minor formatting edits in the Electrical Characteristics section.	1
		Updated all the Typical Performance Curves.	2
		Reordered the Dimensions section; updated the Product Package and Recommended Land Pattern images.	3
		Made minor formatting edits and updated the following values in the Ordering Information section: • Replaced the MPL-AT2514-2R2 and MPL-AT2514-4R7 with the MPL-AT2512-2R2 and MPL-AT2512-4R7, respectively • MPL-AT2512-R33: Updated R_{DC} (Typ), $I_{SAT\ 25°C}$ (Typ), and $I_{SAT\ 100°C}$ (Typ) • MPL-AT2512-R47: Updated R_{DC} (Typ) and I_R (Typ) • MPL-AT2512-R68: Updated R_{DC} (Typ) and I_R (Typ) • MPL-AT2512-1R0: Updated R_{DC} (Typ) and I_R (Typ) • MPL-AT2512-1R5: Updated R_{DC} (Typ) and I_R (Typ) • MPL-AT2512-3R3: Updated R_{DC} (Typ), I_R (Typ), $I_{SAT\ 25°C}$ (Typ), and $I_{SAT\ 100°C}$ (Typ) • MPL-AT2512-6R8: Updated R_{DC} (Typ) • MPL-AT2512-100: Updated R_{DC} (Typ)	4

NOTICE: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited.
© 2025 MPS. All Rights Reserved.