



The Future of Analog IC Technology®

## MP3398E

4-String, Max 400mA/String, 80V Return,  
Step-Up, WLED Controller

### DESCRIPTION

The MP3398E is a step-up controller with four current channels designed to drive WLED arrays for large LCD panel backlighting applications. The MP3398E is able to expand the number of LED channels with two or more ICs in parallel sharing a single power source.

The MP3398E employs peak-current mode with a fixed switching frequency. The frequency is programmable through an external setting resistor. The MP3398E drives an external MOSFET to boost up the output voltage from a 4.5V to 33V input supply and regulates the current in each LED string to the value set by an external current-setting resistor.

The MP3398E applies four internal current sources for current balancing. The current matching achieves 2.3% regulation accuracy between strings. The low regulation voltage on the LED current sources reduces power loss.

The MP3398E supports direct PWM dimming and analog dimming with PWM input. Full protection features include over-current protection (OCP), over-temperature protection (OTP), under-voltage protection (UVP), over-voltage protection (OVP), LED short/open protection, and inductor/diode short protection.

The MP3398E is available in TSSOP-16EP, SOIC-16 and PDIP-16 packages.

### FEATURES


- 4-String, Max 400mA/String WLED Driver
- 4.5V to 33V Input Voltage Range
- 80V ABS Rating for Each String
- 2.3% Current Matching Accuracy between Each String
- Direct PWM Dimming Mode
- Analog Dimming Mode with PWM Input
- Cascading Capability with a Single Power Source
- LED Open and Short Protection
- Programmable Recoverable Over-Voltage Protection (OVP)
- 202mV Latch-Off Cycle-by-Cycle Current Limit Threshold
- Latch-Off Over-Temperature Protection (OTP)
- Short Inductor/Diode Protection
- Available in TSSOP-16EP, SOIC-16 and PDIP-16 Packages

### APPLICATIONS

- Desktop LCD Flat Panel Displays
- All-in-One PCs
- 2D/3D LCD TVs

All MPS parts are lead-free, halogen-free, and adhere to the RoHS directive. For MPS green status, please visit the MPS website under Quality Assurance. "MPS" and "The Future of Analog IC Technology" are registered trademarks of Monolithic Power Systems, Inc.

## TYPICAL APPLICATION



## ORDERING INFORMATION

| Part Number  | Package               | Top Marking      |
|--------------|-----------------------|------------------|
| MP3398EGF*   | TSSOP-16EP            | <i>See Below</i> |
| MP3398EGP**  | PDIP-16               | <i>See Below</i> |
| MP3398EGS*** | SOIC16 <sup>(1)</sup> | <i>See Below</i> |

\* For Tape & Reel, add suffix -Z (e.g. MP3398EGF-Z)

\*\* For Tape & Reel, add suffix -Z (e.g. MP3398EGP-Z)

\*\*\* For Tape & Reel, add suffix -Z (e.g. MP3398EGS-Z)

**NOTE:**

1) For the MP3398E with the SOIC16 package, check with the factory to ensure that the product is in stock.

### TOP MARKING (MP3398EGF)

**MPSYYWW**

**MP3398E**

**LLLLLL**

MPS: MPS prefix  
YY: Year code  
WW: Week code  
MP3398E: Part number  
LLLLLL: Lot number

### TOP MARKING (MP3398EGP)

**MPSYYWW**

**MP3398E**

**LLLLLLLL**

MPS: MPS prefix  
YY: Year code  
WW: Week code  
MP3398E: Part number  
LLLLLLLL: Lot number

### TOP MARKING (MP3398EGS)

**MPSYYWW**

**MP3398E**

**LLLLLL**

MPS: MPS prefix  
YY: Year code  
WW: Week code  
MP3398E: Part number  
LLLLLLLL: Lot number

## PACKAGE REFERENCE

| TOP VIEW                              |                |                |
|---------------------------------------|----------------|----------------|
| <p>Exposed Pad<br/>Connect to GND</p> |                |                |
| <b>TSSOP-16EP</b>                     | <b>PDIP-16</b> | <b>SOIC-16</b> |

**ABSOLUTE MAXIMUM RATINGS** <sup>(1)</sup>

|                                                                          |                 |
|--------------------------------------------------------------------------|-----------------|
| $V_{IN}$ .....                                                           | -0.3V to +40V   |
| $V_{LED1}$ to $V_{LED4}$ .....                                           | -0.3V to +80V   |
| All other pins .....                                                     | -0.3V to +6.5V  |
| Continuous power dissipation ( $T_A = 25^\circ\text{C}$ ) <sup>(2)</sup> |                 |
| TSSOP-16EP.....                                                          | 2.78W           |
| PDIP16.....                                                              | 1.39W           |
| SOIC16.....                                                              | 1.56W           |
| Junction temperature .....                                               | 150°C           |
| Lead temperature.....                                                    | 260°C           |
| Storage temperature.....                                                 | -60°C to +150°C |

**Recommended Operating Conditions** <sup>(3)</sup>

|                                   |                 |
|-----------------------------------|-----------------|
| Supply voltage ( $V_{IN}$ ) ..... | 4.5V to 33V     |
| Max LED current.....              | 400mA           |
| Operating junction temp.....      | -40°C to +125°C |

**Thermal Resistance** <sup>(4)</sup>

|                   | $\theta_{JA}$ | $\theta_{JC}$ |
|-------------------|---------------|---------------|
| TSSOP-16 EP ..... | 45 .....      | 10 ... °C/W   |
| PDIP-16.....      | 90 .....      | 25 ... °C/W   |
| SOIC-16.....      | 80.....       | 35.... °C/W   |

**NOTES:**

- 1) Exceeding these ratings may damage the device.
- 2) The maximum allowable power dissipation is a function of the maximum junction temperature  $T_J$  (MAX), the junction-to-ambient thermal resistance  $\theta_{JA}$ , and the ambient temperature  $T_A$ . The maximum allowable continuous power dissipation at any ambient temperature is calculated by  $P_D$  (MAX) =  $(T_J$  (MAX) -  $T_A$ ) /  $\theta_{JA}$ . Exceeding the maximum allowable power dissipation produces an excessive die temperature, causing the regulator to go into thermal shutdown. Internal thermal shutdown circuitry protects the device from permanent damage.
- 3) The device is not guaranteed to function outside of its operating conditions.
- 4) Measured on JESD51-7, 4-layer PCB.

## ELECTRICAL CHARACTERISTICS

$V_{IN} = 12V$ ,  $V_{EN} = 5V$ ,  $T_A = 25^{\circ}C$ , unless otherwise noted.

| Parameters                          | Symbol          | Condition                                     | Min  | Typ  | Max  | Unit      |
|-------------------------------------|-----------------|-----------------------------------------------|------|------|------|-----------|
| <b>General</b>                      |                 |                                               |      |      |      |           |
| Operating input voltage             | $V_{IN}$        |                                               | 4.5  |      | 33   | V         |
| Supply current (quiescent)          | $I_Q$           | $V_{IN} = 12V$ , no switching                 |      | 3.85 | 4.5  | mA        |
| Supply current (shutdown)           | $I_{ST}$        | $V_{EN} = 0V$ , $V_{IN} = 12V$                |      |      | 1    | $\mu A$   |
| LDO output voltage                  | $V_{CC}$        | $7V < V_{IN} < 28V$ ,<br>$0 < I_{VCC} < 10mA$ | 5.5  | 5.9  | 6.3  | V         |
| VCC UVLO threshold                  | $V_{IN\_UVLO}$  | Rising edge                                   | 3.7  | 4    | 4.3  | V         |
| VCC UVLO hysteresis                 |                 |                                               |      | 350  |      | mV        |
| EN high voltage                     | $V_{EN\_HIGH}$  | $V_{EN}$ rising                               | 1.5  |      |      | V         |
| EN low voltage                      | $V_{EN\_LOW}$   | $V_{EN}$ falling                              |      |      | 0.6  | V         |
| <b>Step-Up Converter</b>            |                 |                                               |      |      |      |           |
| Gate driver sourcing impedance      |                 | $V_{CC} = 5.9V$ , $V_{GATE} = 5.9V$           |      | 4    |      | $\Omega$  |
| Gate driver sinking impedance       |                 | $V_{CC} = 5.9V$ , $I_{GATE} = 10mA$           |      | 2.5  |      | $\Omega$  |
| Switching frequency                 | $f_{SW}$        | $R_{OSC} = 100k\Omega$                        | 305  | 382  | 460  | kHz       |
| OSC voltage                         | $V_{OSC}$       | $R_{OSC} = 100k\Omega$ , $f_{SW} = 382kHz$    | 0.77 | 0.8  | 0.83 | V         |
| Maximum duty cycle                  | $D_{MAX}$       | $R_{OSC} = 100k\Omega$                        | 90   |      |      | %         |
| Cycle-by-cycle ISENSE current limit |                 |                                               | 180  | 202  | 224  | mV        |
| COMP source current limit           | $I_{COMP\_SOL}$ | $1V < COMP < 2.9V$                            |      | 30   |      | $\mu A$   |
| COMP sink current limit             | $I_{COMP\_SIL}$ | $1V < COMP < 2.9V$                            |      | 18   |      | $\mu A$   |
| COMP transconductance               | $G_{COMP}$      | $\Delta I_{COMP} = \pm 10\mu A$               |      | 120  |      | $\mu A/V$ |
| <b>Current Dimming</b>              |                 |                                               |      |      |      |           |
| PWM input low threshold             | $V_{PWM\_LO}$   | $V_{PWM}$ falling                             |      |      | 0.4  | V         |
| PWM input high threshold            | $V_{PWM\_HI}$   | $V_{PWM}$ rising                              | 1.5  |      |      | V         |
| ADIM input low threshold            | $V_{ADIM\_LO}$  | $V_{ADIM}$ falling                            |      |      | 0.4  | V         |
| ADIM input high threshold           | $V_{ADIM\_HI}$  | $V_{ADIM}$ rising                             | 1.5  |      |      | V         |
| <b>Current Regulation</b>           |                 |                                               |      |      |      |           |
| ISET voltage                        | $V_{ISET}$      |                                               | 1.95 | 2    | 2.05 | V         |
| LEDX average current                | $I_{LED}$       | $R_{ISET} = 100.8k\Omega$                     | 192  | 202  | 212  | mA        |
| Current matching <sup>(5)</sup>     |                 | $I_{LED} = 200mA$                             |      |      | 2.3  | %         |
| LEDX regulation voltage             |                 | $I_{LED} = 200mA$                             |      | 430  |      | mV        |
|                                     |                 | $I_{LED} = 60mA$                              |      | 285  |      | mV        |

# ELECTRICAL CHARACTERISTICS *(continued)*

$V_{IN} = 12V$ ,  $V_{EN} = 5V$ ,  $T_A = 25^{\circ}C$ , unless otherwise noted.


| Parameters                   | Symbol         | Condition               | Min | Typ | Max | Unit        |
|------------------------------|----------------|-------------------------|-----|-----|-----|-------------|
| <b>Protection</b>            |                |                         |     |     |     |             |
| OVP threshold                | $V_{OVP\_OV}$  |                         | 1.9 | 2.0 | 2.1 | V           |
| OVP UVLO threshold           | $V_{OVP\_UV}$  | Step-up converter fails |     | 55  |     | mV          |
| LEDX UVLO threshold          | $V_{LEDX\_UV}$ |                         |     | 200 |     | mV          |
| LEDX over-voltage threshold  | $V_{LEDX\_OV}$ |                         | 7.2 | 8   | 8.8 | V           |
| Thermal protection threshold | $T_{ST}$       |                         |     | 130 |     | $^{\circ}C$ |

## NOTE :


5) Matching is defined as the difference between the maximum to minimum current divided by 2 times the average current.

## TYPICAL CHARACTERISTICS


**$I_Q$  vs. Temperature**  
 $V_{IN}=12V$ , No Switching




**$V_{CC}$  UVLO vs. Temperature**




**OVP Threshold vs. Temperature**




**$I_{LED}$  Average vs. Temperature**  
 $R_{SET}=100.8k\Omega$




**$I_{LED}$  Matching vs. Temperature**




**SW Frequency vs. Temperature**  
 $R_{OSC}=100k\Omega$




**$V_{SENSE\_LIMIT}$  vs. Temperature**



**LEDX Regulation Voltage vs. Temperature**






**$V_{SET}$  Matching vs. Temperature**




## TYPICAL PERFORMANCE CHARACTERISTICS


$V_{IN} = 19V$ ,  $V_{EN} = 3.3V$ , 120mA/string, 4 strings, 20 LEDs in series,  $T_A = 25^\circ C$ , unless otherwise noted.

**Steady State**

 **$V_{IN}$  Power On**

**EN On**

**PWM Dimming**


$f_{SW}=200Hz$ ,  $D_{PWM}=50\%$


**Analog Dimming**


$f_{PWM}=20kHz$ ,  $D_{PWM}=50\%$


**Open LED Protection**



Open One LED String at Working


**Short LED Protection**

Short One LED String at Working


**Short-Inductor Protection**


$V_{IN}=19V$ , 20S4P, 120mA/string


**Short-Diode Protection**


## PIN FUNCTIONS

| TSSOP-16<br>Pin # | PDIP-16/<br>SOIC-16<br>Pin # | Name   | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
|-------------------|------------------------------|--------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1                 | 13                           | LED1   | <b>LED string 1 current input.</b> LED1 is the open-drain output of an internal dimming control switch. Connect the LED string 1 cathode to LED1.                                                                                                                                                                                                                                                                                                                                                                                                                  |
| 2                 | 14                           | LED2   | <b>LED string 2 current input.</b> LED2 is the open-drain output of an internal dimming control switch. Connect the LED string 2 cathode to LED2.                                                                                                                                                                                                                                                                                                                                                                                                                  |
| 3                 | 15                           | GND    | <b>Ground.</b>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| 4                 | 16                           | LED3   | <b>LED string 3 current input.</b> LED3 is the open-drain output of an internal dimming control switch. Connect the LED string 3 cathode to LED3.                                                                                                                                                                                                                                                                                                                                                                                                                  |
| 5                 | 1                            | LED4   | <b>LED string 4 current input.</b> LED4 is the open-drain output of an internal dimming control switch. Connect the LED string 4 cathode to LED4.                                                                                                                                                                                                                                                                                                                                                                                                                  |
| 6                 | 2                            | ISET   | <b>LED current set.</b> Tie a current-setting resistor from ISET to ground to program the current in each LED string.                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| 7                 | 3                            | OVP    | <b>Output over-voltage protection.</b> Connect a resistor divider from output to OVP to program the OVP threshold.                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| 8                 | 4                            | OSC    | <b>Switching frequency set.</b> Connect a resistor between OSC and GND to set the step-up converter switching frequency. The clock frequency is proportional to the current source from OSC.                                                                                                                                                                                                                                                                                                                                                                       |
| 9                 | 5                            | EN     | <b>Enable control input.</b> A voltage greater than 1.5V turns the part on; a voltage less than 0.6V turns the part off. Do not float EN.                                                                                                                                                                                                                                                                                                                                                                                                                          |
| 10                | 6                            | ISENSE | <b>Current sense input.</b> During normal operation, ISENSE senses the voltage across the external inductor current-sensing resistor ( $R_{SENSE}$ ) for peak-current-mode control. ISENSE also limits the inductor current during every switching cycle. For cascading applications, tie ISENSE of the slave IC to GND. Do not float ISENSE.                                                                                                                                                                                                                      |
| 11                | 7                            | GATE   | <b>Step-up converter power switch driver output.</b> GATE drives the external power N-channel MOSFET device.                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| 12                | 8                            | VCC    | <b>The internal 5.9V linear regulator output.</b> VCC provides the power supply for the external MOSFET switch gate driver and the internal control circuitry. Bypass VCC to GND with a ceramic capacitor.                                                                                                                                                                                                                                                                                                                                                         |
| 13                | 9                            | VIN    | <b>Supply input.</b> VIN must be bypassed locally.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| 14                | 10                           | ADIM   | <b>Input for analog brightness control.</b> The LED current amplitude is determined by the duty cycle of the PWM signal applied to ADIM. An internal R-C filter (10M $\Omega$ resistor and 100pF capacitor) is integrated into ADIM. A frequency greater than 20kHz is recommended to achieve a better PWM signal filtering performance and ensure that the high-level voltage of $V_{ADIM}$ is above 1.5V and the low-level voltage is below 0.4V. If Analog dimming is not required, pulling this pin to high voltage ( $1.5V < V_{ADIM} \leq 5V$ ).             |
| 15                | 11                           | COMP   | <b>Step-up converter compensation.</b> COMP compensates for the regulation control loop. Connect a ceramic capacitor or a resistor and capacitor from COMP to GND.                                                                                                                                                                                                                                                                                                                                                                                                 |
| 16                | 12                           | PWM    | <b>Input signal for PWM brightness control.</b> By applying a PWM signal on PWM, the LED current is chopped, and the average current is equal to $ISET \times D_{DIM}$ , where ISET is the LED current value set by a resistor between ISET and GND, and $D_{DIM}$ is the duty cycle of the PWM dimming duty cycle. Ensure that the high level voltage is above 1.5V and the low-level voltage is below 0.4V. If PWM is floating, weakly pull it to GND internally. If PWM dimming is not required, pulling this pin to high voltage ( $1.5V < V_{PWM} \leq 5V$ ). |

## BLOCK DIAGRAM



**Figure 1: Functional Block Diagram**

## OPERATION

The MP3398E is a programmable constant frequency, peak-current mode, step-up converter with 4-channel regulated current sources to drive an array of up to four strings of white LEDs.

### Internal 5.9V Regulator

The MP3398E includes an internal linear regulator (VCC). When VIN is greater than 6.5V, this regulator outputs a 5.9V power supply to the external MOSFET switch gate driver and the internal control circuitry. The VCC voltage drops to 0V when the chip shuts down. The MP3398E features under-voltage lockout (UVLO). The chip is disabled until VCC exceeds the UVLO threshold. The UVLO hysteresis is approximately 350mV.

### System Start-Up

When enabled, the MP3398E checks the topology connection first. The chip monitors the over-voltage protection (OVP) pin to determine if the Schottky diode is connected or if the boost output is shorted to GND. An OVP voltage higher than 55mV allows the chip to switch normally; otherwise, switching is disabled. The MP3398E also checks other safety limits, including UVLO, over-temperature protection (OTP), and over-current protection (OCP) after passing the OVP test. If all protection tests pass, the chip then begins boosting the step-up converter with an internal soft start.

It is recommended that the enable signal occur after the establishment of the input voltage and PWM dimming signal during the start-up sequence to prevent a large inrush current.

### Step-Up Converter

At the beginning of each switching cycle, the internal clock turns on the external MOSFET. During normal operation, the minimum turn-on time is around 150ns. A stabilizing ramp added to the output of the current sense amplifier prevents subharmonic oscillations for duty cycles greater than 50%. This result is fed into the PWM comparator. When the summed voltage reaches the output voltage of the error amplifier ( $V_{COMP}$ ), the external MOSFET turns off.

The output voltage of the internal error amplifier is an amplified signal of the difference between the reference voltage and the feedback voltage. The converter chooses the lowest active LEDX pin voltage automatically to provide a high enough bus voltage to power all of the LED arrays.

If the feedback voltage drops below the reference, the output of the error amplifier increases. This results in more current flowing through the MOSFET, increasing the power delivered to the output and forming a closed loop that regulates the output voltage.

Under light-load operation, especially in the case of  $V_{OUT} \approx V_{IN}$ , the converter runs in pulse-skipping mode. In this mode, the MOSFET turns on for a minimum on time, and then the converter discharges the power to the output for the remaining period. The external MOSFET remains off until the output voltage needs to be boosted again.

### Dimming Control

The MP3398E provides two dimming methods: PWM and analog dimming mode.

For PWM dimming, apply a PWM signal to PWM. The LED current is chopped by this PWM signal, and the average LED current is equal to  $I_{SET} \times D_{DIM}$ , where  $D_{DIM}$  is the duty cycle of the PWM dimming signal, and  $I_{SET}$  is the LED current amplitude.

For analog dimming, apply a PWM signal to ADIM. An internal R-C filter (10M $\Omega$  resistor and 100pF capacitor) is integrated to ADIM. This PWM signal is filtered to the DC voltage by the internal R-C filter. The LED current amplitude is equal to  $I_{SET} \times D_{DIM}$ , where  $D_{DIM}$  is the duty cycle of the PWM dimming signal, and  $I_{SET}$  is the LED current amplitude. A PWM signal 20kHz or higher is recommended for better filtering.

### Operation Switching Frequency

The converter operating frequency is set through an external resistor on OSC. This helps optimize both the size of the external components and the system efficiency.

### Open-String Protection

Open-string protection is achieved through detecting the voltage of OVP and LED (1 to 4). If one or more strings are open, the respective LEDX pins are pulled to ground, and the IC continues charging the output voltage until it reaches the over-voltage protection (OVP) threshold. If the OVP point has been triggered, the chip stops switching and marks off the strings that have an LEDX pin voltage lower than 200mV. Once marked, the remaining LED strings force the output voltage back into tight regulation. The string with the largest voltage drop determines the output regulation.

The MP3398E always attempts to light at least one string. If all strings are open, the MP3398E shuts down the step-up converter. The strings remain in this marked state until the chip resets.

### Short-String Protection

The MP3398E monitors the LEDX pin voltages to determine if a short-string fault has occurred. If one or more strings are shorted, the respective LEDX pins tolerate high-voltage stress. If an LEDX pin voltage is higher than the protection threshold, this condition triggers the detection of a short-string fault. When a short-string fault remains for 10ms, the fault string is marked off and disabled. Once a string is marked off, it disconnects from the output voltage loop until VIN or EN restarts.

To prevent mistriggering a short LED protection when the LED string is open, the short LED protection function is disabled when  $V_{LEDX}$  of all used LED channels is higher than 2.1V.

### Cycle-by-Cycle Current Limit

To prevent the external components from exceeding their current stress ratings, the IC employs cycle-by-cycle current-limit protection. When the current exceeds the current limit value, the IC latches off until the power resets.

### Short Inductor/Diode Protection

When the external inductor or diode is shorted, the IC provides protection by detecting the current flowing through the power MOSFET. When the current sense voltage across the sense resistor (connected between ISENSE and GND) reaches the current protection threshold and lasts for eight switching cycles, the IC stops switching and latches.

### Thermal Shutdown

To prevent the IC from operating at exceedingly high temperatures, thermal shutdown is implemented by monitoring the silicon die temperature. When the die temperature exceeds the threshold ( $T_{ST}$ ), the IC latches off until the power resets.

## APPLICATION INFORMATION

### Selecting the Switching Frequency

The switching frequency of the step-up converter is recommended to be between 100kHz and 900kHz for most applications. A resistor on OSC sets the internal oscillator frequency for the step-up converter according to Equation (1):

$$F_{sw}(\text{kHz}) = \frac{38200}{R_{osc}(\text{k}\Omega)} \quad (1)$$

For  $R_{osc} = 100\text{k}\Omega$ , the switching frequency is set to 382kHz.

### Setting the LED Current

The current in each LED string can be set through the current setting resistor on ISET and can be calculated with Equation (2):

$$I_{LED}(\text{mA}) = \frac{20362}{R_{iset}(\text{k}\Omega)} \quad (2)$$

For  $R_{iset} = 100.8\text{k}\Omega$ , the LED current is set to 202mA. Do not leave ISET open.

### Selecting the Input Capacitor

The input capacitor reduces the surge current drawn from the input supply and the switching noise from the device. The input capacitor impedance at the switching frequency should be less than the input source impedance to prevent the high-frequency switching current from passing through to the input. Ceramic capacitors with X5R or X7R dielectrics are recommended for their low ESR and small temperature coefficients. For most applications, use a  $4.7\mu\text{F}$  ceramic capacitor in parallel with a  $220\mu\text{F}$  electrolytic capacitor.

### Selecting the Inductor and Current-Sensing Resistor

A larger value inductor results in less ripple current and lower peak inductor current, which reduces stress on the N-channel MOSFET. However, the larger value inductor has a larger physical size, a higher series resistance, and a lower saturation current. Choose an inductor that will not saturate under the worst-case load conditions. Select the minimum inductor value to ensure that the boost converter works in continuous conduction mode with high efficiency and good EMI performance.

Calculate the required inductance value using Equation (3) and Equation (4):

$$L \geq \frac{\eta \times V_{out} \times D \times (1-D)^2}{2 \times f_{sw} \times I_{load}} \quad (3)$$

$$D = 1 - \frac{V_{in}}{V_{out}} \quad (4)$$

Where  $V_{in}$  and  $V_{out}$  are the input and output voltages,  $f_{sw}$  is the switching frequency,  $I_{load}$  is the LED load current, and  $\eta$  is the efficiency.

The switching current is used for peak-current-mode control. To avoid reaching the current limit, the voltage across the sensing resistor ( $R_{sense}$ ) must be less than 80% of the current limit voltage ( $V_{sense}$ ) in the worst-case scenario. Calculate  $R_{sense}$  and  $I_{L(PEAK)}$  with Equation (5) and Equation (6):

$$R_{sense} = \frac{0.8 \times V_{sense}}{I_{L(PEAK)}} \quad (5)$$

$$I_{L(PEAK)} = \frac{V_{out} \times I_{load}}{\eta V_{in}} + \frac{V_{in} \times (V_{out} - V_{in})}{2 \times L \times f_{sw} \times V_{out}} \quad (6)$$

### Selecting the Power MOSFET

The MP3398E is capable of driving a wide variety of N-channel power MOSFETS. The critical parameters of selection for a MOSFET are maximum drain-to-source voltage ( $V_{DS(MAX)}$ ), maximum current ( $I_{D(MAX)}$ ), on resistance ( $R_{DS(ON)}$ ), gate source charge ( $Q_{GS}$ ) and gate drain charge ( $Q_{GD}$ ), and total gate charge ( $Q_G$ ).

Ideally, the off-state voltage across the MOSFET is equal to the output voltage. Considering the voltage spike when it turns off,  $V_{DS(MAX)}$  should be greater than 1.5 times the output voltage.

The maximum current through the power MOSFET occurs at the minimum input voltage and the maximum output power. The maximum RMS current through the MOSFET is given using Equation (7) and Equation (8):

$$I_{RMS(MAX)} = I_{IN(MAX)} \times \sqrt{D_{MAX}} \quad (7)$$

$$D_{MAX} \approx \frac{V_{out} - V_{IN(MIN)}}{V_{out}} \quad (8)$$

The current rating of the MOSFET should be greater than  $1.5 \times I_{RMS}$ .

The on resistance of the MOSFET determines the conduction loss, which is given by Equation (9):

$$P_{\text{cond}} = I_{\text{RMS}}^2 \times R_{\text{DS(on)}} \times k \quad (9)$$

Where k is the temperature coefficient of the MOSFET.

The switching loss is related to  $Q_{\text{GD}}$  and  $Q_{\text{GS1}}$ , which determine the commutation time.  $Q_{\text{GS1}}$  is the charge between the threshold voltage and the plateau voltage when a driver charges the gate, which can be read in the  $V_{\text{GS}}$  vs.  $Q_{\text{G}}$  chart in the MOSFET datasheet.  $Q_{\text{GD}}$  is the charge during the plateau voltage. These two parameters are needed to estimate the turn-on and turn-off losses and can be calculated with Equation (10):

$$P_{\text{SW}} = \frac{Q_{\text{GS1}} \times R_{\text{G}}}{V_{\text{DR}} - V_{\text{TH}}} \times V_{\text{DS}} \times I_{\text{IN}} \times f_{\text{SW}} + \frac{Q_{\text{GD}} \times R_{\text{G}}}{V_{\text{DR}} - V_{\text{PLT}}} \times V_{\text{DS}} \times I_{\text{IN}} \times f_{\text{SW}} \quad (10)$$

Where  $V_{\text{TH}}$  is the threshold voltage,  $V_{\text{PLT}}$  is the plateau voltage,  $V_{\text{DS}}$  is the drain-source voltage, and  $R_{\text{G}}$  is the gate resistance.  $R_{\text{G}}$  is recommended to be 10-20Ω.

Please note that calculating the switching loss is the most difficult part of loss estimation. The formula above provides a simplified equation. For more accurate estimates, the equation becomes much more complex.

The total gate charge ( $Q_{\text{G}}$ ) is used to calculate the gate drive loss and can be calculated with Equation (11):

$$P_{\text{DR}} = Q_{\text{G}} \times V_{\text{DR}} \times f_{\text{SW}} \quad (11)$$

Where  $V_{\text{DR}}$  is the drive voltage.

### Selecting the Output Capacitor

The output capacitor keeps the output voltage ripple small and ensures feedback loop stability. The output capacitor impedance must be low at the switching frequency. Ceramic capacitors with X7R dielectrics are recommended for their low ESR characteristics. A 4.7μF ceramic capacitor in parallel with a 22~47μF electrolytic capacitor is sufficient for most applications.

### Setting the Over-Voltage Protection (OVP)

Open-string protection is achieved through the detection of the voltage on OVP. In some cases, an LED string failure results in the feedback voltage always being zero. The MP3398E continues boosting the output voltage higher and higher. If the output voltage reaches the programmed OVP threshold, the protection is triggered.

To ensure that the chip functions properly, an appropriate OVP voltage is required. The recommended OVP point is about 1.1 to 1.2 times higher than the output voltage for normal operation. The OVP voltage is set by an external resistor on OVP and can be calculated with Equation (12):

$$V_{\text{OVP}} = 2(V) \times \left(1 + \frac{R_{\text{HIGH}}}{R_{\text{LOW}}}\right) \quad (12)$$

### Expanding LED Channels


The MP3398E can expand the number of LED channels by using two or three ICs in parallel. To connect two ICs for a total of eight LED strings, tie the VCC pins of the master IC and the slave IC together to power the slave IC internal logic circuitry. Tie the COMP pins of the slave IC and the master IC together to regulate the voltage of all eight LED strings. The slave IC MOSFET driving signal is not used; the boost converter can be driven by the master IC only. Do not leave the ISENSE of the slave IC floating; tie it to ground. Apply the EN and DIM signals to both ICs.

### PCB Layout Guidelines

Efficient PCB layout is critical for stable operation and reducing EMI noise. For best results, follow the guidelines below:

1. Ensure that the loop among the external MOSFET, the output diode, and the output ceramic capacitor is as small and short as possible since it carries a high-frequency pulse current.
2. Separate the power ground (PGND) and signal ground (GND) to reduce noise affection.
3. Connect PGND and GND together. All logic signals refer to the signal ground.
4. Place ceramic capacitors as close to VIN and VCC as possible.

## TYPICAL APPLICATION CIRCUIT




**Figure 2: 4-String, 20 LEDs in Series, 120mA/String Application**


**NOTE:** Some components are reasonably adjustable based on real cases.

# PACKAGE INFORMATION


## TSSOP-16 EP




**TOP VIEW**




**RECOMMENDED LAND PATTERN**




**FRONT VIEW**



**SIDE VIEW**



**BOTTOM VIEW**




**DETAIL "A"**

### NOTE:


- 1) ALL DIMENSIONS ARE IN MILLIMETERS
- 2) PACKAGE LENGTH DOES NOT INCLUDE MOLD FLASH, PROTRUSION OR GATE BURR.
- 3) PACKAGE WIDTH DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION.
- 4) LEAD COPLANARITY (BOTTOM OF LEADS AFTER FORMING) SHALL BE 0.10 MILLIMETERS MAX
- 5) DRAWING CONFORMS TO JEDEC MO-153, VARIATION ABT.
- 6) DRAWING IS NOT TO SCALE

# PACKAGE INFORMATION *(continued)*


## PDIP-16



**TOP VIEW**



**FRONT VIEW**






**SIDE VIEW**

## NOTE:

- 1) CONTROL DIMENSION IS IN INCHES. DIMENSION IN BRACKET IS IN MILLIMETERS.
- 2) PACKAGE LENGTH AND WIDTH DO NOT INCLUDE MOLD FLASH, OR PROTRUSIONS.
- 3) DRAWING CONFORMS TO JEDEC MS-001.VARIATION BB.
- 4) DRAWING IS NOT TO SCALE.

# PACKAGE INFORMATION

## SOIC16



### NOTE:

- 1) CONTROL DIMENSION IS IN INCHES. DIMENSION IN BRACKET IS IN MILLIMETERS.
- 2) PACKAGE LENGTH DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.
- 3) PACKAGE WIDTH DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSIONS.
- 4) LEAD COPLANARITY (BOTTOM OF LEADS AFTER FORMING) SHALL BE 0.004" INCHES MAX.
- 5) DRAWING CONFORMS TO JEDEC MS-012, VARIATION AC.
- 6) DRAWING IS NOT TO SCALE.

## Revision History

| Revision # | Revision Date | Description                                                                                                                                                                                                                                                                                                       | Pages Updated |
|------------|---------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| 1.05       | 1/26/2021     | <ol style="list-style-type: none"> <li>For the ADIM pin description, add “If Analog dimming is not required, pulling this pin to high voltage (1.5V&lt;VADIM &lt;=5V)”</li> <li>For PWM pin description, add “If PWM dimming is not required, pulling this pin to high voltage (1.5V &lt;VPWM&lt;=5V)”</li> </ol> | Page 9        |

**NOTICE:** The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.